

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918512

Luminaire Tested: DFN2DIP-4P2F0-020D030US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918512
REPORT IS A COMBINATION OF REPORTS P899018 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US935-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3749.6 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 40
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918512
CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P918512
 CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1782	1782	1782
5°	1781	1749	1762
10°	1760	1710	1702
15°	1732	1649	1611
20°	1697	1568	1499
25°	1660	1476	1392
30°	1613	1383	1257
35°	1565	1284	1139
40°	1517	1181	1003
45°	1462	1068	881
50°	1405	954	762
55°	1344	833	647
60°	1274	707	530
65°	1193	579	474
70°	1095	460	425
75°	972	397	380
80°	795	321	320
85°	511	197	226

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1462 cd/sqm



TEST NUMBER: P918512

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.8
10°-20°	183.1	4.9
20°-30°	257.1	6.9
30°-40°	280.2	7.5
40°-50°	257.6	6.9
50°-60°	202.3	5.4
60°-70°	131.7	3.5
70°-80°	67.8	1.8
80°-90°	19.6	0.5
90°-100°	50.6	1.3
100°-110°	160.6	4.3
110°-120°	274.9	7.3
120°-130°	361.5	9.6
130°-140°	405.7	10.8
140°-150°	397.9	10.6
150°-160°	333.8	8.9
160°-170°	221.3	5.9
170°-180°	77.4	2.1
0°-30°	506.9	13.5
0°-40°	787.1	21.0
0°-60°	1247.0	33.3
0°-90°	1466.0	39.1
90°-120°	486.0	13.0
90°-150°	1651.1	44.0
90°-180°	2284.0	60.9
0°-180°	3749.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	1	9	24	23	23	4
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	



TEST NUMBER: P918512

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3



TEST NUMBER: P918512

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9



TEST NUMBER: P918512
 CATALOG NUMBER: DFN2DIP-4P2F0-020D030US935-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.91	8.66	8.96	9.71	11.13	3.87	4.62	4.92	5.67	7.09
	3H	9.56	10.22	10.62	11.29	12.73	5.03	5.70	6.09	6.76	8.20
	4H	10.14	10.78	11.22	11.84	13.29	5.46	6.10	6.53	7.16	8.61
	6H	10.54	11.13	11.63	12.19	13.65	5.76	6.34	6.84	7.41	8.87
	8H	10.66	11.21	11.74	12.29	13.75	5.84	6.39	6.92	7.48	8.93
	12H	10.71	11.23	11.80	12.31	13.79	5.87	6.40	6.96	7.47	8.95
4H	2H	7.91	8.54	8.99	9.61	11.05	4.44	5.08	5.52	6.14	7.59
	3H	9.70	10.23	10.79	11.32	12.78	5.76	6.29	6.85	7.38	8.84
	4H	10.38	10.86	11.47	11.94	13.42	6.29	6.77	7.38	7.85	9.33
	6H	10.86	11.28	11.96	12.38	13.86	6.68	7.09	7.78	8.20	9.67
	8H	11.03	11.41	12.12	12.51	14.00	6.79	7.18	7.89	8.28	9.77
	12H	11.10	11.45	12.22	12.56	14.06	6.84	7.19	7.96	8.30	9.80
8H	4H	10.33	10.72	11.43	11.81	13.30	6.55	6.93	7.65	8.03	9.52
	6H	10.87	11.19	11.99	12.33	13.81	7.03	7.35	8.15	8.49	9.98
	8H	11.07	11.35	12.20	12.47	13.98	7.21	7.49	8.34	8.61	10.11
	12H	11.19	11.44	12.32	12.55	14.09	7.31	7.55	8.44	8.67	10.21
12H	4H	10.28	10.63	11.40	11.74	13.23	6.54	6.89	7.66	8.00	9.50
	6H	10.84	11.12	11.97	12.24	13.75	7.08	7.36	8.20	8.48	9.98
	8H	11.04	11.29	12.17	12.40	13.95	7.27	7.51	8.40	8.63	10.17