

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918538

Luminaire Tested: DFN2DIP-4P2F0-040D040US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918538
REPORT IS A COMBINATION OF REPORTS P899027 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-040D040US935-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6457.5 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 73.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918538

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918538

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3356	3356	3356
5°	3354	3300	3325
10°	3320	3247	3275
15°	3265	3185	3199
20°	3192	3103	3122
25°	3120	3005	3033
30°	3030	2914	2922
35°	2945	2808	2804
40°	2842	2701	2692
45°	2738	2593	2577
50°	2625	2479	2445
55°	2506	2348	2321
60°	2370	2193	2180
65°	2221	2031	2014
70°	2032	1835	1833
75°	1775	1599	1659
80°	1459	1299	1343
85°	978	812	835

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2738 cd/sqm

TEST NUMBER: P918538

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	2.0
10°-20°	354.9	5.5
20°-30°	521.5	8.1
30°-40°	605.7	9.4
40°-50°	605.0	9.4
50°-60°	527.5	8.2
60°-70°	389.9	6.0
70°-80°	220.6	3.4
80°-90°	61.3	0.9
90°-100°	67.4	1.0
100°-110°	214.2	3.3
110°-120°	366.5	5.7
120°-130°	482.0	7.5
130°-140°	541.0	8.4
140°-150°	530.5	8.2
150°-160°	445.0	6.9
160°-170°	295.1	4.6
170°-180°	103.2	1.6
0°-30°	1002.5	15.5
0°-40°	1608.3	24.9
0°-60°	2740.7	42.4
0°-90°	3412.6	52.8
90°-120°	648.0	10.0
90°-150°	2201.5	34.1
90°-180°	3045.0	47.2
0°-180°	6457.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	1	12	32	30	31	6
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	

TEST NUMBER: P918538

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1



TEST NUMBER: P918538

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2

TEST NUMBER: P918538

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.60	12.49	12.53	13.44	14.67	11.16	12.04	12.09	12.99	14.22
	3H	13.24	14.04	14.18	15.00	16.25	12.75	13.55	13.70	14.51	15.76
	4H	13.82	14.57	14.77	15.53	16.79	13.32	14.07	14.28	15.04	16.30
	6H	14.20	14.89	15.17	15.86	17.14	13.70	14.39	14.67	15.36	16.64
	8H	14.30	14.96	15.27	15.94	17.21	13.79	14.46	14.77	15.44	16.71
	12H	14.34	14.97	15.32	15.95	17.24	13.83	14.46	14.81	15.44	16.73
4H	2H	12.05	12.81	13.02	13.77	15.03	11.70	12.45	12.66	13.41	14.68
	3H	13.89	14.52	14.87	15.52	16.79	13.49	14.12	14.46	15.11	16.39
	4H	14.59	15.17	15.57	16.15	17.45	14.17	14.74	15.15	15.73	17.03
	6H	15.09	15.58	16.08	16.59	17.89	14.65	15.15	15.65	16.16	17.46
	8H	15.23	15.69	16.22	16.69	18.01	14.79	15.25	15.79	16.26	17.57
	12H	15.29	15.71	16.30	16.73	18.05	14.84	15.26	15.86	16.28	17.60
8H	4H	14.78	15.24	15.77	16.24	17.56	14.40	14.86	15.40	15.87	17.18
	6H	15.38	15.76	16.40	16.81	18.12	15.00	15.38	16.02	16.43	17.74
	8H	15.59	15.92	16.62	16.96	18.29	15.19	15.53	16.22	16.56	17.89
	12H	15.70	16.00	16.74	17.03	18.40	15.29	15.59	16.33	16.62	17.99
12H	4H	14.76	15.18	15.78	16.20	17.52	14.39	14.81	15.41	15.83	17.15
	6H	15.41	15.74	16.44	16.78	18.11	15.03	15.37	16.06	16.40	17.73
	8H	15.63	15.93	16.66	16.95	18.33	15.25	15.55	16.28	16.57	17.95