

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915917

Luminaire Tested: DFN2DIP-4P4F0-030D030US930-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P915917  
REPORT IS A COMBINATION OF REPORTS P900600 AND P897523  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-030D030US930-RLLONL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4500.5 lumens  
Efficiency: N/A  
Efficacy: 88.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 50.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.983  
Total Harmonic Distortion (THDi): 0.073  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P915917  
CATALOG NUMBER: DFN2DIP-4P4F0-030D030US930-RLLONL

### Luminous Intensity Polar Plot



TEST NUMBER: P915917

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US930-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46				46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45				40	
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39				34	
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34				29	
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29				26	
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26				23	
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23				20	
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				16	
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17				15	
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	656	656	656
5°	657	646	650
10°	650	633	629
15°	642	612	596
20°	630	584	557
25°	618	552	518
30°	601	519	469
35°	585	483	426
40°	569	446	377
45°	551	406	332
50°	531	364	288
55°	511	320	246
60°	487	274	203
65°	460	227	183
70°	428	184	166
75°	386	162	151
80°	327	137	132
85°	228	93	101

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 551 cd/sqm



TEST NUMBER: P915917

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US930-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.7	2.1
10°-20°	260.1	5.8
20°-30°	365.1	8.1
30°-40°	398.0	8.8
40°-50°	365.8	8.1
50°-60°	287.3	6.4
60°-70°	187.0	4.2
70°-80°	96.3	2.1
80°-90°	26.0	0.6
90°-100°	27.2	0.6
100°-110°	101.5	2.3
110°-120°	269.1	6.0
120°-130°	446.3	9.9
130°-140°	474.1	10.5
140°-150°	440.6	9.8
150°-160°	354.3	7.9
160°-170°	228.3	5.1
170°-180°	78.6	1.7
0°-30°	720.0	16.0
0°-40°	1118.0	24.8
0°-60°	1771.2	39.4
0°-90°	2080.5	46.2
90°-120°	397.8	8.8
90°-150°	1758.9	39.1
90°-180°	2420.0	53.8
0°-180°	4500.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	1	7	12	15	16	4
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	



TEST NUMBER: P915917

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US930-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2



TEST NUMBER: P915917

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US930-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5



TEST NUMBER: P915917  
 CATALOG NUMBER: DFN2DIP-4P4F0-030D030US930-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.34	6.14	6.33	7.14	8.47	1.30	2.10	2.29	3.10	4.43
	3H	7.02	7.73	8.02	8.75	10.09	2.48	3.20	3.49	4.21	5.56
	4H	7.63	8.31	8.65	9.32	10.68	2.94	3.61	3.95	4.63	5.98
	6H	8.05	8.68	9.08	9.70	11.06	3.26	3.88	4.29	4.90	6.27
	8H	8.18	8.77	9.22	9.81	11.17	3.35	3.94	4.38	4.97	6.34
	12H	8.25	8.81	9.28	9.84	11.22	3.39	3.95	4.43	4.98	6.37
4H	2H	5.35	6.03	6.38	7.04	8.40	1.89	2.57	2.92	3.58	4.94
	3H	7.18	7.75	8.22	8.79	10.16	3.24	3.80	4.27	4.85	6.22
	4H	7.88	8.39	8.92	9.43	10.82	3.79	4.30	4.83	5.34	6.73
	6H	8.40	8.84	9.45	9.90	11.29	4.21	4.65	5.26	5.71	7.10
	8H	8.58	8.99	9.63	10.04	11.44	4.34	4.75	5.39	5.80	7.21
	12H	8.67	9.05	9.74	10.11	11.52	4.41	4.78	5.47	5.84	7.25
8H	4H	7.85	8.26	8.90	9.31	10.71	4.07	4.48	5.12	5.53	6.94
	6H	8.42	8.76	9.49	9.85	11.25	4.59	4.93	5.67	6.02	7.42
	8H	8.64	8.94	9.72	10.01	11.43	4.79	5.08	5.87	6.16	7.58
	12H	8.78	9.04	9.86	10.11	11.57	4.91	5.17	5.99	6.24	7.70
12H	4H	7.80	8.17	8.87	9.23	10.64	4.08	4.45	5.14	5.51	6.92
	6H	8.39	8.69	9.47	9.77	11.19	4.64	4.94	5.72	6.02	7.44
	8H	8.62	8.88	9.70	9.95	11.41	4.85	5.12	5.94	6.19	7.65