

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915921

Luminaire Tested: DFN2DIP-4P4F0-030D040US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915921
REPORT IS A COMBINATION OF REPORTS P900612 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-030D040US930-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5307.6 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 58.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915921
CATALOG NUMBER: DFN2DIP-4P4F0-030D040US930-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P915921

CATALOG NUMBER: DFN2DIP-4P4F0-030D040US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19			
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15			
8	53	42	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	656	656	656
5°	657	646	650
10°	650	633	629
15°	642	612	596
20°	630	584	557
25°	618	552	518
30°	601	519	469
35°	585	483	426
40°	569	446	377
45°	551	406	332
50°	531	364	288
55°	511	320	246
60°	487	274	203
65°	460	227	183
70°	428	184	166
75°	386	162	151
80°	327	137	132
85°	228	93	101

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 566 cd/sqm



TEST NUMBER: P915921

CATALOG NUMBER: DFN2DIP-4P4F0-030D040US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.8
10°-20°	260.1	4.9
20°-30°	365.1	6.9
30°-40°	398.0	7.5
40°-50°	365.8	6.9
50°-60°	287.3	5.4
60°-70°	187.0	3.5
70°-80°	96.3	1.8
80°-90°	26.5	0.5
90°-100°	36.3	0.7
100°-110°	135.3	2.5
110°-120°	358.8	6.8
120°-130°	595.1	11.2
130°-140°	632.1	11.9
140°-150°	587.5	11.1
150°-160°	472.3	8.9
160°-170°	304.4	5.7
170°-180°	104.8	2.0
0°-30°	720.0	13.6
0°-40°	1118.0	21.1
0°-60°	1771.2	33.4
0°-90°	2080.9	39.2
90°-120°	530.4	10.0
90°-150°	2345.2	44.2
90°-180°	3227.0	60.8
0°-180°	5307.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	1	10	16	20	21	5
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	



TEST NUMBER: P915921

CATALOG NUMBER: DFN2DIP-4P4F0-030D040US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9



TEST NUMBER: P915921

CATALOG NUMBER: DFN2DIP-4P4F0-030D040US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7



TEST NUMBER: P915921
 CATALOG NUMBER: DFN2DIP-4P4F0-030D040US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.60	5.35	5.65	6.40	7.82	0.56	1.31	1.61	2.36	3.78
	3H	6.28	6.95	7.34	8.01	9.45	1.75	2.42	2.81	3.48	4.91
	4H	6.89	7.52	7.96	8.58	10.03	2.19	2.83	3.27	3.89	5.34
	6H	7.31	7.89	8.39	8.96	10.42	2.51	3.10	3.59	4.16	5.62
	8H	7.44	7.99	8.52	9.07	10.52	2.60	3.16	3.69	4.24	5.69
	12H	7.50	8.03	8.59	9.10	10.58	2.64	3.17	3.73	4.25	5.72
4H	2H	4.61	5.24	5.69	6.31	7.75	1.15	1.78	2.23	2.85	4.29
	3H	6.44	6.97	7.52	8.06	9.51	2.49	3.02	3.58	4.11	5.57
	4H	7.13	7.62	8.22	8.70	10.17	3.04	3.53	4.13	4.60	6.08
	6H	7.65	8.06	8.75	9.17	10.64	3.46	3.87	4.56	4.98	6.45
	8H	7.82	8.21	8.92	9.31	10.80	3.59	3.97	4.69	5.07	6.56
	12H	7.92	8.27	9.03	9.38	10.87	3.65	4.00	4.77	5.11	6.60
8H	4H	7.09	7.48	8.19	8.58	10.06	3.32	3.71	4.42	4.80	6.29
	6H	7.66	7.98	8.78	9.12	10.60	3.84	4.16	4.96	5.29	6.78
	8H	7.88	8.16	9.01	9.28	10.79	4.03	4.31	5.16	5.43	6.93
	12H	8.02	8.27	9.15	9.38	10.93	4.15	4.39	5.28	5.51	7.05
12H	4H	7.04	7.39	8.16	8.50	9.99	3.32	3.67	4.44	4.78	6.27
	6H	7.64	7.92	8.77	9.04	10.54	3.89	4.17	5.01	5.29	6.79
	8H	7.86	8.11	8.99	9.22	10.76	4.10	4.34	5.23	5.46	7.00