

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921245

Luminaire Tested: DFN2DIP-4P2F0-020D040US940-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921245
REPORT IS A COMBINATION OF REPORTS P900544 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D040US940-RLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5047.1 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 49.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921245
CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P921245

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	30
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	18	16	15	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1846	1846	1846
5°	1845	1812	1825
10°	1823	1771	1763
15°	1794	1708	1668
20°	1757	1624	1553
25°	1720	1529	1442
30°	1670	1433	1302
35°	1621	1329	1180
40°	1571	1223	1039
45°	1514	1106	912
50°	1455	988	789
55°	1392	862	670
60°	1320	732	549
65°	1236	600	491
70°	1134	477	440
75°	1006	411	394
80°	823	333	332
85°	530	205	235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1514 cd/sqm



TEST NUMBER: P921245

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	1.4
10°-20°	189.6	3.8
20°-30°	266.3	5.3
30°-40°	290.2	5.8
40°-50°	266.8	5.3
50°-60°	209.5	4.2
60°-70°	136.4	2.7
70°-80°	70.2	1.4
80°-90°	20.0	0.4
90°-100°	39.7	0.8
100°-110°	148.0	2.9
110°-120°	392.4	7.8
120°-130°	650.9	12.9
130°-140°	691.4	13.7
140°-150°	642.6	12.7
150°-160°	516.6	10.2
160°-170°	332.9	6.6
170°-180°	114.6	2.3
0°-30°	525.0	10.4
0°-40°	815.2	16.2
0°-60°	1291.4	25.6
0°-90°	1518.0	30.1
90°-120°	580.1	11.5
90°-150°	2565.0	50.8
90°-180°	3529.0	69.9
0°-180°	5047.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	1	10	17	22	24	5
95°	56	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	537	134	72	493
125°	708	720	736	742	745	632
135°	876	890	898	907	905	677
145°	1016	1016	1030	1036	1032	636
155°	1119	1112	1122	1127	1120	516
165°	1179	1174	1177	1183	1177	333
175°	1206	1200	1202	1208	1199	115
180°	1204	1204	1204	1204	1204	



TEST NUMBER: P921245

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	0.8	10.4	17.4	21.8	23.5
92.5°	21.8	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.3	37.5
97.5°	101.9	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.5	58.3
102.5°	211.6	210.0	51.4	60.9	63.6
105°	264.7	291.0	53.1	62.7	66.2
107.5°	326.6	348.4	54.9	64.5	67.9
110°	385.9	404.1	152.5	65.4	68.8



TEST NUMBER: P921245

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.7	457.3	442.5	67.1	69.7
115°	500.8	515.6	537.4	134.1	71.5
117.5°	552.2	569.6	584.5	459.9	231.7
120°	609.8	622.8	638.5	649.0	531.4
122.5°	658.4	672.4	689.9	695.1	696.0
125°	708.1	719.5	736.0	742.2	744.8
127.5°	753.4	765.6	778.7	787.5	788.3
130°	796.1	810.1	819.6	829.2	828.4
132.5°	839.6	851.0	860.6	868.4	867.6
135°	876.3	890.3	898.0	906.8	905.1
137.5°	914.5	925.0	933.8	942.4	939.9
140°	952.0	959.0	968.6	976.4	972.1
142.5°	983.5	989.5	1000.9	1007.7	1003.4
145°	1016.5	1015.7	1030.4	1036.5	1032.2
147.5°	1045.2	1042.6	1057.4	1061.8	1058.4
150°	1073.1	1067.0	1081.0	1086.2	1081.8
152.5°	1096.6	1089.7	1102.7	1108.0	1101.9
155°	1119.3	1111.5	1121.9	1127.1	1120.2
157.5°	1137.6	1130.6	1138.5	1144.6	1137.6
160°	1153.2	1148.0	1153.2	1158.4	1152.4
162.5°	1167.2	1162.0	1166.4	1172.4	1164.6
165°	1179.4	1174.2	1176.8	1182.9	1176.8
167.5°	1189.0	1183.7	1186.4	1192.5	1184.6
170°	1196.9	1191.6	1193.3	1199.4	1191.6
172.5°	1202.0	1196.9	1198.6	1204.7	1196.9
175°	1206.3	1200.2	1202.0	1208.1	1199.4
177.5°	1208.1	1202.0	1202.9	1209.1	1201.2
180°	1203.8	1203.8	1203.8	1203.8	1203.8



TEST NUMBER: P921245
 CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.92	7.61	8.04	8.72	10.25	2.88	3.57	4.00	4.68	6.21
	3H	8.56	9.18	9.69	10.30	11.84	4.04	4.66	5.16	5.77	7.32
	4H	9.15	9.74	10.28	10.85	12.41	4.47	5.06	5.60	6.17	7.73
	6H	9.55	10.08	10.69	11.20	12.77	4.76	5.30	5.91	6.42	7.99
	8H	9.66	10.17	10.80	11.30	12.86	4.84	5.35	5.99	6.49	8.04
	12H	9.71	10.19	10.86	11.32	12.90	4.87	5.36	6.02	6.48	8.06
4H	2H	6.92	7.50	8.06	8.62	10.17	3.45	4.04	4.59	5.15	6.71
	3H	8.70	9.19	9.85	10.33	11.90	4.76	5.25	5.91	6.39	7.96
	4H	9.37	9.82	10.52	10.95	12.54	5.29	5.73	6.44	6.87	8.45
	6H	9.86	10.24	11.02	11.40	12.97	5.67	6.06	6.83	7.21	8.79
	8H	10.02	10.38	11.17	11.52	13.11	5.79	6.15	6.94	7.29	8.88
	12H	10.09	10.42	11.26	11.58	13.17	5.84	6.16	7.01	7.32	8.91
8H	4H	9.33	9.68	10.48	10.83	12.42	5.54	5.90	6.70	7.05	8.64
	6H	9.86	10.16	11.04	11.34	12.93	6.03	6.32	7.20	7.51	9.10
	8H	10.06	10.32	11.24	11.49	13.10	6.20	6.46	7.38	7.62	9.23
	12H	10.18	10.40	11.36	11.57	13.21	6.30	6.52	7.48	7.69	9.33
12H	4H	9.27	9.59	10.44	10.75	12.35	5.54	5.86	6.71	7.02	8.62
	6H	9.83	10.09	11.01	11.26	12.87	6.07	6.33	7.25	7.49	9.10
	8H	10.03	10.26	11.22	11.42	13.07	6.25	6.48	7.44	7.64	9.29