

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923968

Luminaire Tested: DFN2DIP-4P2F0-020D030US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923968
REPORT IS A COMBINATION OF REPORTS P899018 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US950-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4154.6 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 40
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923968

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923968

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1975	1975	1975
5°	1974	1938	1952
10°	1950	1895	1886
15°	1919	1828	1785
20°	1880	1737	1661
25°	1840	1636	1543
30°	1787	1532	1393
35°	1735	1422	1262
40°	1681	1308	1112
45°	1620	1183	976
50°	1556	1057	844
55°	1489	923	717
60°	1412	783	587
65°	1322	642	525
70°	1213	510	471
75°	1077	440	421
80°	881	356	356
85°	567	218	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1620 cd/sqm

TEST NUMBER: P923968

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	1.8
10°-20°	202.9	4.9
20°-30°	284.8	6.9
30°-40°	310.5	7.5
40°-50°	285.4	6.9
50°-60°	224.1	5.4
60°-70°	145.9	3.5
70°-80°	75.1	1.8
80°-90°	21.7	0.5
90°-100°	56.0	1.3
100°-110°	178.0	4.3
110°-120°	304.6	7.3
120°-130°	400.5	9.6
130°-140°	449.6	10.8
140°-150°	440.9	10.6
150°-160°	369.8	8.9
160°-170°	245.3	5.9
170°-180°	85.7	2.1
0°-30°	561.6	13.5
0°-40°	872.1	21.0
0°-60°	1381.7	33.3
0°-90°	1624.4	39.1
90°-120°	538.5	13.0
90°-150°	1829.5	44.0
90°-180°	2530.0	60.9
0°-180°	4154.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	789	789	789	789	789	
5°	789	785	776	782	780	75
15°	750	742	718	704	697	211
25°	681	658	611	582	571	313
35°	587	550	488	442	427	367
45°	480	432	357	306	289	370
55°	365	309	232	189	176	326
65°	246	188	124	100	98	244
75°	131	81	57	52	51	139
85°	31	16	14	14	14	35
90°	1	10	27	25	26	4
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P923968

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	788.6	788.6	788.6	788.6	788.6
2.5°	792.1	788.6	780.7	787.9	786.5
5°	788.6	785.0	775.7	782.2	780.0
7.5°	782.2	777.9	767.9	770.7	767.1
10°	773.6	768.5	754.3	752.1	747.9
12.5°	762.9	756.4	737.2	733.0	725.0
15°	750.0	742.1	717.9	704.3	697.3
17.5°	735.1	723.6	693.7	677.9	666.6
20°	717.9	703.6	668.0	650.2	634.4
22.5°	699.4	683.0	641.6	617.3	606.6
25°	680.9	658.0	610.8	581.7	570.9
27.5°	658.7	634.4	582.3	548.7	532.3
30°	635.2	608.0	550.9	514.6	495.2
32.5°	612.3	579.5	521.0	478.1	460.3
35°	586.6	550.3	487.5	442.5	426.7
37.5°	561.6	522.3	456.0	406.8	388.9
40°	535.2	492.5	423.2	372.5	353.9
42.5°	508.1	462.5	390.4	337.5	319.8
45°	479.6	431.7	356.9	306.1	289.0
47.5°	452.5	401.8	324.7	274.0	258.3
50°	422.5	371.9	293.4	244.0	229.2
52.5°	393.1	339.6	263.3	216.3	202.7
55°	364.6	309.0	231.9	189.2	175.5
57.5°	335.4	278.3	204.2	164.2	152.7
60°	305.5	248.3	174.9	138.5	127.1
62.5°	276.2	219.1	149.9	115.6	109.9
65°	246.2	188.4	124.2	100.0	97.8
67.5°	217.7	159.8	100.0	87.8	85.7
70°	187.7	132.0	82.7	75.7	72.8
72.5°	159.1	106.3	69.2	63.5	62.1
75°	131.3	81.3	57.0	52.1	51.4
77.5°	103.5	57.8	44.9	42.1	40.6
80°	77.8	41.4	34.2	31.4	31.4
82.5°	54.2	27.9	23.6	22.1	22.1
85°	30.6	15.6	13.5	13.5	13.5
87.5°	11.4	5.7	5.7	5.0	5.0
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P923968

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P923968

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.26	9.01	9.31	10.06	11.48	4.23	4.97	5.28	6.03	7.45
	3H	9.91	10.58	10.97	11.64	13.08	5.39	6.06	6.45	7.12	8.56
	4H	10.50	11.13	11.57	12.20	13.64	5.82	6.45	6.89	7.52	8.96
	6H	10.90	11.48	11.98	12.55	14.01	6.12	6.70	7.20	7.77	9.22
	8H	11.01	11.57	12.10	12.65	14.10	6.20	6.75	7.28	7.83	9.28
	12H	11.06	11.59	12.15	12.67	14.14	6.23	6.75	7.32	7.83	9.30
4H	2H	8.27	8.90	9.34	9.96	11.41	4.80	5.43	5.88	6.50	7.94
	3H	10.06	10.59	11.15	11.68	13.14	6.12	6.64	7.20	7.73	9.19
	4H	10.73	11.22	11.82	12.30	13.78	6.64	7.13	7.74	8.21	9.69
	6H	11.22	11.63	12.32	12.74	14.21	7.04	7.45	8.13	8.55	10.03
	8H	11.38	11.77	12.48	12.86	14.35	7.15	7.54	8.25	8.63	10.12
	12H	11.46	11.81	12.58	12.92	14.41	7.20	7.55	8.32	8.66	10.15
8H	4H	10.69	11.07	11.79	12.17	13.66	6.90	7.29	8.00	8.39	9.88
	6H	11.23	11.55	12.35	12.68	14.17	7.39	7.71	8.51	8.85	10.33
	8H	11.43	11.71	12.55	12.83	14.33	7.56	7.84	8.69	8.96	10.47
	12H	11.55	11.79	12.68	12.91	14.45	7.66	7.91	8.79	9.02	10.57
12H	4H	10.64	10.99	11.75	12.09	13.59	6.90	7.25	8.02	8.36	9.85
	6H	11.20	11.48	12.33	12.60	14.10	7.43	7.71	8.56	8.83	10.34
	8H	11.40	11.65	12.53	12.76	14.31	7.62	7.87	8.75	8.98	10.53