

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916019

Luminaire Tested: DFN2DIP-4P4F0-070D050US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916019
REPORT IS A COMBINATION OF REPORTS P900631 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D050US930-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9685.8 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 114.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916019
CATALOG NUMBER: DFN2DIP-4P4F0-070D050US930-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P916019
 CATALOG NUMBER: DFN2DIP-4P4F0-070D050US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45	41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1441	1441	1441
5°	1443	1421	1431
10°	1431	1402	1412
15°	1411	1380	1382
20°	1382	1348	1352
25°	1354	1310	1316
30°	1319	1275	1271
35°	1285	1233	1224
40°	1244	1191	1178
45°	1203	1149	1132
50°	1158	1105	1078
55°	1111	1054	1029
60°	1058	993	973
65°	1000	930	906
70°	926	854	835
75°	823	762	770
80°	700	646	644
85°	509	444	435

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1203 cd/sqm



TEST NUMBER: P916019

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.0	2.2
10°-20°	588.1	6.1
20°-30°	864.2	8.9
30°-40°	1003.7	10.4
40°-50°	1002.5	10.4
50°-60°	874.2	9.0
60°-70°	646.2	6.7
70°-80°	365.6	3.8
80°-90°	98.9	1.0
90°-100°	45.4	0.5
100°-110°	169.1	1.7
110°-120°	448.5	4.6
120°-130°	743.9	7.7
130°-140°	790.2	8.2
140°-150°	734.4	7.6
150°-160°	590.4	6.1
160°-170°	380.5	3.9
170°-180°	130.9	1.4
0°-30°	1661.3	17.2
0°-40°	2665.1	27.5
0°-60°	4541.7	46.9
0°-90°	5652.4	58.4
90°-120°	663.0	6.8
90°-150°	2931.5	30.3
90°-180°	4033.0	41.6
0°-180°	9685.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2221	2221	2221	2221	2221	
5°	2221	2212	2189	2206	2202	211
15°	2114	2101	2073	2082	2071	595
25°	1913	1896	1860	1864	1860	880
35°	1651	1629	1595	1582	1572	1031
45°	1343	1328	1296	1273	1264	1037
55°	1016	1004	978	952	942	909
65°	686	673	651	632	621	678
75°	359	355	344	331	335	383
85°	88	85	83	77	75	98
90°	1	12	20	25	27	9
95°	65	32	39	44	43	77
105°	303	333	61	72	76	323
115°	572	589	614	153	82	564
125°	809	822	841	848	851	722
135°	1002	1018	1026	1036	1034	774
145°	1162	1161	1178	1185	1180	727
155°	1279	1270	1282	1288	1280	589
165°	1348	1342	1345	1352	1345	381
175°	1379	1372	1374	1381	1371	131
180°	1376	1376	1376	1376	1376	



TEST NUMBER: P916019

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2220.6	2220.6	2220.6	2220.6	2220.6
2.5°	2233.6	2222.9	2199.3	2220.6	2216.6
5°	2220.6	2212.3	2188.7	2205.7	2201.6
7.5°	2205.7	2193.0	2169.4	2186.7	2182.4
10°	2182.4	2167.4	2141.8	2158.8	2152.5
12.5°	2150.2	2137.5	2111.9	2122.5	2118.2
15°	2114.0	2101.3	2073.4	2082.0	2071.3
17.5°	2069.1	2056.4	2028.5	2039.2	2028.5
20°	2019.9	2007.3	1977.3	1983.7	1975.3
22.5°	1971.0	1951.7	1923.9	1923.9	1919.5
25°	1913.3	1896.2	1860.0	1864.1	1860.0
27.5°	1849.1	1834.2	1806.5	1800.2	1789.5
30°	1785.3	1768.0	1736.1	1729.7	1721.1
32.5°	1716.8	1704.1	1669.9	1657.0	1648.4
35°	1650.7	1629.4	1595.1	1582.2	1571.6
37.5°	1575.9	1556.6	1522.4	1507.5	1496.8
40°	1499.1	1481.9	1447.6	1428.6	1420.0
42.5°	1424.3	1407.1	1373.1	1351.6	1338.9
45°	1343.2	1328.3	1296.1	1272.8	1264.1
47.5°	1264.1	1249.2	1215.0	1191.4	1178.8
50°	1180.8	1170.1	1140.2	1110.4	1099.7
52.5°	1099.7	1084.8	1057.1	1033.6	1018.6
55°	1016.5	1003.6	978.0	952.4	941.8
57.5°	933.2	922.5	894.6	869.0	860.5
60°	849.8	841.4	811.5	788.0	781.6
62.5°	768.7	753.7	732.5	711.2	702.5
65°	685.6	672.6	651.3	632.1	621.4
67.5°	600.1	589.3	570.2	555.3	546.7
70°	521.1	512.5	493.2	478.3	469.9
72.5°	439.9	431.4	420.7	405.8	399.4
75°	358.6	354.6	343.6	331.0	335.3
77.5°	286.2	277.5	273.2	266.8	260.6
80°	213.6	211.4	207.1	200.7	196.4
82.5°	145.2	145.2	143.2	134.6	134.6
85°	87.5	85.4	83.4	76.8	74.8
87.5°	38.5	34.2	29.9	23.6	21.3
90°	1.0	11.9	19.9	24.9	26.8
92.5°	24.9	21.0	23.9	25.9	26.8
95°	64.7	31.8	38.8	43.9	42.8
97.5°	116.4	34.9	50.7	53.8	54.7
100°	176.3	39.9	56.7	64.7	66.7
102.5°	241.9	239.9	58.8	69.6	72.7
105°	302.6	332.6	60.7	71.7	75.7
107.5°	373.3	398.1	62.8	73.6	77.7
110°	441.1	461.9	174.2	74.7	78.6



TEST NUMBER: P916019

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.8	522.6	505.7	76.6	79.7
115°	572.4	589.3	614.2	153.4	81.7
117.5°	631.1	651.0	668.1	525.5	264.8
120°	696.8	711.8	729.7	741.7	607.2
122.5°	752.5	768.5	788.5	794.4	795.5
125°	809.3	822.3	841.2	848.2	851.2
127.5°	861.0	875.0	890.1	899.9	900.9
130°	909.9	925.9	936.7	947.7	946.8
132.5°	959.7	972.7	983.5	992.5	991.6
135°	1001.5	1017.5	1026.3	1036.4	1034.4
137.5°	1045.2	1057.2	1067.2	1077.2	1074.2
140°	1088.0	1096.1	1106.9	1115.9	1111.0
142.5°	1124.0	1131.0	1143.9	1151.8	1146.8
145°	1161.8	1160.7	1177.6	1184.6	1179.7
147.5°	1194.6	1191.6	1208.5	1213.5	1209.6
150°	1226.5	1219.5	1235.4	1241.4	1236.4
152.5°	1253.3	1245.4	1260.3	1266.3	1259.3
155°	1279.2	1270.3	1282.2	1288.2	1280.3
157.5°	1300.1	1292.2	1301.1	1308.1	1300.1
160°	1318.1	1312.1	1318.1	1324.0	1317.0
162.5°	1333.9	1328.0	1332.9	1339.9	1331.0
165°	1347.9	1342.0	1344.9	1351.8	1344.9
167.5°	1358.9	1352.8	1355.9	1362.9	1353.9
170°	1367.8	1361.8	1363.8	1370.8	1361.8
172.5°	1373.8	1367.8	1369.9	1376.8	1367.8
175°	1378.8	1371.7	1373.8	1380.7	1370.8
177.5°	1380.7	1373.8	1374.8	1381.8	1372.8
180°	1375.7	1375.7	1375.7	1375.7	1375.7



TEST NUMBER: P916019
 CATALOG NUMBER: DFN2DIP-4P4F0-070D050US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.30	10.24	10.18	11.14	12.29	8.85	9.79	9.73	10.70	11.84
	3H	10.97	11.81	11.86	12.73	13.90	10.48	11.32	11.37	12.24	13.41
	4H	11.56	12.36	12.47	13.28	14.46	11.07	11.87	11.98	12.79	13.97
	6H	11.97	12.71	12.89	13.63	14.83	11.47	12.21	12.39	13.13	14.33
	8H	12.08	12.78	13.01	13.73	14.92	11.58	12.28	12.51	13.22	14.42
	12H	12.14	12.80	13.07	13.74	14.96	11.63	12.29	12.56	13.23	14.45
4H	2H	9.77	10.57	10.68	11.49	12.67	9.41	10.21	10.33	11.13	12.31
	3H	11.65	12.32	12.57	13.26	14.46	11.24	11.91	12.17	12.86	14.05
	4H	12.37	12.98	13.31	13.92	15.14	11.95	12.56	12.88	13.50	14.72
	6H	12.90	13.42	13.84	14.39	15.61	12.46	12.99	13.41	13.96	15.18
	8H	13.05	13.54	14.00	14.50	15.74	12.61	13.10	13.56	14.06	15.30
	12H	13.13	13.57	14.10	14.55	15.79	12.68	13.12	13.65	14.10	15.34
8H	4H	12.57	13.07	13.53	14.03	15.26	12.20	12.69	13.15	13.65	14.89
	6H	13.22	13.62	14.19	14.62	15.86	12.83	13.24	13.81	14.24	15.48
	8H	13.44	13.80	14.43	14.79	16.04	13.05	13.41	14.03	14.40	15.65
	12H	13.58	13.90	14.57	14.88	16.18	13.17	13.49	14.16	14.47	15.77
12H	4H	12.56	13.01	13.54	13.99	15.23	12.20	12.64	13.17	13.62	14.86
	6H	13.25	13.61	14.23	14.60	15.85	12.87	13.23	13.86	14.23	15.48
	8H	13.50	13.81	14.49	14.80	16.10	13.12	13.43	14.11	14.42	15.72