

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902215

Luminaire Tested: DFN2DIP-4P3F0-040D020US830-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902215
REPORT IS A COMBINATION OF REPORTS P900553 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D020US830-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5598.7 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 53
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902215
CATALOG NUMBER: DFN2DIP-4P3F0-040D020US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P902215
 CATALOG NUMBER: DFN2DIP-4P3F0-040D020US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67	67	67	67
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56	56	56	56
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47	47	47	47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40	40	40	40
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34	34	34	34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30	30	30	30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26	26	26	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23	23	23	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21	21	21	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19	19	19	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1672	1672	1672
5°	1673	1647	1659
10°	1659	1624	1636
15°	1633	1596	1600
20°	1599	1558	1564
25°	1565	1513	1522
30°	1523	1470	1469
35°	1483	1420	1412
40°	1434	1370	1358
45°	1385	1319	1303
50°	1331	1266	1240
55°	1275	1205	1181
60°	1211	1132	1114
65°	1142	1056	1035
70°	1053	964	949
75°	931	853	870
80°	782	712	719
85°	551	471	471

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1385 cd/sqm



TEST NUMBER: P902215

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	2.5
10°-20°	388.5	6.9
20°-30°	570.9	10.2
30°-40°	663.1	11.8
40°-50°	662.3	11.8
50°-60°	577.5	10.3
60°-70°	426.9	7.6
70°-80°	241.5	4.3
80°-90°	64.9	1.2
90°-100°	21.0	0.4
100°-110°	78.2	1.4
110°-120°	207.4	3.7
120°-130°	344.0	6.1
130°-140°	365.4	6.5
140°-150°	339.6	6.1
150°-160°	273.0	4.9
160°-170°	175.9	3.1
170°-180°	60.6	1.1
0°-30°	1097.5	19.6
0°-40°	1760.6	31.4
0°-60°	3000.3	53.6
0°-90°	3733.6	66.7
90°-120°	306.6	5.5
90°-150°	1355.6	24.2
90°-180°	1865.0	33.3
0°-180°	5598.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	0	6	9	12	12	5
95°	30	15	18	20	20	35
105°	140	154	28	33	35	150
115°	265	272	284	71	38	261
125°	374	380	389	392	394	334
135°	463	470	475	479	478	358
145°	537	537	545	548	546	336
155°	592	587	593	596	592	273
165°	623	621	622	625	622	176
175°	638	634	635	638	634	61
180°	636	636	636	636	636	



TEST NUMBER: P902215

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	0.5	5.6	9.1	11.5	12.4
92.5°	11.5	9.7	11.0	12.0	12.4
95°	29.9	14.7	17.9	20.3	19.8
97.5°	53.8	16.1	23.5	24.9	25.4
100°	81.5	18.4	26.2	29.9	30.8
102.5°	111.9	110.9	27.1	32.2	33.6
105°	140.0	153.7	28.1	33.1	35.0
107.5°	172.7	184.1	29.0	34.0	35.9
110°	204.0	213.6	80.6	34.6	36.4



TEST NUMBER: P902215

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	233.4	241.7	233.8	35.4	36.9
115°	264.7	272.5	284.1	70.9	37.8
117.5°	291.8	301.0	308.9	243.1	122.4
120°	322.3	329.1	337.4	343.0	280.8
122.5°	348.0	355.3	364.6	367.3	367.9
125°	374.3	380.2	389.0	392.2	393.6
127.5°	398.2	404.6	411.6	416.1	416.6
130°	420.8	428.1	433.2	438.3	437.8
132.5°	443.7	449.8	454.8	458.9	458.5
135°	463.2	470.5	474.6	479.3	478.3
137.5°	483.3	488.9	493.5	498.1	496.7
140°	503.1	506.9	511.9	516.0	513.8
142.5°	519.7	523.0	529.0	532.6	530.3
145°	537.2	536.8	544.6	547.8	545.5
147.5°	552.4	551.0	558.8	561.1	559.3
150°	567.1	563.9	571.3	574.0	571.7
152.5°	579.6	575.9	582.8	585.6	582.3
155°	591.5	587.4	593.0	595.7	592.0
157.5°	601.2	597.6	601.7	604.9	601.2
160°	609.5	606.7	609.5	612.3	609.1
162.5°	616.8	614.1	616.4	619.6	615.5
165°	623.3	620.6	621.9	625.2	621.9
167.5°	628.4	625.6	627.0	630.3	626.0
170°	632.5	629.7	630.7	633.9	629.7
172.5°	635.3	632.5	633.5	636.7	632.5
175°	637.5	634.3	635.3	638.5	633.9
177.5°	638.5	635.3	635.7	638.9	634.8
180°	636.2	636.2	636.2	636.2	636.2



TEST NUMBER: P902215
 CATALOG NUMBER: DFN2DIP-4P3F0-040D020US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.44	11.47	11.24	12.29	13.30	9.99	11.03	10.79	11.85	12.86
	3H	12.11	13.03	12.92	13.87	14.91	11.62	12.54	12.43	13.38	14.42
	4H	12.70	13.58	13.53	14.41	15.47	12.20	13.08	13.03	13.92	14.97
	6H	13.10	13.91	13.95	14.76	15.82	12.60	13.41	13.45	14.26	15.32
	8H	13.21	13.98	14.06	14.85	15.91	12.71	13.48	13.56	14.35	15.41
	12H	13.26	14.00	14.12	14.86	15.95	12.75	13.49	13.61	14.35	15.44
4H	2H	10.91	11.79	11.75	12.63	13.68	10.56	11.44	11.39	12.28	13.33
	3H	12.79	13.52	13.64	14.40	15.46	12.38	13.12	13.23	13.99	15.05
	4H	13.51	14.18	14.37	15.05	16.14	13.08	13.75	13.94	14.62	15.72
	6H	14.03	14.61	14.90	15.50	16.60	13.60	14.17	14.47	15.07	16.17
	8H	14.18	14.72	15.06	15.61	16.72	13.74	14.28	14.62	15.17	16.28
	12H	14.26	14.75	15.16	15.65	16.77	13.81	14.30	14.71	15.21	16.32
8H	4H	13.71	14.25	14.59	15.14	16.25	13.34	13.88	14.22	14.77	15.88
	6H	14.35	14.79	15.25	15.72	16.83	13.96	14.41	14.87	15.34	16.45
	8H	14.57	14.96	15.48	15.89	17.01	14.17	14.57	15.09	15.49	16.62
	12H	14.70	15.05	15.62	15.97	17.15	14.29	14.64	15.21	15.56	16.74
12H	4H	13.71	14.19	14.61	15.10	16.22	13.34	13.83	14.24	14.73	15.85
	6H	14.38	14.77	15.29	15.70	16.82	14.00	14.40	14.92	15.33	16.45
	8H	14.62	14.97	15.54	15.89	17.07	14.24	14.59	15.16	15.51	16.69