

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902218

Luminaire Tested: DFN2DIP-4P3F0-040D030US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902218
REPORT IS A COMBINATION OF REPORTS P899043 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D030US830-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6234.9 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902218
CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P902218

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55	50
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1672	1672	1672
5°	1673	1647	1659
10°	1659	1624	1636
15°	1633	1596	1600
20°	1599	1558	1564
25°	1565	1513	1522
30°	1523	1470	1469
35°	1483	1420	1412
40°	1434	1370	1358
45°	1385	1319	1303
50°	1331	1266	1240
55°	1275	1205	1181
60°	1211	1132	1114
65°	1142	1056	1035
70°	1053	964	949
75°	931	853	870
80°	782	712	719
85°	551	471	471

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1385 cd/sqm



TEST NUMBER: P902218

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	2.2
10°-20°	388.5	6.2
20°-30°	570.9	9.2
30°-40°	663.1	10.6
40°-50°	662.3	10.6
50°-60°	577.5	9.3
60°-70°	426.9	6.8
70°-80°	241.5	3.9
80°-90°	66.3	1.1
90°-100°	55.3	0.9
100°-110°	175.8	2.8
110°-120°	300.9	4.8
120°-130°	395.7	6.3
130°-140°	444.2	7.1
140°-150°	435.6	7.0
150°-160°	365.4	5.9
160°-170°	242.3	3.9
170°-180°	84.7	1.4
0°-30°	1097.5	17.6
0°-40°	1760.6	28.2
0°-60°	3000.3	48.1
0°-90°	3735.0	59.9
90°-120°	532.1	8.5
90°-150°	1807.5	29.0
90°-180°	2500.0	40.1
0°-180°	6234.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	1	10	26	25	26	6
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	



TEST NUMBER: P902218

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4



TEST NUMBER: P902218

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3



TEST NUMBER: P902218
 CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.89	10.85	10.76	11.74	12.86	9.45	10.40	10.31	11.29	12.41
	3H	11.55	12.41	12.43	13.31	14.46	11.06	11.92	11.94	12.82	13.97
	4H	12.14	12.95	13.04	13.86	15.02	11.65	12.46	12.54	13.36	14.52
	6H	12.54	13.29	13.45	14.20	15.37	12.04	12.79	12.95	13.70	14.87
	8H	12.65	13.36	13.56	14.29	15.46	12.15	12.86	13.06	13.79	14.96
	12H	12.70	13.38	13.62	14.30	15.50	12.19	12.87	13.11	13.79	14.99
4H	2H	10.36	11.17	11.26	12.08	13.23	10.00	10.82	10.90	11.72	12.88
	3H	12.23	12.91	13.14	13.84	15.01	11.82	12.50	12.73	13.43	14.61
	4H	12.94	13.56	13.86	14.49	15.69	12.52	13.14	13.44	14.07	15.27
	6H	13.46	13.99	14.39	14.95	16.15	13.03	13.56	13.96	14.52	15.72
	8H	13.61	14.11	14.55	15.06	16.27	13.17	13.67	14.11	14.62	15.83
	12H	13.68	14.13	14.64	15.10	16.32	13.24	13.69	14.19	14.65	15.87
8H	4H	13.14	13.64	14.08	14.59	15.80	12.77	13.27	13.70	14.21	15.43
	6H	13.77	14.19	14.74	15.18	16.39	13.39	13.80	14.35	14.79	16.00
	8H	13.99	14.36	14.96	15.34	16.57	13.60	13.96	14.57	14.94	16.17
	12H	14.12	14.45	15.10	15.42	16.70	13.71	14.03	14.69	15.01	16.29
12H	4H	13.13	13.58	14.09	14.55	15.77	12.76	13.21	13.72	14.18	15.40
	6H	13.80	14.17	14.77	15.15	16.38	13.43	13.79	14.40	14.77	16.00
	8H	14.04	14.37	15.02	15.34	16.62	13.66	13.99	14.64	14.96	16.24