

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918661

Luminaire Tested: DFN2DIP-4P4F0-030D070US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918661
REPORT IS A COMBINATION OF REPORTS P900648 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-030D070US935-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8162.2 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918661
CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918661

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23				23
2	85	78	72	67	75	70	65	61	55	51	49	41	39	37	28	27	26	20				20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22	17				17
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19	15				15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	23	20	18	17	13				13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12				12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10				10
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	13	12	9				9
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	9				9
10	44	33	26	22	40	30	24	20	24	20	16	19	15	13	13	11	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	693	693	693
5°	694	682	686
10°	687	669	664
15°	678	647	630
20°	665	616	588
25°	652	583	547
30°	635	548	495
35°	618	510	450
40°	601	471	398
45°	581	428	350
50°	561	385	304
55°	539	338	260
60°	515	290	214
65°	486	240	193
70°	452	194	175
75°	408	172	160
80°	345	145	139
85°	241	98	106

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1049 cd/sqm



TEST NUMBER: P918661

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	1.2
10°-20°	274.7	3.4
20°-30°	385.6	4.7
30°-40°	420.3	5.1
40°-50°	386.3	4.7
50°-60°	303.4	3.7
60°-70°	197.5	2.4
70°-80°	101.7	1.2
80°-90°	29.5	0.4
90°-100°	67.1	0.8
100°-110°	250.0	3.1
110°-120°	663.1	8.1
120°-130°	1099.8	13.5
130°-140°	1168.3	14.3
140°-150°	1085.8	13.3
150°-160°	872.9	10.7
160°-170°	562.5	6.9
170°-180°	193.6	2.4
0°-30°	760.3	9.3
0°-40°	1180.7	14.5
0°-60°	1870.4	22.9
0°-90°	2199.1	26.9
90°-120°	980.2	12.0
90°-150°	4334.1	53.1
90°-180°	5963.0	73.1
0°-180°	8162.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1068	1063	1050	1059	1056	101
15°	1015	1005	972	954	944	286
25°	922	891	827	787	773	424
35°	794	745	660	599	578	497
45°	649	584	483	414	391	501
55°	494	418	314	256	238	441
65°	333	255	168	135	132	330
75°	178	110	77	70	70	188
85°	42	21	18	18	18	48
90°	1	18	29	37	40	8
95°	96	47	57	65	63	113
105°	448	492	90	106	112	478
115°	846	871	908	227	121	833
125°	1196	1216	1244	1254	1258	1067
135°	1481	1504	1517	1532	1529	1144
145°	1718	1716	1741	1751	1744	1074
155°	1891	1878	1896	1904	1893	872
165°	1993	1984	1988	1999	1988	563
175°	2038	2028	2031	2041	2027	194
180°	2034	2034	2034	2034	2034	



TEST NUMBER: P918661

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.6	1067.6	1067.6	1067.6	1067.6
2.5°	1072.4	1067.6	1056.9	1066.6	1064.7
5°	1067.6	1062.7	1050.2	1058.9	1055.9
7.5°	1058.9	1053.1	1039.6	1043.4	1038.5
10°	1047.2	1040.5	1021.2	1018.2	1012.5
12.5°	1032.8	1024.1	998.0	992.2	981.5
15°	1015.4	1004.7	971.9	953.6	943.9
17.5°	995.1	979.6	939.0	917.8	902.3
20°	971.9	952.5	904.2	880.2	858.8
22.5°	946.8	924.5	868.5	835.7	821.2
25°	921.7	890.7	827.0	787.4	772.8
27.5°	891.7	858.8	788.3	743.0	720.7
30°	859.9	823.1	745.8	696.6	670.5
32.5°	828.9	784.5	705.3	647.3	623.1
35°	794.2	744.8	659.9	599.0	577.7
37.5°	760.3	707.1	617.3	550.6	526.6
40°	724.6	666.7	572.9	504.3	479.2
42.5°	687.9	626.1	528.5	456.9	432.8
45°	649.3	584.4	483.1	414.4	391.2
47.5°	612.5	544.0	439.6	370.9	349.7
50°	572.0	503.3	397.1	330.4	310.1
52.5°	532.3	459.9	356.5	292.7	274.4
55°	493.6	418.3	313.9	256.1	237.7
57.5°	454.1	376.8	276.4	222.2	206.7
60°	413.5	336.2	236.7	187.4	172.0
62.5°	373.9	296.6	202.9	156.5	148.9
65°	333.3	255.0	168.1	135.3	132.3
67.5°	294.7	216.4	135.3	118.8	115.9
70°	254.1	178.7	112.0	102.4	98.5
72.5°	215.4	143.9	93.7	86.0	84.0
75°	177.7	110.1	77.3	70.5	69.6
77.5°	140.1	78.2	60.9	57.0	55.0
80°	105.3	56.1	46.3	42.5	42.5
82.5°	73.4	37.7	31.9	30.0	30.0
85°	41.5	21.2	18.3	18.3	18.3
87.5°	15.5	7.7	7.7	6.8	6.8
90°	1.4	17.7	29.4	36.9	39.7
92.5°	36.9	30.9	35.3	38.3	39.7
95°	95.6	47.0	57.3	64.8	63.3
97.5°	172.1	51.6	75.0	79.6	80.9
100°	260.6	58.9	83.9	95.6	98.6
102.5°	357.6	354.8	86.9	103.0	107.5
105°	447.5	491.6	89.8	105.9	111.8
107.5°	551.9	588.7	92.8	108.9	114.9
110°	652.1	682.9	257.6	110.5	116.2



TEST NUMBER: P918661

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	746.3	772.7	747.7	113.2	117.8
115°	846.3	871.2	908.1	226.7	120.8
117.5°	933.1	962.5	987.7	777.1	391.5
120°	1030.3	1052.3	1078.9	1096.6	897.8
122.5°	1112.6	1136.2	1165.8	1174.5	1176.0
125°	1196.5	1215.7	1243.7	1254.0	1258.3
127.5°	1273.1	1293.6	1315.9	1330.6	1332.0
130°	1345.2	1368.8	1384.9	1401.2	1399.8
132.5°	1418.8	1438.0	1454.1	1467.4	1466.0
135°	1480.7	1504.2	1517.4	1532.2	1529.3
137.5°	1545.3	1563.1	1577.9	1592.6	1588.2
140°	1608.6	1620.5	1636.6	1649.8	1642.5
142.5°	1661.7	1672.1	1691.1	1702.8	1695.5
145°	1717.7	1716.1	1741.1	1751.4	1744.1
147.5°	1766.1	1761.8	1786.7	1794.1	1788.3
150°	1813.3	1803.0	1826.6	1835.3	1828.0
152.5°	1853.0	1841.2	1863.3	1872.2	1861.9
155°	1891.3	1878.1	1895.7	1904.5	1892.8
157.5°	1922.2	1910.5	1923.7	1934.1	1922.2
160°	1948.8	1939.8	1948.8	1957.5	1947.1
162.5°	1972.2	1963.4	1970.7	1981.1	1967.8
165°	1992.8	1984.1	1988.4	1998.7	1988.4
167.5°	2009.1	2000.1	2004.7	2015.0	2001.7
170°	2022.3	2013.4	2016.4	2026.7	2013.4
172.5°	2031.1	2022.3	2025.3	2035.6	2022.3
175°	2038.4	2028.1	2031.1	2041.3	2026.7
177.5°	2041.3	2031.1	2032.6	2043.0	2029.6
180°	2034.0	2034.0	2034.0	2034.0	2034.0



TEST NUMBER: P918661
 CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.22	3.89	4.36	5.02	6.58	0.00	0.00	0.32	0.98	2.54
	3H	4.89	5.49	6.04	6.62	8.21	0.36	0.96	1.50	2.09	3.67
	4H	5.49	6.07	6.65	7.20	8.79	0.80	1.37	1.96	2.50	4.09
	6H	5.91	6.44	7.08	7.57	9.17	1.12	1.64	2.28	2.78	4.38
	8H	6.04	6.54	7.20	7.69	9.28	1.20	1.70	2.37	2.85	4.44
	12H	6.10	6.57	7.26	7.71	9.33	1.24	1.71	2.41	2.86	4.47
4H	2H	3.22	3.79	4.38	4.92	6.51	0.00	0.33	0.92	1.46	3.05
	3H	5.04	5.51	6.21	6.67	8.27	1.10	1.57	2.26	2.73	4.33
	4H	5.73	6.17	6.90	7.31	8.93	1.64	2.08	2.81	3.22	4.84
	6H	6.24	6.61	7.41	7.78	9.39	2.05	2.42	3.22	3.59	5.20
	8H	6.42	6.76	7.59	7.93	9.55	2.18	2.53	3.35	3.69	5.32
	12H	6.51	6.82	7.70	8.00	9.63	2.24	2.55	3.43	3.73	5.36
8H	4H	5.69	6.03	6.86	7.20	8.82	1.91	2.26	3.08	3.42	5.05
	6H	6.25	6.54	7.44	7.74	9.37	2.43	2.71	3.62	3.92	5.54
	8H	6.47	6.72	7.67	7.90	9.55	2.62	2.87	3.82	4.05	5.69
	12H	6.61	6.83	7.81	8.01	9.68	2.73	2.95	3.93	4.13	5.81
12H	4H	5.63	5.95	6.82	7.12	8.75	1.91	2.23	3.10	3.40	5.03
	6H	6.23	6.48	7.42	7.66	9.30	2.48	2.73	3.67	3.91	5.55
	8H	6.44	6.66	7.65	7.84	9.52	2.68	2.90	3.88	4.08	5.76