

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918746

Luminaire Tested: DFN2DIP-4P4F0-070D050US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918746
REPORT IS A COMBINATION OF REPORTS P899111 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D050US935-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9776.6 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 114.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918746

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918746

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89		77	77	77		66
1	100	96	92	88	94	90	86	83	79	76	74		68	66	65		59
2	91	84	77	72	85	79	73	68	69	65	61		60	57	54		52
3	83	74	66	60	78	69	63	57	61	56	51		53	49	46		46
4	76	65	57	51	71	61	54	49	54	48	44		47	43	39		41
5	70	58	50	44	65	55	47	42	48	42	38		42	38	34		37
6	65	52	44	38	60	49	42	36	44	38	33		38	34	30		33
7	60	47	39	33	56	45	37	32	40	34	29		35	30	26		31
8	56	43	35	30	52	41	33	28	36	30	26		32	27	24		28
9	52	39	32	27	48	37	30	25	33	27	23		30	25	21		26
10	48	36	29	24	45	34	28	23	31	25	21		27	23	19		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1521	1521	1521
5°	1524	1501	1511
10°	1512	1481	1491
15°	1490	1457	1460
20°	1460	1424	1427
25°	1430	1384	1390
30°	1393	1346	1343
35°	1357	1302	1292
40°	1314	1258	1244
45°	1270	1214	1195
50°	1223	1167	1139
55°	1173	1113	1087
60°	1117	1049	1027
65°	1056	983	957
70°	978	902	882
75°	870	805	813
80°	740	683	680
85°	537	469	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1270 cd/sqm

TEST NUMBER: P918746

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.7	2.3
10°-20°	621.0	6.4
20°-30°	912.7	9.3
30°-40°	1060.0	10.8
40°-50°	1058.7	10.8
50°-60°	923.2	9.4
60°-70°	682.4	7.0
70°-80°	386.1	3.9
80°-90°	105.8	1.1
90°-100°	84.2	0.9
100°-110°	267.7	2.7
110°-120°	458.1	4.7
120°-130°	602.5	6.2
130°-140°	676.3	6.9
140°-150°	663.1	6.8
150°-160°	556.3	5.7
160°-170°	368.9	3.8
170°-180°	128.9	1.3
0°-30°	1754.4	17.9
0°-40°	2814.4	28.8
0°-60°	4796.3	49.1
0°-90°	5970.6	61.1
90°-120°	810.0	8.3
90°-150°	2751.9	28.1
90°-180°	3806.0	38.9
0°-180°	9776.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	1	15	40	38	39	9
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P918746

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8

TEST NUMBER: P918746

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5

TEST NUMBER: P918746

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.71	10.68	10.57	11.56	12.66	9.27	10.24	10.12	11.11	12.22
	3H	11.38	12.26	12.25	13.14	14.27	10.89	11.77	11.76	12.65	13.78
	4H	11.98	12.80	12.87	13.70	14.84	11.49	12.31	12.37	13.20	14.34
	6H	12.39	13.15	13.29	14.05	15.20	11.89	12.65	12.79	13.55	14.70
	8H	12.50	13.22	13.41	14.14	15.30	12.00	12.72	12.90	13.64	14.79
	12H	12.56	13.24	13.47	14.16	15.34	12.05	12.74	12.96	13.65	14.83
4H	2H	10.19	11.01	11.08	11.90	13.04	9.83	10.65	10.72	11.55	12.69
	3H	12.07	12.76	12.97	13.68	14.84	11.66	12.35	12.56	13.27	14.43
	4H	12.79	13.42	13.70	14.34	15.52	12.37	12.99	13.28	13.92	15.10
	6H	13.32	13.86	14.24	14.80	15.99	12.89	13.43	13.81	14.37	15.55
	8H	13.47	13.98	14.40	14.92	16.11	13.04	13.54	13.96	14.48	15.68
	12H	13.55	14.01	14.50	14.97	16.17	13.11	13.56	14.05	14.52	15.72
8H	4H	13.00	13.50	13.93	14.44	15.64	12.62	13.13	13.55	14.07	15.26
	6H	13.64	14.06	14.59	15.04	16.23	13.26	13.68	14.21	14.66	15.85
	8H	13.87	14.24	14.83	15.21	16.42	13.47	13.84	14.44	14.81	16.03
	12H	14.01	14.33	14.97	15.30	16.56	13.60	13.92	14.56	14.89	16.15
12H	4H	12.99	13.45	13.94	14.40	15.60	12.62	13.08	13.57	14.03	15.24
	6H	13.67	14.04	14.64	15.01	16.23	13.30	13.67	14.26	14.64	15.85
	8H	13.92	14.25	14.89	15.21	16.47	13.54	13.87	14.51	14.83	16.09