

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918768

Luminaire Tested: DFN2DIP-4P4F0-080D040US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918768
REPORT IS A COMBINATION OF REPORTS P899102 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D040US935-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8902.7 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918768

CATALOG NUMBER: DFN2DIP-4P4F0-080D040US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918768

CATALOG NUMBER: DFN2DIP-4P4F0-080D040US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1847	1847	1847
5°	1850	1818	1830
10°	1832	1783	1771
15°	1807	1725	1679
20°	1773	1644	1567
25°	1739	1553	1459
30°	1694	1461	1321
35°	1649	1361	1199
40°	1603	1257	1060
45°	1550	1142	934
50°	1496	1026	811
55°	1438	902	693
60°	1372	772	571
65°	1296	640	514
70°	1204	517	467
75°	1088	457	426
80°	921	386	372
85°	643	261	284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1550 cd/sqm

TEST NUMBER: P918768

CATALOG NUMBER: DFN2DIP-4P4F0-080D040US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.8	3.0
10°-20°	732.4	8.2
20°-30°	1028.3	11.6
30°-40°	1120.9	12.6
40°-50°	1030.3	11.6
50°-60°	809.1	9.1
60°-70°	526.6	5.9
70°-80°	271.1	3.0
80°-90°	72.3	0.8
90°-100°	67.4	0.8
100°-110°	214.2	2.4
110°-120°	366.5	4.1
120°-130°	482.0	5.4
130°-140°	541.0	6.1
140°-150°	530.5	6.0
150°-160°	445.0	5.0
160°-170°	295.1	3.3
170°-180°	103.2	1.2
0°-30°	2027.6	22.8
0°-40°	3148.5	35.4
0°-60°	4987.8	56.0
0°-90°	5857.9	65.8
90°-120°	648.0	7.3
90°-150°	2201.5	24.7
90°-180°	3045.0	34.2
0°-180°	8902.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2847	2847	2847	2847	2847	
5°	2847	2834	2800	2824	2816	270
15°	2708	2679	2592	2543	2517	763
25°	2458	2375	2205	2100	2061	1130
35°	2118	1986	1760	1597	1540	1326
45°	1731	1559	1288	1105	1043	1337
55°	1316	1116	837	683	634	1176
65°	889	680	448	361	353	881
75°	474	294	206	188	186	501
85°	111	57	49	49	49	127
90°	1	12	32	30	31	9
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	

TEST NUMBER: P918768

CATALOG NUMBER: DFN2DIP-4P4F0-080D040US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2846.8	2846.8	2846.8	2846.8	2846.8
2.5°	2859.6	2846.8	2818.4	2844.3	2839.1
5°	2846.8	2834.0	2800.3	2823.6	2815.9
7.5°	2823.6	2808.2	2772.2	2782.3	2769.4
10°	2792.6	2774.7	2723.3	2715.3	2700.0
12.5°	2754.2	2730.9	2661.2	2645.8	2617.4
15°	2707.7	2679.3	2591.8	2542.9	2517.1
17.5°	2653.5	2612.3	2504.0	2447.5	2406.1
20°	2591.8	2540.1	2411.4	2347.2	2290.3
22.5°	2524.8	2465.5	2316.0	2228.5	2189.9
25°	2457.8	2375.3	2205.3	2099.8	2061.0
27.5°	2378.0	2290.3	2102.2	1981.2	1921.8
30°	2293.0	2194.9	1988.8	1857.6	1787.9
32.5°	2210.4	2091.9	1880.8	1726.1	1661.6
35°	2117.8	1986.3	1759.7	1597.4	1540.5
37.5°	2027.6	1885.8	1646.3	1468.3	1404.1
40°	1932.3	1777.8	1527.7	1344.8	1277.8
42.5°	1834.4	1669.6	1409.3	1218.6	1154.3
45°	1731.3	1558.6	1288.2	1105.1	1043.4
47.5°	1633.5	1450.6	1172.3	989.2	932.6
50°	1525.2	1342.4	1058.9	881.0	827.1
52.5°	1419.4	1226.1	950.6	780.7	731.8
55°	1316.4	1115.5	837.2	682.8	633.9
57.5°	1210.9	1004.8	736.9	592.6	551.3
60°	1102.6	896.6	631.1	499.9	458.7
62.5°	997.1	791.0	541.0	417.4	396.9
65°	888.9	680.0	448.2	360.8	352.8
67.5°	785.8	577.0	360.8	316.8	309.2
70°	677.6	476.7	298.8	273.0	262.7
72.5°	574.5	383.7	249.9	229.4	224.1
75°	474.0	293.6	206.1	188.0	185.6
77.5°	373.7	208.5	162.4	152.0	146.8
80°	280.7	149.6	123.6	113.4	113.4
82.5°	195.7	100.6	85.0	79.8	79.8
85°	110.7	56.6	48.9	48.9	48.9
87.5°	41.2	20.5	20.5	18.1	18.1
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1

TEST NUMBER: P918768

CATALOG NUMBER: DFN2DIP-4P4F0-080D040US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2

TEST NUMBER: P918768

CATALOG NUMBER: DFN2DIP-4P4F0-080D040US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.66	11.64	11.47	12.47	13.50	6.62	7.60	7.43	8.43	9.46
	3H	12.35	13.23	13.18	14.07	15.13	7.82	8.70	8.65	9.54	10.60
	4H	12.97	13.80	13.82	14.65	15.72	8.28	9.10	9.12	9.95	11.02
	6H	13.41	14.17	14.26	15.02	16.10	8.61	9.37	9.47	10.23	11.31
	8H	13.54	14.26	14.41	15.14	16.22	8.70	9.43	9.57	10.30	11.38
	12H	13.61	14.30	14.48	15.17	16.27	8.75	9.44	9.62	10.31	11.42
4H	2H	10.69	11.52	11.54	12.37	13.44	7.23	8.06	8.09	8.91	9.98
	3H	12.54	13.23	13.40	14.11	15.20	8.60	9.29	9.46	10.17	11.25
	4H	13.25	13.87	14.12	14.75	15.86	9.16	9.78	10.03	10.66	11.77
	6H	13.77	14.31	14.66	15.22	16.33	9.58	10.12	10.47	11.03	12.14
	8H	13.96	14.46	14.85	15.36	16.48	9.72	10.22	10.61	11.12	12.24
	12H	14.06	14.51	14.97	15.43	16.56	9.79	10.24	10.70	11.16	12.29
8H	4H	13.22	13.73	14.12	14.62	15.75	9.45	9.95	10.34	10.85	11.98
	6H	13.80	14.22	14.72	15.16	16.28	9.98	10.39	10.90	11.33	12.46
	8H	14.02	14.39	14.95	15.32	16.47	10.17	10.54	11.10	11.47	12.61
	12H	14.17	14.50	15.10	15.42	16.62	10.30	10.62	11.23	11.55	12.74
12H	4H	13.18	13.63	14.09	14.55	15.68	9.46	9.91	10.37	10.83	11.96
	6H	13.78	14.15	14.71	15.08	16.22	10.03	10.40	10.96	11.33	12.47
	8H	14.01	14.33	14.94	15.26	16.45	10.25	10.57	11.18	11.50	12.69