

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918773

Luminaire Tested: DFN2DIP-4P4F0-080D050US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918773
REPORT IS A COMBINATION OF REPORTS P900634 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D050US935-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open
No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10116.8 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 126
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918773

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918773

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	92	84	79	74	85	79	74	69	69	65	62	59	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	41
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	27	23	20
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1847	1847	1847
5°	1850	1818	1830
10°	1832	1783	1771
15°	1807	1725	1679
20°	1773	1644	1567
25°	1739	1553	1459
30°	1694	1461	1321
35°	1649	1361	1199
40°	1603	1257	1060
45°	1550	1142	934
50°	1496	1026	811
55°	1438	902	693
60°	1372	772	571
65°	1296	640	514
70°	1204	517	467
75°	1088	457	426
80°	921	386	372
85°	643	261	284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1550 cd/sqm

TEST NUMBER: P918773

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.8	2.6
10°-20°	732.4	7.2
20°-30°	1028.3	10.2
30°-40°	1120.9	11.1
40°-50°	1030.3	10.2
50°-60°	809.1	8.0
60°-70°	526.6	5.2
70°-80°	271.1	2.7
80°-90°	71.8	0.7
90°-100°	47.9	0.5
100°-110°	178.6	1.8
110°-120°	473.7	4.7
120°-130°	785.6	7.8
130°-140°	834.5	8.2
140°-150°	775.6	7.7
150°-160°	623.5	6.2
160°-170°	401.8	4.0
170°-180°	138.3	1.4
0°-30°	2027.6	20.0
0°-40°	3148.5	31.1
0°-60°	4987.8	49.3
0°-90°	5857.4	57.9
90°-120°	700.2	6.9
90°-150°	3095.8	30.6
90°-180°	4259.0	42.1
0°-180°	10116.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2847	2847	2847	2847	2847	
5°	2847	2834	2800	2824	2816	270
15°	2708	2679	2592	2543	2517	763
25°	2458	2375	2205	2100	2061	1130
35°	2118	1986	1760	1597	1540	1326
45°	1731	1559	1288	1105	1043	1337
55°	1316	1116	837	683	634	1176
65°	889	680	448	361	353	881
75°	474	294	206	188	186	501
85°	111	57	49	49	49	127
90°	1	13	21	26	28	10
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	

TEST NUMBER: P918773

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2846.8	2846.8	2846.8	2846.8	2846.8
2.5°	2859.6	2846.8	2818.4	2844.3	2839.1
5°	2846.8	2834.0	2800.3	2823.6	2815.9
7.5°	2823.6	2808.2	2772.2	2782.3	2769.4
10°	2792.6	2774.7	2723.3	2715.3	2700.0
12.5°	2754.2	2730.9	2661.2	2645.8	2617.4
15°	2707.7	2679.3	2591.8	2542.9	2517.1
17.5°	2653.5	2612.3	2504.0	2447.5	2406.1
20°	2591.8	2540.1	2411.4	2347.2	2290.3
22.5°	2524.8	2465.5	2316.0	2228.5	2189.9
25°	2457.8	2375.3	2205.3	2099.8	2061.0
27.5°	2378.0	2290.3	2102.2	1981.2	1921.8
30°	2293.0	2194.9	1988.8	1857.6	1787.9
32.5°	2210.4	2091.9	1880.8	1726.1	1661.6
35°	2117.8	1986.3	1759.7	1597.4	1540.5
37.5°	2027.6	1885.8	1646.3	1468.3	1404.1
40°	1932.3	1777.8	1527.7	1344.8	1277.8
42.5°	1834.4	1669.6	1409.3	1218.6	1154.3
45°	1731.3	1558.6	1288.2	1105.1	1043.4
47.5°	1633.5	1450.6	1172.3	989.2	932.6
50°	1525.2	1342.4	1058.9	881.0	827.1
52.5°	1419.4	1226.1	950.6	780.7	731.8
55°	1316.4	1115.5	837.2	682.8	633.9
57.5°	1210.9	1004.8	736.9	592.6	551.3
60°	1102.6	896.6	631.1	499.9	458.7
62.5°	997.1	791.0	541.0	417.4	396.9
65°	888.9	680.0	448.2	360.8	352.8
67.5°	785.8	577.0	360.8	316.8	309.2
70°	677.6	476.7	298.8	273.0	262.7
72.5°	574.5	383.7	249.9	229.4	224.1
75°	474.0	293.6	206.1	188.0	185.6
77.5°	373.7	208.5	162.4	152.0	146.8
80°	280.7	149.6	123.6	113.4	113.4
82.5°	195.7	100.6	85.0	79.8	79.8
85°	110.7	56.6	48.9	48.9	48.9
87.5°	41.2	20.5	20.5	18.1	18.1
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0



TEST NUMBER: P918773

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8

TEST NUMBER: P918773

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.00	10.90	10.90	11.81	12.97	5.97	6.86	6.86	7.77	8.93
	3H	11.69	12.50	12.60	13.42	14.60	7.16	7.96	8.07	8.88	10.06
	4H	12.31	13.07	13.23	13.99	15.18	7.62	8.37	8.54	9.30	10.49
	6H	12.74	13.44	13.67	14.37	15.57	7.94	8.64	8.87	9.57	10.77
	8H	12.87	13.53	13.81	14.48	15.68	8.04	8.70	8.97	9.65	10.85
	12H	12.94	13.57	13.88	14.51	15.74	8.08	8.71	9.03	9.65	10.88
4H	2H	10.03	10.79	10.96	11.71	12.91	6.57	7.33	7.50	8.25	9.45
	3H	11.87	12.50	12.81	13.46	14.66	7.93	8.56	8.87	9.52	10.72
	4H	12.57	13.15	13.52	14.10	15.33	8.48	9.06	9.43	10.01	11.24
	6H	13.10	13.59	14.06	14.56	15.80	8.91	9.40	9.87	10.38	11.61
	8H	13.28	13.74	14.24	14.70	15.95	9.04	9.50	10.00	10.47	11.71
	12H	13.38	13.79	14.36	14.78	16.03	9.11	9.52	10.09	10.51	11.76
8H	4H	12.55	13.01	13.51	13.97	15.22	8.77	9.23	9.73	10.20	11.44
	6H	13.12	13.50	14.11	14.51	15.75	9.30	9.68	10.28	10.68	11.93
	8H	13.34	13.68	14.34	14.68	15.94	9.49	9.82	10.48	10.82	12.08
	12H	13.49	13.78	14.49	14.77	16.08	9.61	9.91	10.61	10.90	12.21
12H	4H	12.50	12.92	13.48	13.90	15.15	8.78	9.20	9.76	10.18	11.43
	6H	13.10	13.43	14.09	14.43	15.69	9.35	9.68	10.34	10.68	11.94
	8H	13.32	13.62	14.32	14.61	15.92	9.56	9.86	10.56	10.85	12.16

END OF REPORT