

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907646

Luminaire Tested: DFN2DIP-4P3F0-020D060US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907646
REPORT IS A COMBINATION OF REPORTS P899069 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D060US840-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7361.9 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 62.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907646

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907646

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35			27
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30			23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25			19
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21			16
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18			14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16			12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14			11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12			9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11			8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10			8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	896	896	896
5°	896	883	889
10°	889	870	876
15°	875	855	857
20°	857	835	838
25°	839	810	815
30°	816	788	787
35°	795	761	756
40°	768	734	728
45°	742	707	698
50°	713	678	664
55°	683	645	633
60°	649	606	597
65°	612	566	554
70°	564	516	509
75°	498	457	466
80°	419	381	385
85°	295	253	253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1919 cd/sqm

TEST NUMBER: P907646

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.0	1.0
10°-20°	208.1	2.8
20°-30°	305.8	4.2
30°-40°	355.2	4.8
40°-50°	354.8	4.8
50°-60°	309.4	4.2
60°-70°	228.7	3.1
70°-80°	129.4	1.8
80°-90°	39.6	0.5
90°-100°	118.6	1.6
100°-110°	376.8	5.1
110°-120°	644.8	8.8
120°-130°	848.0	11.5
130°-140°	951.8	12.9
140°-150°	933.4	12.7
150°-160°	783.0	10.6
160°-170°	519.2	7.1
170°-180°	181.5	2.5
0°-30°	587.9	8.0
0°-40°	943.2	12.8
0°-60°	1607.3	21.8
0°-90°	2005.0	27.2
90°-120°	1140.1	15.5
90°-150°	3873.3	52.6
90°-180°	5357.0	72.8
0°-180°	7361.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	786	783	775	781	779	75
15°	748	744	734	737	733	211
25°	677	671	658	660	658	312
35°	584	577	564	560	556	365
45°	475	470	459	450	447	367
55°	360	355	346	337	333	322
65°	243	238	231	224	220	240
75°	127	126	122	117	119	135
85°	31	30	30	27	26	35
90°	2	21	57	53	55	7
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	

TEST NUMBER: P907646

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	785.9	785.9	785.9	785.9	785.9
2.5°	790.4	786.7	778.3	785.9	784.5
5°	785.9	782.9	774.6	780.6	779.1
7.5°	780.6	776.1	767.8	773.9	772.3
10°	772.3	767.1	758.0	764.0	761.7
12.5°	760.9	756.5	747.4	751.1	749.6
15°	748.1	743.7	733.8	736.8	733.1
17.5°	732.3	727.8	717.9	721.6	717.9
20°	714.9	710.3	699.7	702.1	699.0
22.5°	697.5	690.7	680.9	680.9	679.3
25°	677.1	671.1	658.2	659.6	658.2
27.5°	654.4	649.1	639.3	637.1	633.3
30°	631.8	625.7	614.4	612.2	609.0
32.5°	607.5	603.1	591.0	586.4	583.4
35°	584.2	576.6	564.5	560.0	556.1
37.5°	557.7	550.9	538.8	533.5	529.7
40°	530.5	524.4	512.3	505.6	502.5
42.5°	504.0	498.0	485.9	478.4	473.8
45°	475.3	470.1	458.7	450.4	447.4
47.5°	447.4	442.1	430.0	421.6	417.2
50°	417.9	414.1	403.5	392.9	389.2
52.5°	389.2	383.8	374.1	365.8	360.5
55°	359.7	355.2	346.1	337.1	333.3
57.5°	330.2	326.5	316.6	307.6	304.5
60°	300.7	297.8	287.2	278.8	276.6
62.5°	272.1	266.7	259.2	251.7	248.6
65°	242.6	238.0	230.6	223.7	219.9
67.5°	212.4	208.5	201.8	196.5	193.5
70°	184.4	181.4	174.5	169.3	166.3
72.5°	155.7	152.7	148.9	143.6	141.4
75°	126.9	125.5	121.6	117.1	118.7
77.5°	101.3	98.3	96.6	94.4	92.2
80°	75.6	74.8	73.3	71.0	69.5
82.5°	51.4	51.4	50.7	47.7	47.7
85°	30.9	30.2	29.5	27.2	26.5
87.5°	13.6	12.1	10.6	8.4	7.6
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0

TEST NUMBER: P907646

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US840-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3

TEST NUMBER: P907646

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US840-FLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.24	4.93	5.38	6.06	7.62	3.80	4.49	4.93	5.61	7.17
	3H	5.89	6.50	7.03	7.63	9.21	5.40	6.01	6.54	7.15	8.72
	4H	6.46	7.05	7.61	8.18	9.76	5.97	6.56	7.12	7.69	9.27
	6H	6.85	7.39	8.01	8.52	10.12	6.35	6.89	7.51	8.02	9.62
	8H	6.95	7.46	8.11	8.61	10.20	6.45	6.96	7.61	8.11	9.70
	12H	6.99	7.48	8.15	8.62	10.23	6.48	6.97	7.64	8.11	9.72
4H	2H	4.68	5.27	5.84	6.40	7.98	4.33	4.91	5.48	6.04	7.63
	3H	6.53	7.01	7.69	8.17	9.77	6.12	6.61	7.28	7.76	9.36
	4H	7.23	7.68	8.39	8.82	10.44	6.81	7.26	7.97	8.40	10.02
	6H	7.73	8.12	8.90	9.28	10.89	7.30	7.68	8.47	8.85	10.46
	8H	7.87	8.23	9.04	9.39	11.01	7.44	7.80	8.60	8.96	10.58
	12H	7.94	8.26	9.12	9.43	11.06	7.49	7.81	8.67	8.98	10.61
8H	4H	7.41	7.77	8.57	8.93	10.55	7.03	7.39	8.20	8.55	10.17
	6H	8.03	8.32	9.21	9.52	11.14	7.64	7.94	8.83	9.14	10.76
	8H	8.24	8.50	9.43	9.68	11.32	7.85	8.11	9.04	9.29	10.93
	12H	8.36	8.59	9.56	9.77	11.44	7.95	8.18	9.15	9.36	11.03
12H	4H	7.38	7.71	8.57	8.88	10.51	7.01	7.34	8.20	8.51	10.14
	6H	8.05	8.31	9.24	9.49	11.13	7.68	7.94	8.87	9.12	10.76
	8H	8.28	8.51	9.48	9.69	11.36	7.90	8.13	9.10	9.31	10.98

END OF REPORT