

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907652

Luminaire Tested: DFN2DIP-4P3F0-030D020US840-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907652  
REPORT IS A COMBINATION OF REPORTS P899032 AND P895917  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-030D020US840-RLLFLL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4362.6 lumens  
Efficiency: N/A  
Efficacy: 105.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 41.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907652  
CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P907652

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51			
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44			
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38			
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26			
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19			
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1427	1427	1427
5°	1428	1403	1413
10°	1413	1375	1366
15°	1393	1328	1295
20°	1366	1265	1207
25°	1339	1194	1123
30°	1303	1121	1016
35°	1267	1043	922
40°	1231	963	814
45°	1189	873	716
50°	1145	783	621
55°	1099	686	529
60°	1046	586	435
65°	985	484	391
70°	911	389	353
75°	818	341	320
80°	684	283	276
85°	464	184	205

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1189 cd/sqm



TEST NUMBER: P907652

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.4	2.7
10°-20°	322.1	7.4
20°-30°	452.3	10.4
30°-40°	493.0	11.3
40°-50°	453.1	10.4
50°-60°	355.9	8.2
60°-70°	231.6	5.3
70°-80°	119.2	2.7
80°-90°	32.2	0.7
90°-100°	39.5	0.9
100°-110°	125.6	2.9
110°-120°	214.9	4.9
120°-130°	282.7	6.5
130°-140°	317.3	7.3
140°-150°	311.1	7.1
150°-160°	261.0	6.0
160°-170°	173.1	4.0
170°-180°	60.5	1.4
0°-30°	891.8	20.4
0°-40°	1384.8	31.7
0°-60°	2193.8	50.3
0°-90°	2576.9	59.1
90°-120°	380.0	8.7
90°-150°	1291.1	29.6
90°-180°	1786.0	40.9
0°-180°	4362.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	7	19	18	18	4
95°	28	34	34	34	34	31
105°	116	117	119	120	120	122
115°	216	219	218	217	216	213
125°	314	318	317	315	315	280
135°	406	412	413	412	411	314
145°	493	496	500	500	498	308
155°	563	565	566	569	568	259
165°	613	612	612	616	613	173
175°	638	636	635	639	636	61
180°	639	639	639	639	639	



TEST NUMBER: P907652

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.6	7.0	18.9	17.7	18.3
92.5°	11.9	16.2	16.8	17.4	17.4
95°	28.1	33.5	34.4	34.4	33.5
97.5°	46.8	51.8	53.9	53.9	53.9
100°	68.4	72.8	74.3	74.3	73.7
102.5°	91.1	94.3	96.4	97.0	96.4
105°	115.9	117.4	118.7	119.6	119.6
107.5°	140.6	142.9	142.9	143.3	140.6
110°	164.5	167.5	167.5	167.5	166.0



TEST NUMBER: P907652

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	190.3	193.5	193.0	191.4	190.3
115°	215.7	218.7	217.8	217.2	215.7
117.5°	241.0	245.2	242.5	241.0	239.3
120°	266.3	270.5	266.3	266.3	264.6
122.5°	289.4	294.8	292.2	290.6	289.4
125°	313.7	318.5	317.0	315.3	314.7
127.5°	337.4	343.4	341.2	338.9	337.4
130°	359.5	366.5	365.5	364.4	362.2
132.5°	384.4	389.8	390.1	387.5	385.9
135°	405.8	411.7	412.8	412.3	410.7
137.5°	429.6	434.4	435.5	435.1	432.7
140°	450.6	455.4	458.2	458.2	456.1
142.5°	472.2	477.0	478.6	479.1	477.0
145°	492.6	496.4	499.6	500.1	498.0
147.5°	510.9	515.7	518.1	519.0	516.8
150°	529.8	533.0	535.1	536.8	535.1
152.5°	546.5	549.8	552.5	554.6	552.5
155°	563.3	564.8	566.5	569.3	567.5
157.5°	577.7	578.9	579.9	583.7	581.0
160°	590.7	591.8	592.4	595.6	593.3
162.5°	602.6	602.6	603.1	606.8	604.1
165°	612.8	612.2	612.2	616.0	613.4
167.5°	622.0	620.3	620.3	624.1	621.5
170°	628.9	627.4	626.8	630.7	627.4
172.5°	633.8	632.2	631.7	635.5	632.2
175°	637.6	636.1	634.9	638.7	635.5
177.5°	639.7	638.2	637.0	640.3	637.0
180°	638.7	638.7	638.7	638.7	638.7



TEST NUMBER: P907652  
 CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.15	10.06	10.04	10.96	12.10	5.11	6.02	6.00	6.92	8.06
	3H	10.83	11.65	11.73	12.56	13.72	6.30	7.12	7.20	8.02	9.19
	4H	11.44	12.21	12.35	13.12	14.30	6.75	7.52	7.66	8.43	9.61
	6H	11.86	12.57	12.79	13.49	14.68	7.07	7.78	7.99	8.70	9.89
	8H	11.99	12.66	12.92	13.60	14.79	7.16	7.83	8.09	8.77	9.96
	12H	12.05	12.69	12.99	13.62	14.83	7.20	7.85	8.14	8.78	9.99
4H	2H	9.18	9.95	10.10	10.86	12.04	5.72	6.49	6.63	7.40	8.57
	3H	11.01	11.65	11.94	12.59	13.78	7.07	7.71	7.99	8.65	9.84
	4H	11.70	12.29	12.64	13.22	14.44	7.61	8.20	8.55	9.13	10.35
	6H	12.22	12.72	13.17	13.68	14.90	8.03	8.53	8.98	9.49	10.71
	8H	12.39	12.86	13.34	13.82	15.04	8.16	8.62	9.11	9.58	10.81
	12H	12.49	12.91	13.46	13.88	15.12	8.22	8.64	9.19	9.62	10.85
8H	4H	11.68	12.14	12.63	13.10	14.33	7.90	8.36	8.85	9.32	10.55
	6H	12.24	12.63	13.22	13.62	14.85	8.41	8.80	9.39	9.79	11.02
	8H	12.45	12.79	13.44	13.78	15.03	8.60	8.94	9.58	9.93	11.17
	12H	12.59	12.89	13.58	13.87	15.16	8.71	9.01	9.70	9.99	11.29
12H	4H	11.63	12.05	12.60	13.03	14.26	7.90	8.33	8.87	9.30	10.53
	6H	12.21	12.56	13.20	13.54	14.79	8.46	8.80	9.44	9.79	11.03
	8H	12.43	12.73	13.42	13.72	15.01	8.67	8.97	9.66	9.95	11.24