

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907655

Luminaire Tested: DFN2DIP-4P3F0-030D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907655
REPORT IS A COMBINATION OF REPORTS P900561 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D030US840-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5998.7 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 48.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907655

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907655

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1343	1343	1343
5°	1345	1324	1333
10°	1333	1305	1315
15°	1313	1283	1286
20°	1285	1252	1257
25°	1258	1215	1223
30°	1224	1181	1180
35°	1192	1141	1135
40°	1152	1101	1092
45°	1113	1060	1047
50°	1070	1017	996
55°	1025	968	949
60°	973	909	895
65°	918	849	832
70°	846	775	763
75°	748	686	699
80°	628	572	578
85°	443	379	378

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1113 cd/sqm

TEST NUMBER: P907655

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.8
10°-20°	312.2	5.2
20°-30°	458.8	7.6
30°-40°	532.8	8.9
40°-50°	532.2	8.9
50°-60°	464.1	7.7
60°-70°	343.1	5.7
70°-80°	194.1	3.2
80°-90°	53.0	0.9
90°-100°	33.7	0.6
100°-110°	125.7	2.1
110°-120°	333.3	5.6
120°-130°	552.9	9.2
130°-140°	587.3	9.8
140°-150°	545.8	9.1
150°-160°	438.8	7.3
160°-170°	282.8	4.7
170°-180°	97.3	1.6
0°-30°	881.9	14.7
0°-40°	1414.7	23.6
0°-60°	2411.0	40.2
0°-90°	3001.1	50.0
90°-120°	492.7	8.2
90°-150°	2178.7	36.3
90°-180°	2998.0	50.0
0°-180°	5998.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1179	1174	1162	1171	1169	112
15°	1122	1116	1101	1105	1100	316
25°	1016	1007	987	990	987	467
35°	876	865	847	840	834	547
45°	713	705	688	676	671	550
55°	540	533	519	506	500	482
65°	364	357	346	336	330	360
75°	190	188	182	176	178	203
85°	46	45	44	41	40	52
90°	1	9	15	19	20	6
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P907655

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	1178.8	1178.8	1178.8	1178.8
2.5°	1185.7	1180.0	1167.5	1178.8	1176.7
5°	1178.8	1174.4	1161.9	1170.9	1168.7
7.5°	1170.9	1164.2	1151.7	1160.8	1158.5
10°	1158.5	1150.5	1137.0	1146.0	1142.7
12.5°	1141.5	1134.7	1121.2	1126.7	1124.5
15°	1122.2	1115.5	1100.7	1105.2	1099.5
17.5°	1098.3	1091.7	1076.8	1082.5	1076.8
20°	1072.3	1065.5	1049.7	1053.0	1048.5
22.5°	1046.3	1036.1	1021.3	1021.3	1019.0
25°	1015.6	1006.6	987.3	989.6	987.3
27.5°	981.6	973.6	959.0	955.6	950.0
30°	947.7	938.6	921.6	918.2	913.6
32.5°	911.4	904.6	886.5	879.6	875.0
35°	876.3	864.9	846.8	839.9	834.2
37.5°	836.6	826.4	808.2	800.2	794.6
40°	795.8	786.7	768.5	758.4	753.9
42.5°	756.1	747.0	728.9	717.5	710.7
45°	713.1	705.1	688.0	675.6	671.1
47.5°	671.1	663.2	645.0	632.5	625.7
50°	626.8	621.2	605.3	589.5	583.8
52.5°	583.8	575.8	561.2	548.7	540.7
55°	539.7	532.8	519.2	505.6	500.0
57.5°	495.3	489.7	474.9	461.3	456.8
60°	451.1	446.7	430.8	418.3	415.0
62.5°	408.1	400.1	388.8	377.5	372.9
65°	364.0	357.1	345.8	335.6	329.9
67.5°	318.6	312.9	302.7	294.8	290.2
70°	276.6	272.1	261.9	253.9	249.4
72.5°	233.6	228.9	223.3	215.4	212.1
75°	190.4	188.2	182.5	175.7	178.0
77.5°	151.9	147.3	145.0	141.7	138.4
80°	113.4	112.2	109.9	106.5	104.3
82.5°	77.1	77.1	76.0	71.4	71.4
85°	46.5	45.3	44.2	40.8	39.7
87.5°	20.4	18.2	15.9	12.5	11.3
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5

TEST NUMBER: P907655

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US840-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5

TEST NUMBER: P907655

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.27	9.13	9.22	10.10	11.37	7.82	8.68	8.78	9.66	10.93
	3H	9.92	10.70	10.89	11.68	12.97	9.43	10.21	10.40	11.19	12.48
	4H	10.51	11.24	11.49	12.22	13.53	10.01	10.75	11.00	11.73	13.03
	6H	10.90	11.58	11.90	12.57	13.88	10.40	11.08	11.40	12.07	13.38
	8H	11.01	11.65	12.01	12.66	13.97	10.51	11.15	11.50	12.15	13.47
	12H	11.05	11.66	12.06	12.67	14.00	10.54	11.16	11.55	12.16	13.49
4H	2H	8.72	9.46	9.71	10.44	11.74	8.37	9.10	9.36	10.09	11.39
	3H	10.59	11.20	11.58	12.21	13.53	10.18	10.79	11.17	11.80	13.12
	4H	11.30	11.85	12.30	12.86	14.20	10.87	11.43	11.88	12.44	13.78
	6H	11.81	12.29	12.82	13.32	14.65	11.37	11.86	12.39	12.89	14.22
	8H	11.95	12.40	12.97	13.43	14.78	11.52	11.97	12.53	12.99	14.34
	12H	12.03	12.43	13.06	13.47	14.83	11.58	11.98	12.61	13.02	14.38
8H	4H	11.49	11.94	12.51	12.96	14.31	11.11	11.56	12.13	12.58	13.93
	6H	12.11	12.48	13.16	13.55	14.90	11.73	12.10	12.77	13.17	14.52
	8H	12.33	12.66	13.38	13.71	15.08	11.94	12.27	12.99	13.32	14.68
	12H	12.46	12.75	13.51	13.79	15.20	12.05	12.34	13.10	13.38	14.79
12H	4H	11.47	11.88	12.51	12.92	14.27	11.10	11.51	12.14	12.55	13.91
	6H	12.14	12.47	13.19	13.52	14.89	11.77	12.10	12.82	13.15	14.52
	8H	12.38	12.67	13.43	13.71	15.12	12.00	12.29	13.05	13.33	14.74