

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907664

Luminaire Tested: DFN2DIP-4P3F0-030D050US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907664
REPORT IS A COMBINATION OF REPORTS P899062 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D050US840-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7043.8 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 64.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907664
CATALOG NUMBER: DFN2DIP-4P3F0-030D050US840-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P907664

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38	32				32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32	27				27
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28	23				23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20				20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18				18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14				14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13				13
9	49	38	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12				12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	16	17	14	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1427	1427	1427
5°	1428	1403	1413
10°	1413	1375	1366
15°	1393	1328	1295
20°	1366	1265	1207
25°	1339	1194	1123
30°	1303	1121	1016
35°	1267	1043	922
40°	1231	963	814
45°	1189	873	716
50°	1145	783	621
55°	1099	686	529
60°	1046	586	435
65°	985	484	391
70°	911	389	353
75°	818	341	320
80°	684	283	276
85°	464	184	205

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1601 cd/sqm



TEST NUMBER: P907664

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	1.7
10°-20°	322.1	4.6
20°-30°	452.3	6.4
30°-40°	493.0	7.0
40°-50°	453.1	6.4
50°-60°	355.9	5.1
60°-70°	231.6	3.3
70°-80°	119.2	1.7
80°-90°	35.0	0.5
90°-100°	98.8	1.4
100°-110°	314.0	4.5
110°-120°	537.3	7.6
120°-130°	706.6	10.0
130°-140°	793.2	11.3
140°-150°	777.8	11.0
150°-160°	652.5	9.3
160°-170°	432.7	6.1
170°-180°	151.2	2.1
0°-30°	891.8	12.7
0°-40°	1384.8	19.7
0°-60°	2193.8	31.1
0°-90°	2579.6	36.6
90°-120°	950.1	13.5
90°-150°	3227.7	45.8
90°-180°	4464.0	63.4
0°-180°	7043.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	17	47	44	46	7
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P907664

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P907664

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9



TEST NUMBER: P907664
 CATALOG NUMBER: DFN2DIP-4P3F0-030D050US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.95	7.68	8.02	8.75	10.20	2.91	3.64	3.98	4.71	6.16
	3H	8.62	9.27	9.70	10.35	11.82	4.09	4.74	5.17	5.82	7.29
	4H	9.22	9.84	10.31	10.92	12.39	4.53	5.15	5.62	6.23	7.70
	6H	9.63	10.20	10.73	11.28	12.77	4.84	5.41	5.94	6.49	7.98
	8H	9.75	10.30	10.86	11.39	12.88	4.92	5.47	6.03	6.56	8.05
	12H	9.81	10.32	10.92	11.42	12.92	4.96	5.48	6.07	6.57	8.07
4H	2H	6.96	7.58	8.05	8.65	10.13	3.49	4.11	4.59	5.19	6.67
	3H	8.77	9.29	9.87	10.39	11.88	4.83	5.34	5.93	6.45	7.94
	4H	9.46	9.93	10.56	11.02	12.53	5.37	5.84	6.47	6.93	8.44
	6H	9.96	10.37	11.08	11.48	12.99	5.77	6.18	6.89	7.30	8.80
	8H	10.13	10.51	11.25	11.62	13.14	5.90	6.27	7.01	7.38	8.90
	12H	10.22	10.56	11.35	11.68	13.21	5.95	6.30	7.08	7.42	8.94
8H	4H	9.42	9.79	10.53	10.90	12.42	5.64	6.01	6.75	7.12	8.64
	6H	9.97	10.28	11.11	11.44	12.95	6.14	6.45	7.28	7.61	9.12
	8H	10.18	10.46	11.33	11.59	13.13	6.33	6.60	7.47	7.73	9.27
	12H	10.32	10.56	11.46	11.68	13.26	6.44	6.68	7.58	7.81	9.38
12H	4H	9.36	9.70	10.49	10.83	12.35	5.64	5.98	6.77	7.10	8.62
	6H	9.95	10.22	11.09	11.35	12.89	6.19	6.46	7.33	7.60	9.13
	8H	10.16	10.40	11.30	11.53	13.10	6.39	6.63	7.54	7.76	9.33