

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921418

Luminaire Tested: DFN2DIP-4P4F0-050D030US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921418
REPORT IS A COMBINATION OF REPORTS P899083 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D030US940-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6781.5 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 73.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921418
CATALOG NUMBER: DFN2DIP-4P4F0-050D030US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P921418
 CATALOG NUMBER: DFN2DIP-4P4F0-050D030US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	70	70	70	65
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59	59	59	59	55
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	50	50	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	42	42	42	39
4	77	66	58	52	72	62	55	49	55	50	45	49	44	41	43	40	37	37	37	37	33
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	32	32	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	28	28	28	26
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	25	25	25	23
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22	22	22	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	20	20	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	19	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1125	1125	1125
5°	1127	1110	1118
10°	1118	1096	1103
15°	1102	1078	1080
20°	1080	1053	1056
25°	1058	1023	1028
30°	1030	996	993
35°	1004	964	956
40°	972	931	921
45°	940	898	884
50°	905	863	842
55°	868	823	804
60°	826	776	760
65°	781	727	708
70°	723	667	652
75°	643	596	602
80°	547	505	503
85°	397	347	339

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 940 cd/sqm



TEST NUMBER: P921418

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	2.4
10°-20°	459.4	6.8
20°-30°	675.2	10.0
30°-40°	784.2	11.6
40°-50°	783.2	11.5
50°-60°	682.9	10.1
60°-70°	504.8	7.4
70°-80°	285.6	4.2
80°-90°	77.8	1.1
90°-100°	52.3	0.8
100°-110°	166.3	2.5
110°-120°	284.7	4.2
120°-130°	374.4	5.5
130°-140°	420.2	6.2
140°-150°	412.1	6.1
150°-160°	345.7	5.1
160°-170°	229.2	3.4
170°-180°	80.1	1.2
0°-30°	1297.9	19.1
0°-40°	2082.0	30.7
0°-60°	3548.1	52.3
0°-90°	4416.4	65.1
90°-120°	503.4	7.4
90°-150°	1710.0	25.2
90°-180°	2365.0	34.9
0°-180°	6781.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1728	1710	1723	1720	165
15°	1651	1642	1620	1627	1618	465
25°	1495	1481	1453	1456	1453	688
35°	1290	1273	1246	1236	1228	805
45°	1049	1038	1012	994	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	485	530
75°	280	277	268	259	262	299
85°	68	67	65	60	58	76
90°	1	9	25	24	24	7
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	



TEST NUMBER: P921418

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1734.8	1734.8	1734.8	1734.8	1734.8
2.5°	1744.9	1736.6	1718.2	1734.8	1731.7
5°	1734.8	1728.3	1709.9	1723.1	1720.0
7.5°	1723.1	1713.2	1694.9	1708.3	1705.0
10°	1705.0	1693.3	1673.3	1686.5	1681.6
12.5°	1679.8	1669.9	1649.9	1658.2	1654.8
15°	1651.4	1641.5	1619.8	1626.6	1618.2
17.5°	1616.4	1606.5	1584.7	1593.0	1584.7
20°	1578.1	1568.2	1544.8	1549.7	1543.2
22.5°	1539.8	1524.7	1503.0	1503.0	1499.6
25°	1494.7	1481.4	1453.0	1456.3	1453.0
27.5°	1444.6	1432.9	1411.3	1406.3	1398.0
30°	1394.6	1381.3	1356.3	1351.3	1344.6
32.5°	1341.2	1331.3	1304.6	1294.5	1287.8
35°	1289.5	1272.9	1246.2	1236.1	1227.8
37.5°	1231.1	1216.1	1189.4	1177.7	1169.4
40°	1171.2	1157.7	1131.0	1116.1	1109.4
42.5°	1112.8	1099.3	1072.7	1055.9	1046.0
45°	1049.4	1037.7	1012.5	994.3	987.6
47.5°	987.6	975.9	949.2	930.8	920.9
50°	922.5	914.2	890.8	867.5	859.1
52.5°	859.1	847.4	825.8	807.4	795.8
55°	794.2	784.1	764.0	744.0	735.8
57.5°	729.0	720.7	698.9	678.9	672.2
60°	663.9	657.4	634.0	615.5	610.6
62.5°	600.6	588.9	572.2	555.5	548.8
65°	535.6	525.5	508.8	493.8	485.4
67.5°	468.9	460.4	445.5	433.8	427.0
70°	407.1	400.4	385.3	373.6	367.1
72.5°	343.8	337.0	328.7	317.0	312.0
75°	280.2	277.0	268.5	258.6	262.0
77.5°	223.6	216.8	213.5	208.5	203.6
80°	166.9	165.1	161.8	156.9	153.5
82.5°	113.4	113.4	111.8	105.1	105.1
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9



TEST NUMBER: P921418

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1



TEST NUMBER: P921418
 CATALOG NUMBER: DFN2DIP-4P4F0-050D030US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.99	10.01	9.81	10.84	11.88	8.55	9.56	9.36	10.40	11.44
	3H	10.67	11.58	11.50	12.43	13.49	10.18	11.09	11.01	11.94	13.00
	4H	11.27	12.13	12.11	12.98	14.06	10.77	11.63	11.62	12.49	13.56
	6H	11.68	12.47	12.54	13.34	14.43	11.18	11.97	12.04	12.84	13.93
	8H	11.79	12.55	12.66	13.43	14.52	11.29	12.05	12.15	12.93	14.02
	12H	11.85	12.57	12.72	13.44	14.56	11.34	12.06	12.21	12.93	14.05
4H	2H	9.47	10.33	10.32	11.19	12.26	9.12	9.98	9.97	10.83	11.91
	3H	11.36	12.08	12.22	12.96	14.06	10.95	11.67	11.81	12.56	13.65
	4H	12.08	12.74	12.96	13.62	14.74	11.66	12.31	12.53	13.20	14.32
	6H	12.61	13.18	13.50	14.09	15.21	12.18	12.75	13.07	13.66	14.78
	8H	12.77	13.30	13.66	14.20	15.34	12.33	12.86	13.22	13.76	14.90
	12H	12.85	13.33	13.76	14.25	15.39	12.40	12.88	13.31	13.80	14.94
8H	4H	12.29	12.82	13.18	13.73	14.86	11.92	12.45	12.81	13.35	14.48
	6H	12.94	13.38	13.86	14.32	15.45	12.55	12.99	13.47	13.94	15.07
	8H	13.16	13.55	14.09	14.49	15.64	12.77	13.16	13.70	14.10	15.25
	12H	13.30	13.65	14.24	14.58	15.78	12.89	13.24	13.83	14.17	15.37
12H	4H	12.29	12.76	13.20	13.69	14.83	11.92	12.40	12.83	13.32	14.46
	6H	12.97	13.36	13.90	14.29	15.45	12.60	12.99	13.53	13.92	15.07
	8H	13.22	13.56	14.15	14.49	15.70	12.84	13.18	13.77	14.11	15.32