

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907717

Luminaire Tested: DFN2DIP-4P3F0-060D030US840-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907717
REPORT IS A COMBINATION OF REPORTS P900568 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-060D030US840-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8149.7 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907717

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907717

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2854	2854	2854
5°	2857	2807	2826
10°	2827	2750	2733
15°	2786	2657	2590
20°	2733	2530	2415
25°	2678	2388	2246
30°	2605	2243	2031
35°	2534	2086	1843
40°	2461	1925	1628
45°	2377	1746	1433
50°	2290	1566	1242
55°	2199	1373	1058
60°	2093	1172	870
65°	1971	968	782
70°	1823	777	707
75°	1637	681	641
80°	1368	566	553
85°	928	368	410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2377 cd/sqm

TEST NUMBER: P907717

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US840-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	2.9
10°-20°	644.3	7.9
20°-30°	904.6	11.1
30°-40°	986.1	12.1
40°-50°	906.3	11.1
50°-60°	711.7	8.7
60°-70°	463.3	5.7
70°-80°	238.5	2.9
80°-90°	62.7	0.8
90°-100°	33.7	0.4
100°-110°	125.7	1.5
110°-120°	333.3	4.1
120°-130°	552.9	6.8
130°-140°	587.3	7.2
140°-150°	545.8	6.7
150°-160°	438.8	5.4
160°-170°	282.8	3.5
170°-180°	97.3	1.2
0°-30°	1783.6	21.9
0°-40°	2769.6	34.0
0°-60°	4387.7	53.8
0°-90°	5152.1	63.2
90°-120°	492.7	6.0
90°-150°	2178.7	26.7
90°-180°	2998.0	36.8
0°-180°	8149.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2090	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	1	9	15	19	20	8
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P907717

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.3	2504.3	2504.3	2504.3	2504.3
2.5°	2515.6	2504.3	2479.2	2502.0	2497.5
5°	2504.3	2493.0	2463.4	2483.9	2477.1
7.5°	2483.9	2470.3	2438.6	2447.5	2436.2
10°	2456.6	2440.7	2395.6	2388.6	2375.1
12.5°	2422.8	2402.3	2341.0	2327.5	2302.5
15°	2381.9	2356.8	2279.9	2236.9	2214.2
17.5°	2334.3	2297.9	2202.7	2152.9	2116.7
20°	2279.9	2234.4	2121.2	2064.7	2014.7
22.5°	2221.0	2168.8	2037.3	1960.4	1926.4
25°	2162.1	2089.5	1940.0	1847.1	1813.0
27.5°	2091.9	2014.7	1849.3	1742.7	1690.6
30°	2017.1	1930.8	1749.5	1634.1	1572.8
32.5°	1944.5	1840.2	1654.6	1518.4	1461.7
35°	1863.0	1747.4	1548.0	1405.1	1355.1
37.5°	1783.6	1658.8	1448.2	1291.7	1235.2
40°	1699.7	1563.9	1343.8	1183.0	1124.1
42.5°	1613.7	1468.6	1239.7	1071.9	1015.4
45°	1523.0	1371.0	1133.3	972.1	917.8
47.5°	1436.9	1276.1	1031.3	870.2	820.4
50°	1341.7	1180.8	931.5	775.0	727.6
52.5°	1248.6	1078.6	836.3	686.7	643.7
55°	1158.0	981.3	736.5	600.7	557.5
57.5°	1065.2	883.8	648.2	521.3	484.9
60°	970.0	788.7	555.2	439.8	403.4
62.5°	877.2	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.4	317.4	310.4
67.5°	691.3	507.6	317.4	278.7	272.0
70°	596.0	419.3	262.8	240.2	231.1
72.5°	505.4	337.6	219.7	201.8	197.1
75°	417.0	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.4	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P907717

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5

TEST NUMBER: P907717

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.91	12.86	12.75	13.72	14.79	7.87	8.82	8.71	9.68	10.75
	3H	13.59	14.44	14.45	15.31	16.41	9.06	9.91	9.92	10.78	11.88
	4H	14.20	15.01	15.07	15.88	16.99	9.51	10.32	10.38	11.19	12.30
	6H	14.63	15.37	15.51	16.25	17.37	9.83	10.57	10.72	11.46	12.58
	8H	14.75	15.46	15.65	16.36	17.48	9.93	10.63	10.82	11.53	12.65
	12H	14.82	15.49	15.72	16.38	17.53	9.97	10.64	10.87	11.53	12.68
4H	2H	11.94	12.74	12.82	13.62	14.73	8.48	9.28	9.35	10.16	11.27
	3H	13.78	14.44	14.66	15.35	16.47	9.83	10.50	10.72	11.41	12.53
	4H	14.47	15.07	15.37	15.98	17.13	10.38	10.99	11.28	11.89	13.04
	6H	14.99	15.51	15.90	16.44	17.59	10.80	11.32	11.71	12.25	13.40
	8H	15.16	15.65	16.08	16.57	17.74	10.93	11.41	11.84	12.34	13.50
	12H	15.26	15.70	16.19	16.64	17.81	10.99	11.43	11.93	12.37	13.54
8H	4H	14.44	14.93	15.36	15.85	17.02	10.67	11.15	11.58	12.08	13.24
	6H	15.01	15.41	15.95	16.38	17.54	11.18	11.58	12.12	12.55	13.71
	8H	15.22	15.58	16.17	16.53	17.72	11.37	11.72	12.32	12.68	13.86
	12H	15.36	15.68	16.32	16.62	17.86	11.49	11.80	12.44	12.75	13.98
12H	4H	14.40	14.84	15.34	15.78	16.95	10.68	11.11	11.61	12.05	13.23
	6H	14.98	15.34	15.94	16.30	17.48	11.23	11.58	12.18	12.54	13.72
	8H	15.21	15.52	16.16	16.47	17.70	11.44	11.75	12.39	12.70	13.93

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8