

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910384

Luminaire Tested: DFN2DIP-4P3F0-030D030US850-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P910384  
REPORT IS A COMBINATION OF REPORTS P899042 AND P895917  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-030D030US850-RLLFLL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5772.3 lumens  
Efficiency: N/A  
Efficacy: 119.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 48.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P910384  
CATALOG NUMBER: DFN2DIP-4P3F0-030D030US850-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P910384

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US850-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1567	1567	1567
5°	1568	1541	1551
10°	1552	1510	1501
15°	1530	1459	1422
20°	1500	1389	1326
25°	1470	1311	1233
30°	1431	1231	1115
35°	1391	1145	1012
40°	1352	1057	894
45°	1305	959	787
50°	1257	860	682
55°	1207	754	581
60°	1149	644	478
65°	1082	531	430
70°	1001	427	388
75°	899	374	352
80°	751	311	304
85°	510	202	225

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1305 cd/sqm



TEST NUMBER: P910384

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US850-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.9	2.2
10°-20°	353.8	6.1
20°-30°	496.7	8.6
30°-40°	541.4	9.4
40°-50°	497.6	8.6
50°-60°	390.8	6.8
60°-70°	254.4	4.4
70°-80°	130.9	2.3
80°-90°	36.4	0.6
90°-100°	65.1	1.1
100°-110°	206.9	3.6
110°-120°	354.0	6.1
120°-130°	465.6	8.1
130°-140°	522.6	9.1
140°-150°	512.5	8.9
150°-160°	429.9	7.4
160°-170°	285.1	4.9
170°-180°	99.7	1.7
0°-30°	979.3	17.0
0°-40°	1520.7	26.3
0°-60°	2409.2	41.7
0°-90°	2830.9	49.0
90°-120°	626.0	10.8
90°-150°	2126.7	36.8
90°-180°	2941.0	51.0
0°-180°	5772.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	1	11	31	29	30	6
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P910384

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US850-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5



TEST NUMBER: P910384

CATALOG NUMBER: DFN2DIP-4P3F0-030D030US850-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2



TEST NUMBER: P910384  
 CATALOG NUMBER: DFN2DIP-4P3F0-030D030US850-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.58	9.40	9.55	10.39	11.67	4.54	5.36	5.51	6.35	7.63
	3H	10.25	10.99	11.24	11.98	13.29	5.72	6.46	6.71	7.45	8.76
	4H	10.86	11.56	11.86	12.55	13.87	6.17	6.86	7.17	7.86	9.18
	6H	11.28	11.92	12.28	12.92	14.25	6.48	7.12	7.49	8.12	9.45
	8H	11.40	12.01	12.41	13.03	14.35	6.57	7.18	7.58	8.20	9.52
	12H	11.46	12.04	12.48	13.05	14.40	6.61	7.19	7.63	8.20	9.55
4H	2H	8.60	9.29	9.60	10.29	11.61	5.13	5.83	6.14	6.82	8.14
	3H	10.42	11.00	11.43	12.02	13.35	6.48	7.05	7.49	8.08	9.41
	4H	11.11	11.64	12.13	12.65	14.01	7.02	7.55	8.04	8.56	9.92
	6H	11.62	12.07	12.65	13.11	14.46	7.43	7.88	8.46	8.92	10.28
	8H	11.79	12.22	12.82	13.25	14.61	7.56	7.98	8.59	9.01	10.38
	12H	11.88	12.27	12.93	13.31	14.68	7.62	8.00	8.67	9.05	10.42
8H	4H	11.07	11.50	12.11	12.53	13.90	7.30	7.72	8.33	8.75	10.12
	6H	11.63	11.98	12.69	13.06	14.42	7.81	8.16	8.86	9.23	10.59
	8H	11.85	12.16	12.91	13.21	14.60	7.99	8.30	9.05	9.36	10.74
	12H	11.98	12.25	13.05	13.31	14.73	8.11	8.38	9.17	9.43	10.85
12H	4H	11.03	11.41	12.07	12.46	13.83	7.30	7.68	8.35	8.73	10.10
	6H	11.61	11.92	12.67	12.98	14.36	7.85	8.16	8.92	9.22	10.60
	8H	11.83	12.10	12.89	13.15	14.58	8.06	8.33	9.12	9.38	10.81