

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913086

Luminaire Tested: DFN2DIP-4P3F0-020D020US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913086
REPORT IS A COMBINATION OF REPORTS P899029 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D020US927-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2970.7 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 31
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913086
CATALOG NUMBER: DFN2DIP-4P3F0-020D020US927-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P913086

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	703	703	703
5°	703	692	697
10°	697	683	687
15°	686	671	673
20°	672	655	657
25°	658	636	639
30°	640	618	617
35°	623	597	593
40°	603	576	571
45°	582	554	548
50°	559	532	521
55°	536	506	496
60°	509	476	468
65°	480	444	435
70°	443	405	399
75°	391	358	366
80°	329	299	302
85°	231	198	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 582 cd/sqm



TEST NUMBER: P913086

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	2.0
10°-20°	163.3	5.5
20°-30°	239.9	8.1
30°-40°	278.7	9.4
40°-50°	278.3	9.4
50°-60°	242.7	8.2
60°-70°	179.4	6.0
70°-80°	101.5	3.4
80°-90°	28.2	0.9
90°-100°	31.0	1.0
100°-110°	98.5	3.3
110°-120°	168.6	5.7
120°-130°	221.7	7.5
130°-140°	248.9	8.4
140°-150°	244.1	8.2
150°-160°	204.7	6.9
160°-170°	135.8	4.6
170°-180°	47.5	1.6
0°-30°	461.2	15.5
0°-40°	739.9	24.9
0°-60°	1260.8	42.4
0°-90°	1570.0	52.8
90°-120°	298.1	10.0
90°-150°	1012.8	34.1
90°-180°	1401.0	47.2
0°-180°	2970.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	616	616	616	616	616	
5°	616	614	608	612	611	59
15°	587	583	576	578	575	165
25°	531	526	516	518	516	244
35°	458	452	443	439	436	286
45°	373	369	360	353	351	288
55°	282	279	272	264	261	252
65°	190	187	181	176	172	188
75°	100	98	95	92	93	106
85°	24	24	23	21	21	27
90°	0	6	15	14	14	3
95°	22	26	27	27	26	25
105°	91	92	93	94	94	96
115°	169	172	171	170	169	167
125°	246	250	249	247	247	220
135°	318	323	324	323	322	246
145°	386	389	392	392	391	241
155°	442	443	444	447	445	203
165°	481	480	480	483	481	136
175°	500	499	498	501	498	48
180°	501	501	501	501	501	



TEST NUMBER: P913086

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US927-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	616.5	616.5	616.5	616.5	616.5
2.5°	620.0	617.1	610.5	616.5	615.4
5°	616.5	614.2	607.6	612.4	611.2
7.5°	612.4	608.8	602.3	607.0	605.9
10°	605.9	601.7	594.6	599.3	597.5
12.5°	596.9	593.4	586.3	589.2	588.0
15°	586.8	583.4	575.6	578.0	575.0
17.5°	574.4	570.9	563.2	566.1	563.2
20°	560.8	557.2	548.9	550.7	548.3
22.5°	547.2	541.9	534.1	534.1	532.9
25°	531.2	526.4	516.3	517.5	516.3
27.5°	513.3	509.2	501.5	499.8	496.8
30°	495.6	490.8	482.0	480.2	477.8
32.5°	476.6	473.1	463.6	460.0	457.6
35°	458.3	452.3	442.8	439.3	436.3
37.5°	437.5	432.1	422.6	418.5	415.5
40°	416.1	411.4	401.9	396.6	394.2
42.5°	395.4	390.6	381.2	375.3	371.7
45°	372.9	368.8	359.8	353.3	350.9
47.5°	350.9	346.8	337.3	330.7	327.3
50°	327.8	324.9	316.6	308.2	305.3
52.5°	305.3	301.1	293.4	286.9	282.8
55°	282.2	278.6	271.5	264.4	261.4
57.5°	259.0	256.1	248.3	241.3	238.8
60°	235.9	233.6	225.3	218.7	217.0
62.5°	213.4	209.2	203.4	197.4	195.0
65°	190.3	186.7	180.9	175.5	172.5
67.5°	166.6	163.6	158.3	154.2	151.8
70°	144.7	142.3	136.9	132.8	130.5
72.5°	122.2	119.8	116.8	112.6	110.9
75°	99.6	98.5	95.4	91.9	93.1
77.5°	79.5	77.1	75.8	74.1	72.3
80°	59.3	58.7	57.5	55.7	54.5
82.5°	40.3	40.3	39.8	37.4	37.4
85°	24.2	23.7	23.1	21.3	20.8
87.5°	10.7	9.5	8.3	6.6	5.9
90°	0.5	5.5	14.8	13.9	14.3
92.5°	9.3	12.7	13.2	13.6	13.6
95°	22.0	26.3	27.0	27.0	26.3
97.5°	36.7	40.6	42.3	42.3	42.3
100°	53.6	57.1	58.3	58.3	57.8
102.5°	71.5	74.0	75.7	76.1	75.7
105°	90.9	92.1	93.1	93.8	93.8
107.5°	110.3	112.1	112.1	112.4	110.3
110°	129.0	131.4	131.4	131.4	130.2



TEST NUMBER: P913086

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	149.2	151.8	151.4	150.1	149.2
115°	169.2	171.6	170.9	170.4	169.2
117.5°	189.0	192.3	190.2	189.0	187.7
120°	208.9	212.2	208.9	208.9	207.6
122.5°	227.0	231.2	229.2	228.0	227.0
125°	246.1	249.9	248.7	247.3	246.8
127.5°	264.7	269.3	267.7	265.9	264.7
130°	282.0	287.5	286.7	285.8	284.2
132.5°	301.5	305.8	306.0	304.0	302.7
135°	318.3	323.0	323.8	323.4	322.2
137.5°	337.0	340.8	341.6	341.3	339.4
140°	353.5	357.3	359.4	359.4	357.7
142.5°	370.4	374.1	375.4	375.8	374.1
145°	386.4	389.4	391.9	392.3	390.6
147.5°	400.8	404.6	406.4	407.1	405.4
150°	415.6	418.1	419.8	421.1	419.8
152.5°	428.7	431.3	433.4	435.1	433.4
155°	441.9	443.1	444.4	446.6	445.2
157.5°	453.2	454.1	454.9	457.9	455.7
160°	463.3	464.2	464.7	467.2	465.4
162.5°	472.7	472.7	473.1	476.0	473.9
165°	480.7	480.2	480.2	483.2	481.2
167.5°	487.9	486.6	486.6	489.6	487.5
170°	493.4	492.2	491.7	494.7	492.2
172.5°	497.2	495.9	495.5	498.5	495.9
175°	500.2	499.0	498.0	501.1	498.5
177.5°	501.8	500.7	499.7	502.2	499.7
180°	501.1	501.1	501.1	501.1	501.1



TEST NUMBER: P913086
 CATALOG NUMBER: DFN2DIP-4P3F0-020D020US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.27	7.16	7.20	8.11	9.34	5.83	6.71	6.76	7.66	8.89
	3H	7.93	8.72	8.87	9.68	10.94	7.44	8.24	8.38	9.19	10.45
	4H	8.51	9.27	9.47	10.23	11.49	8.02	8.77	8.98	9.74	11.00
	6H	8.91	9.61	9.88	10.58	11.85	8.41	9.11	9.38	10.08	11.35
	8H	9.02	9.68	9.99	10.66	11.94	8.51	9.18	9.49	10.16	11.43
	12H	9.06	9.69	10.05	10.67	11.97	8.55	9.18	9.54	10.16	11.46
4H	2H	6.73	7.48	7.69	8.45	9.71	6.38	7.13	7.34	8.09	9.36
	3H	8.59	9.22	9.57	10.22	11.49	8.19	8.82	9.16	9.81	11.09
	4H	9.31	9.88	10.29	10.87	12.17	8.88	9.46	9.86	10.44	11.74
	6H	9.82	10.31	10.81	11.32	12.62	9.39	9.88	10.38	10.89	12.19
	8H	9.97	10.43	10.96	11.43	12.75	9.53	9.99	10.53	11.00	12.31
	12H	10.04	10.46	11.05	11.48	12.79	9.59	10.01	10.60	11.03	12.35
8H	4H	9.50	9.96	10.50	10.97	12.28	9.12	9.59	10.12	10.59	11.90
	6H	10.13	10.51	11.15	11.56	12.87	9.74	10.13	10.76	11.17	12.48
	8H	10.35	10.68	11.37	11.71	13.04	9.95	10.29	10.98	11.32	12.65
	12H	10.47	10.77	11.51	11.80	13.17	10.06	10.36	11.10	11.39	12.76
12H	4H	9.49	9.90	10.50	10.92	12.24	9.12	9.54	10.13	10.56	11.87
	6H	10.16	10.49	11.19	11.53	12.86	9.78	10.12	10.81	11.15	12.48
	8H	10.40	10.69	11.43	11.72	13.09	10.01	10.31	11.05	11.34	12.71