

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913100

Luminaire Tested: DFN2DIP-4P3F0-020D050US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913100
REPORT IS A COMBINATION OF REPORTS P899060 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D050US927-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4852.1 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913100

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913100

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	25	24	23
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	29	26	24	21	19	17
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	746	746	746
5°	747	734	739
10°	739	719	715
15°	728	695	677
20°	714	662	631
25°	700	624	587
30°	681	586	531
35°	663	546	482
40°	644	503	426
45°	622	457	375
50°	599	409	325
55°	575	359	277
60°	547	307	228
65°	515	253	205
70°	477	203	185
75°	428	178	168
80°	358	148	145
85°	242	96	107

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1257 cd/sqm

TEST NUMBER: P913100

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	1.3
10°-20°	168.5	3.5
20°-30°	236.5	4.9
30°-40°	257.8	5.3
40°-50°	237.0	4.9
50°-60°	186.1	3.8
60°-70°	121.2	2.5
70°-80°	62.3	1.3
80°-90°	19.5	0.4
90°-100°	77.5	1.6
100°-110°	246.3	5.1
110°-120°	421.5	8.7
120°-130°	554.3	11.4
130°-140°	622.2	12.8
140°-150°	610.1	12.6
150°-160°	511.8	10.5
160°-170°	339.4	7.0
170°-180°	118.6	2.4
0°-30°	466.4	9.6
0°-40°	724.2	14.9
0°-60°	1147.3	23.6
0°-90°	1350.3	27.8
90°-120°	745.3	15.4
90°-150°	2532.0	52.2
90°-180°	3502.0	72.2
0°-180°	4852.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	655	652	644	650	648	62
15°	623	616	596	585	579	176
25°	565	546	507	483	474	260
35°	487	457	405	367	354	305
45°	398	358	296	254	240	308
55°	303	257	193	157	146	271
65°	204	156	103	83	81	203
75°	109	68	47	43	43	115
85°	25	13	11	11	11	29
90°	1	14	37	35	36	5
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	

TEST NUMBER: P913100

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US927-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	654.8	654.8	654.8	654.8	654.8
2.5°	657.7	654.8	648.2	654.3	653.1
5°	654.8	651.9	644.1	649.5	647.7
7.5°	649.5	645.9	637.6	640.0	637.0
10°	642.4	638.2	626.4	624.6	621.1
12.5°	633.5	628.1	612.1	608.6	602.1
15°	622.8	616.2	596.1	584.9	579.0
17.5°	610.4	600.9	576.0	562.9	553.5
20°	596.1	584.2	554.7	539.9	526.8
22.5°	580.7	567.1	532.7	512.6	503.7
25°	565.4	546.4	507.2	483.0	474.0
27.5°	547.0	526.8	483.5	455.7	442.0
30°	527.4	504.9	457.5	427.3	411.2
32.5°	508.4	481.2	432.6	397.0	382.2
35°	487.1	456.9	404.8	367.4	354.3
37.5°	466.4	433.7	378.7	337.8	323.0
40°	444.4	408.9	351.4	309.3	293.9
42.5°	421.9	384.0	324.2	280.3	265.5
45°	398.2	358.5	296.4	254.2	240.0
47.5°	375.7	333.7	269.7	227.5	214.5
50°	350.9	308.8	243.6	202.6	190.3
52.5°	326.5	282.0	218.6	179.6	168.3
55°	302.8	256.6	192.6	157.1	145.8
57.5°	278.5	231.1	169.5	136.3	126.8
60°	253.7	206.2	145.2	115.0	105.5
62.5°	229.3	182.0	124.5	96.0	91.3
65°	204.5	156.5	103.1	83.0	81.2
67.5°	180.8	132.7	83.0	72.9	71.1
70°	155.8	109.6	68.7	62.8	60.4
72.5°	132.1	88.2	57.4	52.8	51.6
75°	109.0	67.5	47.4	43.3	42.7
77.5°	86.0	48.0	37.3	34.9	33.7
80°	64.6	34.4	28.4	26.1	26.1
82.5°	45.0	23.1	19.6	18.4	18.4
85°	25.4	13.0	11.2	11.2	11.2
87.5°	9.5	4.8	4.8	4.1	4.1
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5

TEST NUMBER: P913100

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7

TEST NUMBER: P913100

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.55	4.23	4.68	5.35	6.91	0.00	0.19	0.64	1.31	2.87
	3H	5.21	5.82	6.35	6.95	8.52	0.68	1.29	1.82	2.42	3.99
	4H	5.81	6.39	6.96	7.52	9.09	1.12	1.70	2.27	2.83	4.41
	6H	6.22	6.75	7.38	7.88	9.47	1.43	1.96	2.59	3.09	4.68
	8H	6.34	6.85	7.50	7.99	9.57	1.51	2.02	2.67	3.16	4.74
	12H	6.40	6.87	7.56	8.01	9.62	1.55	2.03	2.71	3.17	4.77
4H	2H	3.55	4.12	4.71	5.25	6.83	0.09	0.66	1.24	1.79	3.37
	3H	5.36	5.84	6.52	6.99	8.58	1.42	1.89	2.58	3.05	4.64
	4H	6.04	6.48	7.20	7.62	9.24	1.95	2.39	3.12	3.54	5.15
	6H	6.54	6.92	7.71	8.09	9.69	2.36	2.73	3.53	3.90	5.50
	8H	6.71	7.07	7.88	8.22	9.84	2.48	2.83	3.65	3.99	5.61
	12H	6.80	7.12	7.98	8.29	9.91	2.53	2.85	3.72	4.02	5.64
8H	4H	6.00	6.35	7.16	7.50	9.12	2.22	2.57	3.39	3.73	5.34
	6H	6.55	6.84	7.74	8.04	9.66	2.72	3.01	3.91	4.21	5.83
	8H	6.77	7.02	7.96	8.19	9.83	2.91	3.16	4.10	4.34	5.97
	12H	6.89	7.11	8.09	8.29	9.96	3.02	3.24	4.21	4.41	6.08
12H	4H	5.94	6.26	7.12	7.43	9.05	2.22	2.53	3.40	3.70	5.32
	6H	6.53	6.78	7.72	7.96	9.59	2.77	3.02	3.96	4.20	5.83
	8H	6.74	6.96	7.93	8.13	9.80	2.97	3.19	4.16	4.37	6.03

END OF REPORT