

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924125

Luminaire Tested: DFN2DIP-4P4F0-040D030US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924125
REPORT IS A COMBINATION OF REPORTS P900602 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-040D030US950-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open
No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6077.0 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924125

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924125

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53	53	53
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46	46	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	39	39	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34	34	34
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33	30	30	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21	21	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	19	19	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1023	1023	1023
5°	1025	1007	1014
10°	1015	988	981
15°	1001	955	931
20°	983	911	868
25°	964	861	808
30°	938	809	732
35°	914	754	664
40°	888	696	587
45°	859	633	518
50°	829	569	449
55°	797	500	384
60°	760	428	316
65°	718	355	285
70°	667	287	259
75°	603	253	236
80°	510	214	206
85°	356	144	158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 859 cd/sqm

TEST NUMBER: P924125

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	2.4
10°-20°	405.8	6.7
20°-30°	569.7	9.4
30°-40°	621.0	10.2
40°-50°	570.8	9.4
50°-60°	448.2	7.4
60°-70°	291.8	4.8
70°-80°	150.2	2.5
80°-90°	40.1	0.7
90°-100°	31.9	0.5
100°-110°	118.7	2.0
110°-120°	314.9	5.2
120°-130°	522.3	8.6
130°-140°	554.8	9.1
140°-150°	515.6	8.5
150°-160°	414.5	6.8
160°-170°	267.1	4.4
170°-180°	91.9	1.5
0°-30°	1123.3	18.5
0°-40°	1744.3	28.7
0°-60°	2763.3	45.5
0°-90°	3245.3	53.4
90°-120°	465.5	7.7
90°-150°	2058.1	33.9
90°-180°	2832.0	46.6
0°-180°	6077.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	1	8	14	18	19	6
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	



TEST NUMBER: P924125

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2



TEST NUMBER: P924125

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9

TEST NUMBER: P924125

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.56	8.42	8.49	9.36	10.59	3.52	4.38	4.45	5.32	6.55
	3H	9.24	10.01	10.19	10.97	12.22	4.71	5.48	5.66	6.44	7.68
	4H	9.86	10.58	10.82	11.54	12.80	5.16	5.89	6.12	6.85	8.11
	6H	10.29	10.95	11.26	11.92	13.19	5.49	6.16	6.46	7.12	8.39
	8H	10.42	11.05	11.39	12.03	13.30	5.58	6.22	6.56	7.20	8.47
	12H	10.48	11.08	11.46	12.06	13.35	5.63	6.23	6.61	7.21	8.50
4H	2H	7.58	8.31	8.55	9.27	10.52	4.12	4.85	5.09	5.81	7.06
	3H	9.42	10.02	10.39	11.01	12.28	5.48	6.08	6.45	7.07	8.34
	4H	10.12	10.67	11.10	11.65	12.95	6.03	6.58	7.01	7.56	8.86
	6H	10.64	11.11	11.63	12.12	13.41	6.45	6.92	7.45	7.93	9.22
	8H	10.82	11.26	11.82	12.26	13.57	6.58	7.02	7.58	8.02	9.33
	12H	10.92	11.32	11.93	12.33	13.64	6.65	7.05	7.66	8.06	9.38
8H	4H	10.09	10.53	11.08	11.53	12.84	6.31	6.75	7.31	7.75	9.06
	6H	10.66	11.02	11.68	12.07	13.37	6.83	7.20	7.86	8.24	9.55
	8H	10.88	11.20	11.91	12.23	13.56	7.03	7.35	8.06	8.38	9.70
	12H	11.02	11.31	12.06	12.33	13.70	7.15	7.43	8.18	8.46	9.82
12H	4H	10.04	10.44	11.06	11.45	12.77	6.32	6.72	7.34	7.73	9.05
	6H	10.64	10.96	11.67	11.99	13.31	6.89	7.21	7.92	8.24	9.56
	8H	10.86	11.14	11.89	12.17	13.54	7.10	7.38	8.13	8.41	9.77