

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924144

Luminaire Tested: DFN2DIP-4P4F0-040D080US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924144
REPORT IS A COMBINATION OF REPORTS P899142 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-040D080US950-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9997.9 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 112.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924144

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924144

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1023	1023	1023
5°	1025	1007	1014
10°	1015	988	981
15°	1001	955	931
20°	983	911	868
25°	964	861	808
30°	938	809	732
35°	914	754	664
40°	888	696	587
45°	859	633	518
50°	829	569	449
55°	797	500	384
60°	760	428	316
65°	718	355	285
70°	667	287	259
75°	603	253	236
80°	510	214	206
85°	356	144	158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1829 cd/sqm

TEST NUMBER: P924144

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	1.5
10°-20°	405.8	4.1
20°-30°	569.7	5.7
30°-40°	621.0	6.2
40°-50°	570.8	5.7
50°-60°	448.2	4.5
60°-70°	291.8	2.9
70°-80°	150.2	1.5
80°-90°	45.2	0.5
90°-100°	149.4	1.5
100°-110°	474.6	4.7
110°-120°	812.1	8.1
120°-130°	1068.1	10.7
130°-140°	1198.9	12.0
140°-150°	1175.6	11.8
150°-160°	986.2	9.9
160°-170°	654.0	6.5
170°-180°	228.6	2.3
0°-30°	1123.3	11.2
0°-40°	1744.3	17.4
0°-60°	2763.3	27.6
0°-90°	3250.5	32.5
90°-120°	1436.1	14.4
90°-150°	4878.6	48.8
90°-180°	6747.0	67.5
0°-180°	9997.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	2	26	71	67	69	10
95°	106	127	130	130	127	118
105°	438	444	448	452	452	462
115°	815	827	823	821	815	806
125°	1185	1204	1198	1191	1189	1059
135°	1533	1556	1560	1558	1552	1185
145°	1861	1876	1888	1890	1882	1163
155°	2128	2134	2141	2151	2144	980
165°	2316	2313	2313	2328	2318	653
175°	2409	2404	2399	2414	2401	229
180°	2414	2414	2414	2414	2414	

TEST NUMBER: P924144

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	2.2	26.2	71.4	67.0	69.2
92.5°	45.1	61.2	63.3	65.4	65.4
95°	106.3	126.6	130.2	130.2	126.6
97.5°	176.9	195.8	203.8	203.8	203.8
100°	258.3	275.0	280.9	280.9	278.7
102.5°	344.2	356.6	364.5	366.7	364.5
105°	438.1	443.9	448.3	451.9	451.9
107.5°	531.2	540.0	540.0	541.4	531.2
110°	621.4	633.1	633.1	633.1	627.3

TEST NUMBER: P924144

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	718.9	731.3	729.1	723.3	718.9
115°	815.0	826.6	823.0	820.8	815.0
117.5°	910.3	926.3	916.1	910.3	904.5
120°	1006.4	1022.4	1006.4	1006.4	999.8
122.5°	1093.7	1114.1	1103.9	1098.1	1093.7
125°	1185.3	1203.6	1197.7	1191.2	1189.1
127.5°	1274.9	1297.4	1289.4	1280.7	1274.9
130°	1358.6	1384.7	1381.1	1376.8	1368.8
132.5°	1452.5	1472.8	1474.3	1464.1	1458.3
135°	1533.2	1555.8	1560.2	1558.0	1552.2
137.5°	1623.4	1641.6	1645.3	1643.8	1635.1
140°	1702.8	1720.9	1731.1	1731.1	1723.1
142.5°	1784.3	1802.5	1808.3	1810.5	1802.5
145°	1861.4	1875.9	1887.6	1889.8	1881.8
147.5°	1930.5	1948.7	1957.4	1961.1	1953.1
150°	2001.9	2014.2	2022.2	2028.8	2022.2
152.5°	2065.1	2077.5	2087.7	2095.7	2087.7
155°	2128.5	2134.3	2140.9	2151.0	2144.5
157.5°	2183.0	2187.4	2191.1	2205.6	2195.4
160°	2231.8	2236.2	2238.4	2250.7	2242.0
162.5°	2276.9	2276.9	2279.1	2292.9	2282.7
165°	2315.5	2313.3	2313.3	2327.9	2317.6
167.5°	2350.4	2343.9	2343.9	2358.4	2348.2
170°	2376.6	2370.8	2368.6	2383.2	2370.8
172.5°	2394.8	2389.0	2386.8	2401.3	2389.0
175°	2409.3	2403.5	2399.1	2413.7	2401.3
177.5°	2417.3	2411.5	2407.1	2419.5	2407.1
180°	2413.7	2413.7	2413.7	2413.7	2413.7

TEST NUMBER: P924144

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.34	6.05	6.44	7.14	8.65	1.31	2.01	2.40	3.10	4.61
	3H	7.02	7.65	8.13	8.75	10.27	2.49	3.12	3.59	4.22	5.74
	4H	7.62	8.22	8.74	9.33	10.85	2.93	3.53	4.05	4.63	6.16
	6H	8.04	8.59	9.17	9.70	11.24	3.25	3.80	4.37	4.90	6.44
	8H	8.17	8.69	9.30	9.81	11.34	3.34	3.86	4.47	4.98	6.51
	12H	8.23	8.73	9.36	9.84	11.39	3.38	3.87	4.51	4.99	6.54
4H	2H	5.35	5.95	6.47	7.05	8.57	1.89	2.49	3.01	3.59	5.11
	3H	7.17	7.67	8.30	8.80	10.34	3.23	3.73	4.36	4.86	6.39
	4H	7.86	8.32	9.00	9.44	11.00	3.77	4.23	4.91	5.35	6.91
	6H	8.38	8.77	9.52	9.91	11.46	4.19	4.58	5.33	5.72	7.27
	8H	8.55	8.92	9.69	10.05	11.62	4.32	4.68	5.46	5.81	7.38
	12H	8.65	8.98	9.80	10.12	11.69	4.38	4.71	5.53	5.85	7.42
8H	4H	7.82	8.19	8.96	9.32	10.89	4.05	4.41	5.19	5.55	7.11
	6H	8.39	8.69	9.55	9.87	11.43	4.56	4.87	5.73	6.04	7.60
	8H	8.61	8.87	9.78	10.03	11.61	4.76	5.02	5.92	6.17	7.76
	12H	8.75	8.98	9.92	10.13	11.75	4.87	5.10	6.04	6.25	7.87
12H	4H	7.77	8.10	8.92	9.24	10.81	4.05	4.38	5.20	5.52	7.09
	6H	8.36	8.63	9.53	9.78	11.37	4.61	4.88	5.78	6.03	7.62
	8H	8.58	8.82	9.75	9.97	11.58	4.82	5.05	5.99	6.20	7.82

END OF REPORT