

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913153

Luminaire Tested: DFN2DIP-4P3F0-050D030US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913153
REPORT IS A COMBINATION OF REPORTS P900566 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-050D030US927-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5719.6 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 71.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913153

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913153

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US927-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1866	1866	1866
5°	1867	1835	1847
10°	1848	1798	1786
15°	1821	1737	1693
20°	1786	1654	1578
25°	1751	1561	1468
30°	1703	1466	1328
35°	1656	1364	1205
40°	1609	1258	1064
45°	1554	1141	936
50°	1497	1023	812
55°	1437	897	692
60°	1368	766	569
65°	1288	633	512
70°	1192	508	462
75°	1070	445	419
80°	894	370	361
85°	607	241	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1554 cd/sqm

TEST NUMBER: P913153

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	2.7
10°-20°	421.2	7.4
20°-30°	591.3	10.3
30°-40°	644.6	11.3
40°-50°	592.4	10.4
50°-60°	465.3	8.1
60°-70°	302.9	5.3
70°-80°	155.9	2.7
80°-90°	41.2	0.7
90°-100°	26.5	0.5
100°-110°	98.6	1.7
110°-120°	261.5	4.6
120°-130°	433.7	7.6
130°-140°	460.7	8.1
140°-150°	428.1	7.5
150°-160°	344.2	6.0
160°-170°	221.8	3.9
170°-180°	76.3	1.3
0°-30°	1165.9	20.4
0°-40°	1810.5	31.7
0°-60°	2868.2	50.1
0°-90°	3368.2	58.9
90°-120°	386.5	6.8
90°-150°	1709.0	29.9
90°-180°	2351.0	41.1
0°-180°	5719.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	1	7	12	15	16	5
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	

TEST NUMBER: P913153

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9

TEST NUMBER: P913153

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1

TEST NUMBER: P913153

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.07	10.98	10.96	11.88	13.02	6.03	6.94	6.92	7.84	8.98
	3H	11.75	12.56	12.65	13.47	14.64	7.22	8.03	8.12	8.94	10.11
	4H	12.36	13.13	13.27	14.04	15.22	7.67	8.44	8.58	9.35	10.53
	6H	12.78	13.49	13.71	14.41	15.60	7.99	8.70	8.91	9.62	10.81
	8H	12.91	13.58	13.84	14.52	15.71	8.08	8.75	9.01	9.69	10.88
	12H	12.97	13.61	13.91	14.54	15.75	8.12	8.76	9.06	9.69	10.91
4H	2H	10.10	10.86	11.02	11.78	12.96	6.64	7.40	7.55	8.32	9.49
	3H	11.93	12.57	12.86	13.51	14.70	7.99	8.62	8.91	9.57	10.76
	4H	12.62	13.20	13.56	14.14	15.36	8.53	9.11	9.47	10.05	11.27
	6H	13.14	13.63	14.09	14.60	15.82	8.95	9.45	9.90	10.41	11.63
	8H	13.31	13.78	14.26	14.73	15.96	9.07	9.54	10.03	10.50	11.73
	12H	13.41	13.83	14.38	14.80	16.04	9.14	9.56	10.11	10.53	11.77
8H	4H	12.59	13.06	13.55	14.02	15.25	8.81	9.28	9.77	10.24	11.47
	6H	13.16	13.54	14.13	14.54	15.77	9.33	9.71	10.31	10.71	11.94
	8H	13.37	13.71	14.36	14.70	15.95	9.51	9.85	10.50	10.84	12.09
	12H	13.51	13.81	14.50	14.79	16.09	9.63	9.93	10.62	10.91	12.21
12H	4H	12.55	12.97	13.52	13.94	15.18	8.82	9.24	9.79	10.22	11.45
	6H	13.13	13.47	14.12	14.46	15.71	9.38	9.72	10.36	10.71	11.95
	8H	13.35	13.65	14.34	14.63	15.93	9.58	9.88	10.57	10.87	12.16

END OF REPORT