

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915816

Luminaire Tested: DFN2DIP-4P3F0-020D020US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915816
REPORT IS A COMBINATION OF REPORTS P899030 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D020US930-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2829.1 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 31
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915816
CATALOG NUMBER: DFN2DIP-4P3F0-020D020US930-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915816
 CATALOG NUMBER: DFN2DIP-4P3F0-020D020US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	768	768	768
5°	769	755	760
10°	761	740	735
15°	750	715	697
20°	735	681	650
25°	721	643	604
30°	701	603	547
35°	682	561	496
40°	662	518	438
45°	640	470	386
50°	616	421	334
55°	592	370	285
60°	563	315	234
65°	530	261	211
70°	491	209	190
75°	441	183	172
80°	368	152	148
85°	250	99	111

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 640 cd/sqm



TEST NUMBER: P915816

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	2.2
10°-20°	173.4	6.1
20°-30°	243.4	8.6
30°-40°	265.4	9.4
40°-50°	243.9	8.6
50°-60°	191.5	6.8
60°-70°	124.7	4.4
70°-80°	64.2	2.3
80°-90°	17.8	0.6
90°-100°	31.9	1.1
100°-110°	101.4	3.6
110°-120°	173.5	6.1
120°-130°	228.2	8.1
130°-140°	256.1	9.1
140°-150°	251.2	8.9
150°-160°	210.7	7.4
160°-170°	139.7	4.9
170°-180°	48.8	1.7
0°-30°	480.0	17.0
0°-40°	745.3	26.3
0°-60°	1180.8	41.7
0°-90°	1387.5	49.0
90°-120°	306.8	10.8
90°-150°	1042.3	36.8
90°-180°	1442.0	51.0
0°-180°	2829.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	674	674	674	674	674	
5°	674	671	663	668	667	64
15°	641	634	614	602	596	181
25°	582	562	522	497	488	268
35°	501	470	417	378	365	314
45°	410	369	305	262	247	317
55°	312	264	198	162	150	278
65°	210	161	106	85	84	209
75°	112	70	49	44	44	119
85°	26	13	12	12	12	30
90°	0	6	15	14	15	3
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	



TEST NUMBER: P915816

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	673.9	673.9	673.9	673.9	673.9
2.5°	676.9	673.9	667.2	673.4	672.1
5°	673.9	670.9	662.9	668.5	666.6
7.5°	668.5	664.8	656.2	658.7	655.6
10°	661.1	656.8	644.7	642.8	639.2
12.5°	652.0	646.4	630.0	626.4	619.6
15°	641.0	634.2	613.5	601.9	595.9
17.5°	628.2	618.4	592.8	579.4	569.6
20°	613.5	601.3	570.9	555.6	542.2
22.5°	597.7	583.7	548.3	527.6	518.4
25°	581.9	562.3	522.0	497.1	487.9
27.5°	563.0	542.2	497.7	469.0	454.9
30°	542.8	519.6	470.8	439.8	423.2
32.5°	523.3	495.2	445.2	408.6	393.4
35°	501.3	470.3	416.6	378.1	364.7
37.5°	480.0	446.4	389.7	347.6	332.4
40°	457.4	420.9	361.7	318.4	302.5
42.5°	434.2	395.3	333.6	288.5	273.3
45°	409.9	368.9	305.0	261.6	247.0
47.5°	386.7	343.4	277.5	234.2	220.8
50°	361.1	317.8	250.7	208.6	195.8
52.5°	336.0	290.2	225.0	184.8	173.3
55°	311.6	264.1	198.2	161.7	150.0
57.5°	286.7	237.8	174.5	140.3	130.5
60°	261.1	212.2	149.4	118.4	108.6
62.5°	236.0	187.3	128.1	98.8	93.9
65°	210.4	161.0	106.2	85.4	83.6
67.5°	186.1	136.6	85.4	75.0	73.2
70°	160.4	112.8	70.7	64.7	62.2
72.5°	136.0	90.8	59.1	54.3	53.1
75°	112.2	69.5	48.8	44.5	43.9
77.5°	88.5	49.4	38.4	36.0	34.7
80°	66.4	35.4	29.3	26.8	26.8
82.5°	46.3	23.8	20.1	18.9	18.9
85°	26.2	13.4	11.6	11.6	11.6
87.5°	9.8	4.9	4.9	4.2	4.2
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0



TEST NUMBER: P915816

CATALOG NUMBER: DFN2DIP-4P3F0-020D020US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7



TEST NUMBER: P915816
 CATALOG NUMBER: DFN2DIP-4P3F0-020D020US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.10	6.93	7.08	7.91	9.19	2.07	2.89	3.04	3.87	5.16
	3H	7.78	8.51	8.76	9.50	10.81	3.25	3.98	4.23	4.97	6.28
	4H	8.38	9.08	9.38	10.07	11.39	3.69	4.39	4.69	5.38	6.70
	6H	8.80	9.44	9.81	10.44	11.77	4.01	4.65	5.01	5.65	6.98
	8H	8.92	9.53	9.94	10.55	11.87	4.09	4.70	5.11	5.72	7.04
	12H	8.98	9.56	10.00	10.57	11.92	4.13	4.71	5.15	5.72	7.07
4H	2H	6.12	6.81	7.12	7.81	9.13	2.66	3.35	3.66	4.35	5.67
	3H	7.94	8.52	8.95	9.54	10.88	4.00	4.58	5.01	5.60	6.93
	4H	8.63	9.16	9.65	10.18	11.53	4.54	5.07	5.56	6.09	7.44
	6H	9.14	9.60	10.17	10.63	11.99	4.95	5.41	5.98	6.45	7.80
	8H	9.31	9.74	10.34	10.77	12.14	5.08	5.50	6.11	6.53	7.90
	12H	9.41	9.79	10.45	10.84	12.21	5.14	5.52	6.19	6.57	7.94
8H	4H	8.60	9.02	9.63	10.05	11.42	4.82	5.24	5.85	6.27	7.64
	6H	9.16	9.51	10.21	10.58	11.94	5.33	5.68	6.38	6.75	8.12
	8H	9.37	9.68	10.43	10.74	12.12	5.51	5.82	6.58	6.88	8.26
	12H	9.51	9.78	10.57	10.83	12.25	5.63	5.90	6.69	6.95	8.38
12H	4H	8.55	8.93	9.60	9.98	11.35	4.82	5.21	5.87	6.25	7.62
	6H	9.13	9.44	10.19	10.50	11.88	5.38	5.68	6.44	6.74	8.13
	8H	9.35	9.62	10.41	10.67	12.10	5.58	5.85	6.65	6.90	8.33