

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924207

Luminaire Tested: DFN2DIP-4P4F0-070D060US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924207
REPORT IS A COMBINATION OF REPORTS P900643 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D060US950-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12278.0 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924207

CATALOG NUMBER: DFN2DIP-4P4F0-070D060US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924207

CATALOG NUMBER: DFN2DIP-4P4F0-070D060US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		85	85	85		72	72	72		60	60	60
1	99	94	90	87		91	88	84	81		75	73	70		63	62	60		53	52	50
2	90	82	76	71		83	77	71	67		66	62	58		56	53	50		46	44	42
3	82	72	65	59		76	67	61	56		58	53	49		49	46	42		41	38	36
4	75	64	56	50		69	60	53	47		52	46	42		44	40	36		37	34	31
5	69	57	49	43		64	53	46	41		46	40	36		39	35	32		33	30	27
6	63	51	43	37		59	48	41	35		42	36	31		36	31	28		30	27	24
7	59	46	38	33		54	43	36	31		38	32	28		32	28	24		27	24	21
8	54	42	34	29		50	39	32	28		34	29	25		30	25	22		25	22	19
9	51	38	31	26		47	36	29	25		32	26	22		27	23	20		23	20	17
10	47	35	28	23		44	33	27	22		29	24	20		25	21	18		22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1686	1686	1686
5°	1688	1663	1674
10°	1675	1641	1652
15°	1650	1614	1617
20°	1617	1577	1582
25°	1584	1533	1540
30°	1543	1492	1488
35°	1504	1443	1432
40°	1456	1394	1379
45°	1407	1345	1325
50°	1355	1293	1262
55°	1300	1233	1204
60°	1238	1162	1138
65°	1170	1089	1060
70°	1083	999	977
75°	964	892	901
80°	820	756	754
85°	595	520	509

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1407 cd/sqm

TEST NUMBER: P924207

CATALOG NUMBER: DFN2DIP-4P4F0-070D060US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	2.0
10°-20°	688.1	5.6
20°-30°	1011.3	8.2
30°-40°	1174.5	9.6
40°-50°	1173.1	9.6
50°-60°	1022.9	8.3
60°-70°	756.1	6.2
70°-80°	427.8	3.5
80°-90°	116.3	0.9
90°-100°	63.7	0.5
100°-110°	237.5	1.9
110°-120°	629.8	5.1
120°-130°	1044.5	8.5
130°-140°	1109.5	9.0
140°-150°	1031.2	8.4
150°-160°	829.1	6.8
160°-170°	534.2	4.4
170°-180°	183.9	1.5
0°-30°	1943.9	15.8
0°-40°	3118.5	25.4
0°-60°	5314.4	43.3
0°-90°	6614.7	53.9
90°-120°	930.9	7.6
90°-150°	4116.2	33.5
90°-180°	5663.0	46.1
0°-180°	12278.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	1	17	28	35	38	11
95°	91	45	54	62	60	108
105°	425	467	85	101	106	454
115°	804	828	862	215	115	791
125°	1136	1155	1181	1191	1195	1014
135°	1406	1429	1441	1455	1452	1086
145°	1631	1630	1654	1663	1656	1020
155°	1796	1784	1800	1809	1798	828
165°	1893	1884	1888	1898	1888	535
175°	1936	1926	1929	1939	1925	184
180°	1932	1932	1932	1932	1932	



TEST NUMBER: P924207

CATALOG NUMBER: DFN2DIP-4P4F0-070D060US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	1.3	16.8	27.9	35.0	37.7
92.5°	35.0	29.4	33.5	36.3	37.7
95°	90.8	44.6	54.5	61.6	60.1
97.5°	163.5	48.9	71.2	75.6	76.9
100°	247.5	55.9	79.7	90.8	93.6
102.5°	339.6	337.0	82.5	97.8	102.1
105°	424.9	466.9	85.3	100.6	106.3
107.5°	524.2	559.0	88.1	103.4	109.0
110°	619.3	648.5	244.7	104.9	110.4

TEST NUMBER: P924207

CATALOG NUMBER: DFN2DIP-4P4F0-070D060US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	708.7	733.8	710.1	107.5	111.9
115°	803.7	827.5	862.5	215.3	114.7
117.5°	886.2	914.1	938.0	738.0	371.8
120°	978.5	999.4	1024.7	1041.4	852.7
122.5°	1056.7	1079.1	1107.1	1115.4	1116.9
125°	1136.4	1154.6	1181.1	1191.0	1195.1
127.5°	1209.1	1228.7	1249.7	1263.7	1265.0
130°	1277.6	1300.0	1315.3	1330.7	1329.4
132.5°	1347.5	1365.7	1381.0	1393.6	1392.3
135°	1406.3	1428.7	1441.1	1455.2	1452.4
137.5°	1467.6	1484.4	1498.5	1512.5	1508.4
140°	1527.7	1539.1	1554.4	1566.9	1560.0
142.5°	1578.2	1588.0	1606.2	1617.2	1610.3
145°	1631.3	1629.8	1653.6	1663.4	1656.4
147.5°	1677.3	1673.1	1696.9	1703.8	1698.4
150°	1722.2	1712.3	1734.8	1743.1	1736.1
152.5°	1759.8	1748.7	1769.6	1778.1	1768.2
155°	1796.2	1783.7	1800.5	1808.8	1797.6
157.5°	1825.6	1814.4	1827.0	1836.8	1825.6
160°	1850.8	1842.3	1850.8	1859.1	1849.3
162.5°	1873.0	1864.7	1871.7	1881.5	1868.9
165°	1892.6	1884.3	1888.4	1898.3	1888.4
167.5°	1908.0	1899.6	1903.9	1913.7	1901.0
170°	1920.7	1912.2	1915.1	1924.8	1912.2
172.5°	1929.0	1920.7	1923.5	1933.3	1920.7
175°	1936.0	1926.1	1929.0	1938.7	1924.8
177.5°	1938.7	1929.0	1930.4	1940.2	1927.7
180°	1931.8	1931.8	1931.8	1931.8	1931.8

TEST NUMBER: P924207

CATALOG NUMBER: DFN2DIP-4P4F0-070D060US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.46	10.35	10.38	11.29	12.51	9.01	9.91	9.93	10.85	12.07
	3H	11.13	11.93	12.06	12.88	14.12	10.63	11.44	11.57	12.39	13.63
	4H	11.72	12.48	12.67	13.43	14.68	11.22	11.99	12.17	12.94	14.19
	6H	12.12	12.83	13.09	13.79	15.05	11.62	12.33	12.58	13.29	14.55
	8H	12.23	12.90	13.20	13.88	15.14	11.73	12.40	12.70	13.38	14.63
	12H	12.28	12.92	13.26	13.89	15.18	11.77	12.41	12.75	13.38	14.67
4H	2H	9.92	10.68	10.88	11.64	12.89	9.57	10.33	10.52	11.28	12.53
	3H	11.80	12.43	12.76	13.42	14.68	11.39	12.03	12.36	13.01	14.27
	4H	12.52	13.10	13.49	14.08	15.36	12.09	12.68	13.07	13.65	14.94
	6H	13.04	13.54	14.03	14.54	15.83	12.61	13.11	13.60	14.11	15.40
	8H	13.19	13.66	14.18	14.66	15.96	12.76	13.22	13.75	14.22	15.52
	12H	13.27	13.69	14.28	14.71	16.01	12.82	13.24	13.83	14.26	15.56
8H	4H	12.72	13.19	13.71	14.18	15.48	12.34	12.81	13.33	13.81	15.11
	6H	13.36	13.75	14.37	14.78	16.08	12.97	13.36	13.99	14.40	15.70
	8H	13.58	13.92	14.60	14.95	16.26	13.19	13.53	14.21	14.56	15.87
	12H	13.72	14.02	14.75	15.04	16.40	13.31	13.61	14.33	14.63	15.99
12H	4H	12.71	13.13	13.71	14.14	15.45	12.34	12.76	13.35	13.77	15.08
	6H	13.39	13.73	14.41	14.76	16.07	13.02	13.36	14.04	14.38	15.70
	8H	13.64	13.94	14.66	14.96	16.32	13.26	13.56	14.28	14.58	15.94