

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902427

Luminaire Tested: DFN2DIP-HX2F0-020D040US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902427
REPORT IS A COMBINATION OF REPORTS P900691 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D040US830-FLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5598.7 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902427
CATALOG NUMBER: DFN2DIP-HX2F0-020D040US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P902427

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29	24				24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20				20
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21	17				17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15				15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13				13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12				12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10				10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9				9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1728	1728	1728
5°	1728	1700	1712
10°	1712	1673	1686
15°	1683	1641	1647
20°	1647	1599	1606
25°	1610	1549	1560
30°	1565	1502	1503
35°	1522	1448	1442
40°	1469	1393	1384
45°	1417	1338	1325
50°	1359	1279	1256
55°	1298	1212	1192
60°	1230	1133	1119
65°	1154	1050	1033
70°	1059	949	939
75°	928	828	849
80°	768	674	684
85°	520	423	424

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1417 cd/sqm



TEST NUMBER: P902427

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	1.2
10°-20°	194.2	3.5
20°-30°	285.5	5.1
30°-40°	331.5	5.9
40°-50°	331.1	5.9
50°-60°	288.7	5.2
60°-70°	213.4	3.8
70°-80°	120.8	2.2
80°-90°	34.1	0.6
90°-100°	41.9	0.7
100°-110°	156.4	2.8
110°-120°	414.8	7.4
120°-130°	688.0	12.3
130°-140°	730.8	13.1
140°-150°	679.2	12.1
150°-160°	546.1	9.8
160°-170°	351.9	6.3
170°-180°	121.1	2.2
0°-30°	548.7	9.8
0°-40°	880.3	15.7
0°-60°	1500.2	26.8
0°-90°	1868.5	33.4
90°-120°	613.2	11.0
90°-150°	2711.2	48.4
90°-180°	3730.0	66.6
0°-180°	5598.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	11	18	23	25	5
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	



TEST NUMBER: P902427

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7



TEST NUMBER: P902427

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4



TEST NUMBER: P902427
 CATALOG NUMBER: DFN2DIP-HX2F0-020D040US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.26	7.99	8.35	9.08	10.57	6.84	7.57	7.93	8.66	10.15
	3H	8.89	9.54	9.98	10.64	12.14	8.43	9.08	9.53	10.18	11.68
	4H	9.45	10.07	10.56	11.17	12.68	8.99	9.61	10.10	10.71	12.22
	6H	9.83	10.40	10.94	11.50	13.02	9.37	9.94	10.48	11.04	12.56
	8H	9.92	10.46	11.04	11.58	13.10	9.46	10.00	10.58	11.12	12.64
	12H	9.95	10.47	11.08	11.58	13.12	9.49	10.01	10.61	11.12	12.66
4H	2H	7.70	8.32	8.81	9.42	10.93	7.36	7.98	8.48	9.08	10.59
	3H	9.52	10.04	10.64	11.16	12.69	9.14	9.66	10.26	10.78	12.31
	4H	10.21	10.69	11.34	11.80	13.35	9.82	10.29	10.94	11.41	12.95
	6H	10.70	11.10	11.83	12.24	13.78	10.30	10.71	11.43	11.84	13.38
	8H	10.83	11.21	11.96	12.34	13.89	10.43	10.81	11.57	11.94	13.50
	12H	10.89	11.23	12.03	12.37	13.93	10.48	10.83	11.63	11.97	13.53
8H	4H	10.39	10.77	11.52	11.90	13.45	10.04	10.42	11.17	11.54	13.10
	6H	10.98	11.30	12.14	12.47	14.02	10.63	10.95	11.78	12.12	13.67
	8H	11.19	11.46	12.35	12.61	14.18	10.83	11.11	11.99	12.25	13.83
	12H	11.30	11.54	12.46	12.68	14.29	10.93	11.17	12.09	12.31	13.92
12H	4H	10.36	10.71	11.51	11.85	13.41	10.02	10.37	11.17	11.50	13.06
	6H	11.01	11.28	12.17	12.43	14.00	10.67	10.94	11.82	12.09	13.66
	8H	11.22	11.47	12.39	12.61	14.22	10.88	11.12	12.04	12.27	13.87