

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902430

Luminaire Tested: DFN2DIP-HX2F0-020D050US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902430
REPORT IS A COMBINATION OF REPORTS P899181 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D050US830-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6037.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902430
CATALOG NUMBER: DFN2DIP-HX2F0-020D050US830-FLLFLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P902430
 CATALOG NUMBER: DFN2DIP-HX2F0-020D050US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	31
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	33	34	33	33	26
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27	30	29	27	22
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	27	25	23	27	25	23	18
4	71	60	53	47	63	55	48	43	44	39	35	33	30	28	24	22	20	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	21	19	17	14
6	60	48	40	35	54	44	37	32	35	30	26	27	23	21	19	17	15	19	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14	18	15	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	16	14	12	10
9	47	36	28	24	43	32	26	22	26	21	18	20	17	15	15	13	11	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1728	1728	1728
5°	1728	1700	1712
10°	1712	1673	1686
15°	1683	1641	1647
20°	1647	1599	1606
25°	1610	1549	1560
30°	1565	1502	1503
35°	1522	1448	1442
40°	1469	1393	1384
45°	1417	1338	1325
50°	1359	1279	1256
55°	1298	1212	1192
60°	1230	1133	1119
65°	1154	1050	1033
70°	1059	949	939
75°	928	828	849
80°	768	674	684
85°	520	423	424

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2001 cd/sqm



TEST NUMBER: P902430

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	1.1
10°-20°	194.2	3.2
20°-30°	285.5	4.7
30°-40°	331.5	5.5
40°-50°	331.1	5.5
50°-60°	288.7	4.8
60°-70°	213.4	3.5
70°-80°	120.8	2.0
80°-90°	36.1	0.6
90°-100°	92.2	1.5
100°-110°	293.0	4.9
110°-120°	501.5	8.3
120°-130°	659.5	10.9
130°-140°	740.3	12.3
140°-150°	725.9	12.0
150°-160°	609.0	10.1
160°-170°	403.9	6.7
170°-180°	141.2	2.3
0°-30°	548.7	9.1
0°-40°	880.3	14.6
0°-60°	1500.2	24.8
0°-90°	1870.5	31.0
90°-120°	886.7	14.7
90°-150°	3012.5	49.9
90°-180°	4167.0	69.0
0°-180°	6037.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	16	44	41	43	6
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	



TEST NUMBER: P902430

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3



TEST NUMBER: P902430

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4



TEST NUMBER: P902430
 CATALOG NUMBER: DFN2DIP-HX2F0-020D050US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.95	7.66	8.06	8.77	10.28	6.53	7.24	7.63	8.34	9.86
	3H	8.58	9.21	9.69	10.32	11.86	8.12	8.75	9.23	9.86	11.40
	4H	9.14	9.75	10.26	10.86	12.40	8.68	9.29	9.80	10.40	11.94
	6H	9.51	10.07	10.64	11.18	12.74	9.05	9.61	10.18	10.72	12.28
	8H	9.60	10.13	10.74	11.26	12.81	9.14	9.68	10.28	10.80	12.35
	12H	9.64	10.14	10.78	11.26	12.83	9.17	9.68	10.31	10.80	12.37
4H	2H	7.38	7.99	8.52	9.10	10.64	7.05	7.65	8.18	8.76	10.31
	3H	9.21	9.71	10.34	10.85	12.40	8.83	9.33	9.96	10.47	12.02
	4H	9.90	10.36	11.04	11.49	13.06	9.50	9.97	10.64	11.09	12.67
	6H	10.38	10.78	11.53	11.93	13.49	9.98	10.38	11.13	11.53	13.10
	8H	10.51	10.89	11.66	12.03	13.61	10.12	10.49	11.26	11.63	13.21
	12H	10.57	10.91	11.73	12.06	13.64	10.16	10.50	11.33	11.65	13.24
8H	4H	10.07	10.44	11.22	11.58	13.16	9.72	10.09	10.86	11.23	12.81
	6H	10.67	10.97	11.83	12.16	13.73	10.31	10.62	11.48	11.80	13.38
	8H	10.87	11.14	12.04	12.30	13.90	10.51	10.78	11.68	11.94	13.54
	12H	10.98	11.21	12.15	12.37	14.00	10.61	10.84	11.78	12.00	13.63
12H	4H	10.05	10.38	11.21	11.54	13.12	9.70	10.04	10.86	11.19	12.78
	6H	10.69	10.96	11.86	12.12	13.72	10.35	10.62	11.52	11.78	13.38
	8H	10.91	11.14	12.08	12.30	13.93	10.56	10.80	11.74	11.95	13.59