

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915904

Luminaire Tested: DFN2DIP-4P3F0-060D040US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915904
REPORT IS A COMBINATION OF REPORTS P899058 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-060D040US930-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7044.1 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 91.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915904
CATALOG NUMBER: DFN2DIP-4P3F0-060D040US930-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915904

CATALOG NUMBER: DFN2DIP-4P3F0-060D040US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51			51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44			44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38			38
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			29
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26			26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19			19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2304	2304	2304
5°	2306	2266	2281
10°	2282	2220	2206
15°	2249	2145	2091
20°	2206	2043	1949
25°	2162	1928	1813
30°	2103	1810	1640
35°	2046	1684	1488
40°	1987	1554	1314
45°	1919	1410	1156
50°	1849	1264	1003
55°	1775	1109	855
60°	1690	946	703
65°	1591	781	632
70°	1472	627	570
75°	1322	550	517
80°	1104	456	447
85°	749	297	331

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1919 cd/sqm



TEST NUMBER: P915904

CATALOG NUMBER: DFN2DIP-4P3F0-060D040US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.7
10°-20°	520.2	7.4
20°-30°	730.3	10.4
30°-40°	796.1	11.3
40°-50°	731.7	10.4
50°-60°	574.6	8.2
60°-70°	374.0	5.3
70°-80°	192.5	2.7
80°-90°	52.1	0.7
90°-100°	63.8	0.9
100°-110°	202.8	2.9
110°-120°	347.0	4.9
120°-130°	456.4	6.5
130°-140°	512.3	7.3
140°-150°	502.4	7.1
150°-160°	421.4	6.0
160°-170°	279.5	4.0
170°-180°	97.7	1.4
0°-30°	1439.9	20.4
0°-40°	2236.0	31.7
0°-60°	3542.3	50.3
0°-90°	4160.9	59.1
90°-120°	613.6	8.7
90°-150°	2084.7	29.6
90°-180°	2883.0	40.9
0°-180°	7044.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	1	11	30	29	30	7
95°	45	54	56	56	54	51
105°	187	190	192	193	193	198
115°	348	353	352	351	348	344
125°	506	514	512	509	508	453
135°	655	665	667	666	663	506
145°	795	802	807	808	804	497
155°	910	912	915	919	916	419
165°	989	988	988	995	990	279
175°	1030	1027	1025	1031	1026	98
180°	1031	1031	1031	1031	1031	



TEST NUMBER: P915904

CATALOG NUMBER: DFN2DIP-4P3F0-060D040US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	0.9	11.2	30.5	28.6	29.5
92.5°	19.2	26.1	27.1	28.0	28.0
95°	45.4	54.1	55.7	55.7	54.1
97.5°	75.6	83.6	87.1	87.1	87.1
100°	110.4	117.6	120.0	120.0	119.1
102.5°	147.1	152.4	155.8	156.7	155.8
105°	187.2	189.6	191.5	193.1	193.1
107.5°	227.0	230.7	230.7	231.3	227.0
110°	265.5	270.5	270.5	270.5	268.1



TEST NUMBER: P915904

CATALOG NUMBER: DFN2DIP-4P3F0-060D040US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	307.2	312.5	311.5	309.1	307.2
115°	348.2	353.3	351.6	350.7	348.2
117.5°	389.0	395.8	391.5	389.0	386.5
120°	430.1	436.8	430.1	430.1	427.2
122.5°	467.3	476.1	471.7	469.2	467.3
125°	506.5	514.3	511.8	509.0	508.1
127.5°	544.8	554.4	551.0	547.2	544.8
130°	580.5	591.7	590.2	588.3	584.9
132.5°	620.6	629.3	630.0	625.6	623.1
135°	655.2	664.8	666.7	665.7	663.2
137.5°	693.7	701.5	703.0	702.4	698.7
140°	727.6	735.4	739.7	739.7	736.3
142.5°	762.5	770.2	772.7	773.6	770.2
145°	795.4	801.6	806.6	807.6	804.1
147.5°	824.9	832.7	836.4	838.0	834.5
150°	855.4	860.7	864.1	866.9	864.1
152.5°	882.5	887.7	892.1	895.5	892.1
155°	909.5	912.0	914.8	919.2	916.3
157.5°	932.9	934.7	936.2	942.5	938.1
160°	953.7	955.5	956.4	961.7	958.0
162.5°	972.9	972.9	973.9	979.7	975.4
165°	989.4	988.5	988.5	994.7	990.3
167.5°	1004.4	1001.5	1001.5	1007.8	1003.4
170°	1015.5	1013.0	1012.1	1018.3	1013.0
172.5°	1023.3	1020.8	1019.9	1026.1	1020.8
175°	1029.6	1027.0	1025.2	1031.4	1026.1
177.5°	1033.0	1030.5	1028.6	1033.9	1028.6
180°	1031.4	1031.4	1031.4	1031.4	1031.4



TEST NUMBER: P915904
 CATALOG NUMBER: DFN2DIP-4P3F0-060D040US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.82	11.73	11.70	12.63	13.77	6.78	7.69	7.66	8.59	9.73
	3H	12.50	13.31	13.39	14.22	15.38	7.97	8.78	8.86	9.69	10.85
	4H	13.11	13.88	14.02	14.79	15.96	8.42	9.19	9.33	10.10	11.27
	6H	13.53	14.24	14.45	15.16	16.34	8.74	9.45	9.66	10.37	11.55
	8H	13.66	14.33	14.59	15.27	16.45	8.83	9.50	9.76	10.44	11.62
	12H	13.72	14.36	14.65	15.29	16.50	8.87	9.51	9.81	10.44	11.65
4H	2H	10.85	11.61	11.76	12.53	13.70	7.38	8.15	8.30	9.07	10.24
	3H	12.68	13.31	13.60	14.26	15.45	8.73	9.37	9.66	10.32	11.50
	4H	13.37	13.95	14.30	14.89	16.10	9.28	9.86	10.22	10.80	12.01
	6H	13.88	14.38	14.83	15.35	16.56	9.70	10.20	10.65	11.16	12.37
	8H	14.06	14.53	15.01	15.48	16.71	9.82	10.29	10.77	11.25	12.48
	12H	14.15	14.57	15.12	15.55	16.78	9.89	10.31	10.86	11.28	12.52
8H	4H	13.34	13.81	14.29	14.76	15.99	9.56	10.03	10.51	10.99	12.21
	6H	13.90	14.29	14.88	15.29	16.52	10.08	10.46	11.05	11.46	12.69
	8H	14.12	14.46	15.10	15.45	16.69	10.26	10.60	11.25	11.59	12.84
	12H	14.26	14.56	15.25	15.54	16.83	10.38	10.68	11.37	11.66	12.95
12H	4H	13.30	13.72	14.27	14.69	15.92	9.57	9.99	10.54	10.97	12.20
	6H	13.88	14.22	14.87	15.21	16.45	10.12	10.46	11.11	11.45	12.70
	8H	14.10	14.40	15.09	15.38	16.67	10.33	10.63	11.32	11.61	12.91