

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918549

Luminaire Tested: DFN2DIP-4P3F0-020D030US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918549
REPORT IS A COMBINATION OF REPORTS P900560 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US935-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4020.9 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918549

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918549

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	811	811	811
5°	812	798	803
10°	803	781	777
15°	792	755	736
20°	777	719	686
25°	761	679	638
30°	740	637	577
35°	720	593	524
40°	699	547	463
45°	676	496	407
50°	651	445	353
55°	625	390	301
60°	595	333	247
65°	560	275	223
70°	518	221	201
75°	465	194	182
80°	389	161	157
85°	263	105	116

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 676 cd/sqm

TEST NUMBER: P918549

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.7
10°-20°	183.1	4.6
20°-30°	257.1	6.4
30°-40°	280.2	7.0
40°-50°	257.6	6.4
50°-60°	202.3	5.0
60°-70°	131.7	3.3
70°-80°	67.8	1.7
80°-90°	18.8	0.5
90°-100°	28.7	0.7
100°-110°	107.2	2.7
110°-120°	284.2	7.1
120°-130°	471.3	11.7
130°-140°	500.7	12.5
140°-150°	465.3	11.6
150°-160°	374.1	9.3
160°-170°	241.1	6.0
170°-180°	83.0	2.1
0°-30°	506.9	12.6
0°-40°	787.1	19.6
0°-60°	1247.0	31.0
0°-90°	1465.2	36.4
90°-120°	420.1	10.4
90°-150°	1857.5	46.2
90°-180°	2556.0	63.6
0°-180°	4020.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	1	8	13	16	17	4
95°	41	20	24	28	27	49
105°	192	211	38	45	48	205
115°	363	373	389	97	52	357
125°	513	521	533	537	539	457
135°	635	645	650	657	655	490
145°	736	736	746	751	747	460
155°	810	805	812	816	811	373
165°	854	850	852	857	852	241
175°	874	869	870	875	869	83
180°	872	872	872	872	872	

TEST NUMBER: P918549

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	0.6	7.6	12.6	15.8	17.0
92.5°	15.8	13.3	15.2	16.4	17.0
95°	41.0	20.1	24.5	27.8	27.1
97.5°	73.8	22.1	32.1	34.1	34.7
100°	111.7	25.2	36.0	41.0	42.3
102.5°	153.3	152.1	37.2	44.1	46.1
105°	191.7	210.7	38.5	45.4	48.0
107.5°	236.5	252.3	39.8	46.7	49.2
110°	279.5	292.7	110.4	47.4	49.9

TEST NUMBER: P918549

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	319.9	331.1	320.5	48.6	50.5
115°	362.7	373.4	389.2	97.1	51.7
117.5°	399.9	412.5	423.3	333.0	167.8
120°	441.5	451.0	462.4	469.9	384.8
122.5°	476.8	487.0	499.6	503.3	504.0
125°	512.8	521.0	533.0	537.4	539.3
127.5°	545.6	554.4	564.0	570.2	570.8
130°	576.5	586.7	593.6	600.5	599.9
132.5°	608.0	616.3	623.2	628.9	628.3
135°	634.6	644.7	650.3	656.7	655.4
137.5°	662.3	669.9	676.2	682.5	680.6
140°	689.4	694.5	701.4	707.1	704.0
142.5°	712.2	716.6	724.8	729.8	726.7
145°	736.2	735.5	746.2	750.6	747.4
147.5°	756.9	755.0	765.8	768.9	766.4
150°	777.1	772.7	782.8	786.5	783.4
152.5°	794.1	789.1	798.6	802.4	798.0
155°	810.5	804.9	812.4	816.2	811.2
157.5°	823.8	818.8	824.5	828.9	823.8
160°	835.2	831.4	835.2	839.0	834.5
162.5°	845.2	841.5	844.6	849.0	843.3
165°	854.0	850.3	852.2	856.6	852.2
167.5°	861.0	857.2	859.1	863.6	857.9
170°	866.7	862.9	864.2	868.6	862.9
172.5°	870.5	866.7	868.0	872.4	866.7
175°	873.6	869.2	870.5	874.9	868.6
177.5°	874.9	870.5	871.2	875.5	869.9
180°	871.8	871.8	871.8	871.8	871.8

TEST NUMBER: P918549

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.97	5.70	6.04	6.77	8.23	0.93	1.66	2.00	2.73	4.19
	3H	6.64	7.29	7.72	8.37	9.84	2.11	2.76	3.19	3.84	5.31
	4H	7.24	7.86	8.33	8.94	10.41	2.55	3.17	3.64	4.25	5.73
	6H	7.65	8.22	8.75	9.30	10.79	2.86	3.43	3.96	4.51	6.00
	8H	7.77	8.31	8.88	9.41	10.90	2.94	3.48	4.05	4.58	6.07
	12H	7.83	8.34	8.94	9.43	10.94	2.98	3.49	4.09	4.59	6.09
4H	2H	4.98	5.59	6.07	6.67	8.15	1.51	2.13	2.61	3.21	4.69
	3H	6.79	7.30	7.89	8.41	9.90	2.85	3.36	3.95	4.47	5.96
	4H	7.47	7.95	8.58	9.04	10.56	3.39	3.86	4.50	4.95	6.47
	6H	7.98	8.38	9.10	9.50	11.01	3.79	4.20	4.91	5.32	6.82
	8H	8.15	8.53	9.27	9.64	11.16	3.92	4.29	5.03	5.40	6.93
	12H	8.24	8.58	9.37	9.70	11.23	3.97	4.31	5.11	5.44	6.96
8H	4H	7.43	7.81	8.55	8.92	10.44	3.66	4.03	4.77	5.14	6.67
	6H	7.99	8.30	9.13	9.46	10.97	4.16	4.47	5.30	5.63	7.14
	8H	8.20	8.48	9.35	9.61	11.15	4.35	4.62	5.49	5.75	7.29
	12H	8.33	8.57	9.48	9.70	11.28	4.46	4.70	5.60	5.83	7.40
12H	4H	7.38	7.72	8.51	8.85	10.37	3.66	4.00	4.79	5.12	6.65
	6H	7.97	8.24	9.11	9.37	10.91	4.21	4.48	5.35	5.62	7.15
	8H	8.18	8.42	9.32	9.55	11.12	4.41	4.65	5.56	5.78	7.35