

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902448

Luminaire Tested: DFN2DIP-HX2F0-030D040US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902448
REPORT IS A COMBINATION OF REPORTS P899174 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-030D040US830-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5740.1 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902448

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902448

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2754	2754	2754
5°	2754	2703	2722
10°	2722	2644	2629
15°	2680	2550	2487
20°	2626	2424	2315
25°	2571	2283	2149
30°	2498	2139	1941
35°	2427	1986	1757
40°	2354	1827	1548
45°	2270	1653	1359
50°	2182	1477	1174
55°	2090	1290	997
60°	1983	1095	816
65°	1861	898	729
70°	1711	714	652
75°	1523	617	584
80°	1255	500	492
85°	819	309	345

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2270 cd/sqm

TEST NUMBER: P902448

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	1.9
10°-20°	300.7	5.2
20°-30°	422.1	7.4
30°-40°	460.2	8.0
40°-50°	422.9	7.4
50°-60°	332.2	5.8
60°-70°	216.2	3.8
70°-80°	111.3	1.9
80°-90°	31.8	0.6
90°-100°	73.8	1.3
100°-110°	234.4	4.1
110°-120°	401.2	7.0
120°-130°	527.6	9.2
130°-140°	592.2	10.3
140°-150°	580.8	10.1
150°-160°	487.2	8.5
160°-170°	323.1	5.6
170°-180°	112.9	2.0
0°-30°	832.3	14.5
0°-40°	1292.5	22.5
0°-60°	2047.6	35.7
0°-90°	2406.9	41.9
90°-120°	709.4	12.4
90°-150°	2410.0	42.0
90°-180°	3333.0	58.1
0°-180°	5740.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	1	13	35	33	34	6
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	403	408	406	406	403	398
125°	586	595	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	

TEST NUMBER: P902448

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	1.0	12.9	35.3	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.2	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9

TEST NUMBER: P902448

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.6	408.4	406.5	405.5	402.6
117.5°	449.7	457.6	452.6	449.7	446.9
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.3	550.4	545.4	542.4	540.3
125°	585.6	594.6	591.7	588.4	587.4
127.5°	629.8	640.9	637.0	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.2
132.5°	717.5	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.8
137.5°	802.0	811.0	812.8	812.0	807.8
140°	841.1	850.2	855.2	855.2	851.2
142.5°	881.5	890.4	893.2	894.4	890.4
145°	919.5	926.7	932.5	933.6	929.6
147.5°	953.7	962.6	967.0	968.7	964.8
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.3	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.5	1080.5	1082.3	1089.6	1084.5
160°	1102.5	1104.7	1105.7	1111.8	1107.5
162.5°	1124.7	1124.7	1125.9	1132.7	1127.7
165°	1143.9	1142.7	1142.7	1149.9	1144.9
167.5°	1161.1	1157.8	1157.8	1165.1	1160.0
170°	1174.0	1171.1	1170.1	1177.2	1171.1
172.5°	1183.0	1180.2	1179.0	1186.3	1180.2
175°	1190.2	1187.3	1185.2	1192.3	1186.3
177.5°	1194.2	1191.3	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3

TEST NUMBER: P902448

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.72	10.49	10.75	11.53	12.91	5.71	6.48	6.74	7.51	8.89
	3H	11.37	12.06	12.41	13.10	14.51	6.87	7.56	7.91	8.60	10.01
	4H	11.96	12.61	13.01	13.66	15.07	7.31	7.96	8.36	9.00	10.42
	6H	12.36	12.96	13.42	14.01	15.43	7.61	8.21	8.67	9.26	10.68
	8H	12.47	13.04	13.54	14.11	15.52	7.69	8.26	8.76	9.33	10.75
	12H	12.52	13.06	13.59	14.12	15.56	7.73	8.27	8.80	9.33	10.77
4H	2H	9.73	10.38	10.79	11.43	12.84	6.28	6.93	7.34	7.98	9.39
	3H	11.53	12.07	12.59	13.14	14.56	7.61	8.15	8.67	9.22	10.64
	4H	12.20	12.69	13.27	13.75	15.20	8.14	8.63	9.21	9.69	11.14
	6H	12.68	13.11	13.76	14.20	15.64	8.53	8.96	9.61	10.05	11.49
	8H	12.84	13.24	13.92	14.32	15.78	8.65	9.05	9.73	10.13	11.58
	12H	12.92	13.28	14.02	14.37	15.83	8.71	9.06	9.80	10.16	11.62
8H	4H	12.16	12.55	13.24	13.63	15.09	8.40	8.79	9.48	9.87	11.33
	6H	12.69	13.02	13.79	14.14	15.59	8.89	9.22	9.99	10.34	11.79
	8H	12.89	13.18	14.00	14.28	15.75	9.07	9.35	10.18	10.46	11.93
	12H	13.01	13.26	14.12	14.36	15.87	9.17	9.42	10.28	10.52	12.03
12H	4H	12.10	12.46	13.20	13.55	15.01	8.40	8.75	9.49	9.85	11.31
	6H	12.67	12.95	13.78	14.06	15.53	8.93	9.22	10.04	10.32	11.80
	8H	12.87	13.12	13.98	14.22	15.73	9.13	9.38	10.24	10.48	11.99