

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918554

Luminaire Tested: DFN2DIP-4P3F0-020D050US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918554
REPORT IS A COMBINATION OF REPORTS P899059 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D050US935-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5514.7 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918554

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918554

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	33
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	27	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	764	764	764
5°	764	752	758
10°	758	742	747
15°	746	729	731
20°	731	712	714
25°	715	691	695
30°	696	671	671
35°	678	649	645
40°	655	626	620
45°	633	603	595
50°	608	578	566
55°	582	550	539
60°	553	517	509
65°	521	483	473
70°	481	440	434
75°	425	390	397
80°	357	325	328
85°	251	215	215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1366 cd/sqm

TEST NUMBER: P918554

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.1
10°-20°	177.4	3.2
20°-30°	260.8	4.7
30°-40°	302.9	5.5
40°-50°	302.5	5.5
50°-60°	263.8	4.8
60°-70°	195.0	3.5
70°-80°	110.3	2.0
80°-90°	33.0	0.6
90°-100°	84.2	1.5
100°-110°	267.7	4.9
110°-120°	458.1	8.3
120°-130°	602.5	10.9
130°-140°	676.3	12.3
140°-150°	663.1	12.0
150°-160°	556.3	10.1
160°-170°	368.9	6.7
170°-180°	128.9	2.3
0°-30°	501.3	9.1
0°-40°	804.1	14.6
0°-60°	1370.4	24.8
0°-90°	1708.6	31.0
90°-120°	810.0	14.7
90°-150°	2751.9	49.9
90°-180°	3806.0	69.0
0°-180°	5514.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	670	670	670	670	670	
5°	670	668	660	666	664	64
15°	638	634	626	628	625	180
25°	577	572	561	562	561	266
35°	498	492	481	477	474	311
45°	405	401	391	384	381	313
55°	307	303	295	287	284	274
65°	207	203	197	191	188	205
75°	108	107	104	100	101	116
85°	26	26	25	23	23	29
90°	1	15	40	38	39	5
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P918554

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	670.0	670.0	670.0	670.0	670.0
2.5°	673.9	670.7	663.6	670.0	668.8
5°	670.0	667.5	660.4	665.6	664.3
7.5°	665.6	661.7	654.6	659.8	658.5
10°	658.5	654.0	646.3	651.3	649.5
12.5°	648.8	645.0	637.2	640.4	639.1
15°	637.8	634.0	625.6	628.2	625.0
17.5°	624.3	620.5	612.1	615.3	612.1
20°	609.5	605.6	596.6	598.6	596.0
22.5°	594.7	588.9	580.5	580.5	579.2
25°	577.3	572.1	561.2	562.4	561.2
27.5°	557.9	553.4	545.1	543.2	539.9
30°	538.6	533.5	523.8	521.9	519.3
32.5°	518.0	514.2	503.9	500.0	497.4
35°	498.1	491.6	481.3	477.4	474.2
37.5°	475.5	469.7	459.3	454.9	451.6
40°	452.3	447.1	436.8	431.1	428.4
42.5°	429.7	424.6	414.3	407.9	404.0
45°	405.3	400.8	391.1	384.0	381.4
47.5°	381.4	376.9	366.6	359.5	355.7
50°	356.3	353.1	344.1	335.0	331.8
52.5°	331.8	327.3	318.9	311.9	307.4
55°	306.7	302.8	295.1	287.4	284.1
57.5°	281.5	278.4	269.9	262.3	259.6
60°	256.4	253.9	244.9	237.7	235.8
62.5°	232.0	227.4	221.0	214.6	212.0
65°	206.8	202.9	196.6	190.7	187.5
67.5°	181.1	177.8	172.0	167.6	165.0
70°	157.2	154.6	148.8	144.3	141.8
72.5°	132.8	130.2	126.9	122.4	120.5
75°	108.2	107.0	103.7	99.9	101.2
77.5°	86.4	83.8	82.4	80.5	78.6
80°	64.5	63.8	62.5	60.5	59.2
82.5°	43.8	43.8	43.2	40.6	40.6
85°	26.3	25.7	25.1	23.2	22.6
87.5°	11.6	10.3	9.0	7.1	6.5
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8

TEST NUMBER: P918554

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5

TEST NUMBER: P918554

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US935-FLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.22	4.93	5.32	6.03	7.55	3.77	4.49	4.88	5.59	7.11
	3H	5.86	6.50	6.98	7.61	9.15	5.37	6.01	6.49	7.12	8.66
	4H	6.44	7.05	7.56	8.16	9.70	5.95	6.55	7.07	7.66	9.20
	6H	6.83	7.39	7.96	8.50	10.05	6.33	6.89	7.46	8.00	9.55
	8H	6.93	7.46	8.06	8.59	10.13	6.43	6.96	7.56	8.08	9.63
	12H	6.97	7.47	8.11	8.60	10.16	6.46	6.96	7.60	8.09	9.66
4H	2H	4.66	5.26	5.79	6.37	7.92	4.30	4.91	5.43	6.02	7.56
	3H	6.50	7.01	7.64	8.15	9.70	6.10	6.60	7.23	7.74	9.29
	4H	7.21	7.67	8.35	8.80	10.37	6.78	7.25	7.92	8.38	9.95
	6H	7.71	8.11	8.86	9.26	10.82	7.28	7.68	8.42	8.83	10.39
	8H	7.85	8.23	9.00	9.37	10.95	7.42	7.79	8.56	8.93	10.51
	12H	7.92	8.26	9.08	9.41	10.99	7.47	7.81	8.63	8.96	10.54
8H	4H	7.39	7.76	8.53	8.90	10.48	7.01	7.38	8.16	8.52	10.11
	6H	8.01	8.31	9.17	9.50	11.08	7.62	7.93	8.79	9.11	10.69
	8H	8.22	8.49	9.40	9.65	11.25	7.83	8.10	9.00	9.26	10.86
	12H	8.34	8.58	9.52	9.74	11.37	7.93	8.17	9.11	9.33	10.96
12H	4H	7.37	7.70	8.53	8.85	10.44	7.00	7.34	8.16	8.49	10.07
	6H	8.03	8.30	9.21	9.46	11.06	7.66	7.93	8.83	9.09	10.69
	8H	8.26	8.50	9.44	9.66	11.29	7.88	8.12	9.06	9.28	10.91

END OF REPORT