

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902496

Luminaire Tested: DFN2DIP-HX2F0-050D060US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902496
REPORT IS A COMBINATION OF REPORTS P899198 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D060US830-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9010.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 95.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902496
CATALOG NUMBER: DFN2DIP-HX2F0-050D060US830-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P902496

CATALOG NUMBER: DFN2DIP-HX2F0-050D060US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				33
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33	28				28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28	25				25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22				22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22	19				19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17				17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				16
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14				14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4589	4589	4589
5°	4589	4505	4537
10°	4536	4406	4381
15°	4467	4250	4145
20°	4377	4039	3858
25°	4285	3805	3582
30°	4164	3565	3234
35°	4044	3309	2929
40°	3923	3045	2580
45°	3782	2754	2265
50°	3637	2461	1957
55°	3483	2149	1662
60°	3306	1825	1360
65°	3101	1497	1215
70°	2852	1191	1088
75°	2540	1029	973
80°	2090	833	819
85°	1368	515	575

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3782 cd/sqm



TEST NUMBER: P902496

CATALOG NUMBER: DFN2DIP-HX2F0-050D060US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	2.0
10°-20°	501.1	5.6
20°-30°	703.6	7.8
30°-40°	766.9	8.5
40°-50°	704.9	7.8
50°-60°	553.6	6.1
60°-70°	360.3	4.0
70°-80°	185.5	2.1
80°-90°	52.4	0.6
90°-100°	110.7	1.2
100°-110°	351.6	3.9
110°-120°	601.8	6.7
120°-130°	791.4	8.8
130°-140°	888.4	9.9
140°-150°	871.1	9.7
150°-160°	730.8	8.1
160°-170°	484.6	5.4
170°-180°	169.4	1.9
0°-30°	1387.2	15.4
0°-40°	2154.2	23.9
0°-60°	3412.7	37.9
0°-90°	4010.9	44.5
90°-120°	1064.1	11.8
90°-150°	3615.0	40.1
90°-180°	5000.0	55.5
0°-180°	9010.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1853	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1185	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	19	53	50	51	9
95°	79	94	96	96	94	88
105°	325	329	332	335	335	343
115°	604	613	610	608	604	597
125°	878	892	888	883	881	785
135°	1136	1153	1156	1154	1150	878
145°	1379	1390	1399	1400	1394	862
155°	1577	1582	1586	1594	1589	726
165°	1716	1714	1714	1725	1717	484
175°	1785	1781	1778	1789	1779	170
180°	1789	1789	1789	1789	1789	



TEST NUMBER: P902496

CATALOG NUMBER: DFN2DIP-HX2F0-050D060US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.8	1947.8	1947.8	1947.8	1947.8
2.5°	1956.5	1947.8	1928.3	1946.1	1942.5
5°	1947.8	1939.0	1916.0	1931.8	1926.7
7.5°	1931.8	1921.4	1896.7	1903.7	1894.8
10°	1910.7	1898.4	1863.2	1857.8	1847.3
12.5°	1884.3	1868.5	1820.8	1810.3	1790.8
15°	1852.6	1833.2	1773.3	1739.8	1722.2
17.5°	1815.5	1787.3	1713.3	1674.5	1646.2
20°	1773.3	1738.0	1649.8	1605.9	1567.0
22.5°	1727.5	1686.9	1584.6	1524.8	1498.4
25°	1681.6	1625.1	1508.8	1436.6	1410.0
27.5°	1627.0	1567.0	1438.3	1355.5	1314.9
30°	1568.9	1501.8	1360.7	1270.9	1223.2
32.5°	1512.4	1431.3	1286.9	1181.0	1136.9
35°	1449.0	1359.1	1204.0	1092.9	1054.0
37.5°	1387.2	1290.2	1126.4	1004.7	960.7
40°	1322.0	1216.4	1045.2	920.1	874.3
42.5°	1255.1	1142.3	964.2	833.7	789.8
45°	1184.6	1066.4	881.4	756.1	713.8
47.5°	1117.6	992.5	802.1	676.8	638.1
50°	1043.6	918.4	724.5	602.8	565.9
52.5°	971.2	839.0	650.4	534.1	500.7
55°	900.7	763.2	572.8	467.1	433.7
57.5°	828.5	687.5	504.2	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.9	241.5
67.5°	537.6	394.8	246.9	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.4
75°	324.3	200.9	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	1.6	19.4	52.9	49.6	51.2
92.5°	33.5	45.3	46.9	48.5	48.5
95°	78.7	93.8	96.5	96.5	93.8
97.5°	131.0	145.1	151.0	151.0	151.0
100°	191.4	203.8	208.1	208.1	206.5
102.5°	255.1	264.2	270.1	271.7	270.1
105°	324.6	328.9	332.2	334.9	334.9
107.5°	393.6	400.1	400.1	401.1	393.6
110°	460.5	469.1	469.1	469.1	464.8



TEST NUMBER: P902496

CATALOG NUMBER: DFN2DIP-HX2F0-050D060US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	532.7	541.9	540.3	535.9	532.7
115°	603.9	612.6	609.8	608.2	603.9
117.5°	674.6	686.5	678.8	674.6	670.2
120°	745.7	757.6	745.7	745.7	740.8
122.5°	810.4	825.5	817.9	813.7	810.4
125°	878.4	891.8	887.5	882.7	881.1
127.5°	944.7	961.4	955.5	949.0	944.7
130°	1006.7	1026.1	1023.4	1020.2	1014.3
132.5°	1076.3	1091.4	1092.4	1084.9	1080.5
135°	1136.1	1152.8	1156.0	1154.4	1150.1
137.5°	1203.0	1216.4	1219.2	1218.0	1211.6
140°	1261.8	1275.3	1282.8	1282.8	1276.9
142.5°	1322.1	1335.6	1339.9	1341.5	1335.6
145°	1379.3	1390.1	1398.7	1400.3	1394.4
147.5°	1430.5	1444.0	1450.5	1453.1	1447.2
150°	1483.4	1492.5	1498.5	1503.3	1498.5
152.5°	1530.2	1539.5	1547.0	1552.9	1547.0
155°	1577.2	1581.5	1586.3	1593.9	1589.0
157.5°	1617.6	1620.9	1623.5	1634.4	1626.8
160°	1653.8	1657.0	1658.6	1667.7	1661.3
162.5°	1687.2	1687.2	1688.8	1699.0	1691.5
165°	1715.7	1714.1	1714.1	1724.9	1717.4
167.5°	1741.6	1736.8	1736.8	1747.6	1740.0
170°	1761.0	1756.7	1755.1	1765.9	1756.7
172.5°	1774.5	1770.2	1768.6	1779.3	1770.2
175°	1785.3	1781.0	1777.7	1788.6	1779.3
177.5°	1791.2	1787.0	1783.7	1792.8	1783.7
180°	1788.6	1788.6	1788.6	1788.6	1788.6



TEST NUMBER: P902496
 CATALOG NUMBER: DFN2DIP-HX2F0-050D060US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.77	12.56	12.78	13.57	14.92	7.75	8.54	8.76	9.55	10.90
	3H	13.42	14.12	14.44	15.14	16.51	8.92	9.62	9.94	10.65	12.02
	4H	14.01	14.67	15.04	15.70	17.08	9.36	10.02	10.39	11.05	12.43
	6H	14.40	15.02	15.45	16.05	17.44	9.66	10.27	10.70	11.30	12.69
	8H	14.52	15.10	15.57	16.15	17.53	9.74	10.32	10.79	11.37	12.76
	12H	14.57	15.12	15.62	16.16	17.57	9.78	10.33	10.83	11.37	12.78
4H	2H	11.78	12.44	12.81	13.47	14.85	8.33	8.99	9.36	10.02	11.40
	3H	13.57	14.13	14.62	15.18	16.57	9.65	10.21	10.70	11.26	12.65
	4H	14.24	14.75	15.30	15.80	17.21	10.18	10.69	11.24	11.74	13.15
	6H	14.73	15.17	15.80	16.24	17.65	10.58	11.02	11.65	12.09	13.50
	8H	14.89	15.30	15.96	16.36	17.79	10.70	11.11	11.76	12.17	13.59
	12H	14.97	15.34	16.05	16.42	17.84	10.75	11.12	11.83	12.20	13.63
8H	4H	14.20	14.61	15.27	15.67	17.10	10.45	10.85	11.51	11.91	13.34
	6H	14.74	15.08	15.83	16.18	17.60	10.94	11.27	12.03	12.38	13.80
	8H	14.94	15.24	16.03	16.32	17.76	11.12	11.41	12.21	12.50	13.94
	12H	15.06	15.32	16.16	16.40	17.88	11.22	11.48	12.32	12.56	14.04
12H	4H	14.15	14.52	15.23	15.60	17.03	10.45	10.81	11.53	11.89	13.32
	6H	14.72	15.01	15.81	16.10	17.54	10.98	11.28	12.07	12.36	13.80
	8H	14.92	15.18	16.01	16.26	17.74	11.18	11.43	12.27	12.52	14.00