

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918587

Luminaire Tested: DFN2DIP-4P3F0-040D030US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918587
REPORT IS A COMBINATION OF REPORTS P900563 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D030US935-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5966.7 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918587

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918587

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53
2	91	83	77	72	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	40	38
4	76	65	57	50	70	61	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	24	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1527	1527	1527
5°	1529	1505	1516
10°	1515	1484	1494
15°	1492	1458	1462
20°	1461	1423	1429
25°	1430	1382	1390
30°	1391	1343	1341
35°	1355	1297	1290
40°	1310	1251	1241
45°	1265	1205	1191
50°	1216	1157	1133
55°	1165	1100	1079
60°	1106	1034	1018
65°	1043	965	945
70°	962	880	867
75°	850	779	794
80°	714	650	657
85°	503	431	430

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1265 cd/sqm

TEST NUMBER: P918587

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	2.1
10°-20°	354.9	5.9
20°-30°	521.5	8.7
30°-40°	605.7	10.2
40°-50°	605.0	10.1
50°-60°	527.5	8.8
60°-70°	389.9	6.5
70°-80°	220.6	3.7
80°-90°	59.8	1.0
90°-100°	28.7	0.5
100°-110°	107.2	1.8
110°-120°	284.2	4.8
120°-130°	471.3	7.9
130°-140°	500.7	8.4
140°-150°	465.3	7.8
150°-160°	374.1	6.3
160°-170°	241.1	4.0
170°-180°	83.0	1.4
0°-30°	1002.5	16.8
0°-40°	1608.3	27.0
0°-60°	2740.7	45.9
0°-90°	3411.1	57.2
90°-120°	420.1	7.0
90°-150°	1857.5	31.1
90°-180°	2556.0	42.8
0°-180°	5966.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	1	8	13	16	17	6
95°	41	20	24	28	27	49
105°	192	211	38	45	48	205
115°	363	373	389	97	52	357
125°	513	521	533	537	539	457
135°	635	645	650	657	655	490
145°	736	736	746	751	747	460
155°	810	805	812	816	811	373
165°	854	850	852	857	852	241
175°	874	869	870	875	869	83
180°	872	872	872	872	872	

TEST NUMBER: P918587

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	0.6	7.6	12.6	15.8	17.0
92.5°	15.8	13.3	15.2	16.4	17.0
95°	41.0	20.1	24.5	27.8	27.1
97.5°	73.8	22.1	32.1	34.1	34.7
100°	111.7	25.2	36.0	41.0	42.3
102.5°	153.3	152.1	37.2	44.1	46.1
105°	191.7	210.7	38.5	45.4	48.0
107.5°	236.5	252.3	39.8	46.7	49.2
110°	279.5	292.7	110.4	47.4	49.9

TEST NUMBER: P918587

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	319.9	331.1	320.5	48.6	50.5
115°	362.7	373.4	389.2	97.1	51.7
117.5°	399.9	412.5	423.3	333.0	167.8
120°	441.5	451.0	462.4	469.9	384.8
122.5°	476.8	487.0	499.6	503.3	504.0
125°	512.8	521.0	533.0	537.4	539.3
127.5°	545.6	554.4	564.0	570.2	570.8
130°	576.5	586.7	593.6	600.5	599.9
132.5°	608.0	616.3	623.2	628.9	628.3
135°	634.6	644.7	650.3	656.7	655.4
137.5°	662.3	669.9	676.2	682.5	680.6
140°	689.4	694.5	701.4	707.1	704.0
142.5°	712.2	716.6	724.8	729.8	726.7
145°	736.2	735.5	746.2	750.6	747.4
147.5°	756.9	755.0	765.8	768.9	766.4
150°	777.1	772.7	782.8	786.5	783.4
152.5°	794.1	789.1	798.6	802.4	798.0
155°	810.5	804.9	812.4	816.2	811.2
157.5°	823.8	818.8	824.5	828.9	823.8
160°	835.2	831.4	835.2	839.0	834.5
162.5°	845.2	841.5	844.6	849.0	843.3
165°	854.0	850.3	852.2	856.6	852.2
167.5°	861.0	857.2	859.1	863.6	857.9
170°	866.7	862.9	864.2	868.6	862.9
172.5°	870.5	866.7	868.0	872.4	866.7
175°	873.6	869.2	870.5	874.9	868.6
177.5°	874.9	870.5	871.2	875.5	869.9
180°	871.8	871.8	871.8	871.8	871.8

TEST NUMBER: P918587

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US935-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.35	10.28	10.24	11.19	12.35	8.90	9.83	9.79	10.74	11.91
	3H	11.01	11.84	11.91	12.76	13.95	10.52	11.35	11.42	12.27	13.46
	4H	11.60	12.38	12.52	13.31	14.51	11.10	11.89	12.02	12.82	14.02
	6H	12.00	12.72	12.93	13.66	14.87	11.49	12.22	12.43	13.16	14.37
	8H	12.10	12.79	13.04	13.74	14.95	11.60	12.29	12.54	13.24	14.45
	12H	12.15	12.81	13.09	13.75	14.99	11.64	12.30	12.58	13.24	14.48
4H	2H	9.81	10.60	10.74	11.53	12.73	9.46	10.25	10.38	11.17	12.37
	3H	11.68	12.34	12.61	13.30	14.51	11.27	11.93	12.21	12.89	14.10
	4H	12.39	12.99	13.34	13.95	15.19	11.97	12.57	12.91	13.52	14.76
	6H	12.91	13.43	13.87	14.40	15.64	12.47	12.99	13.43	13.97	15.21
	8H	13.06	13.54	14.02	14.51	15.76	12.62	13.10	13.58	14.07	15.33
	12H	13.13	13.57	14.11	14.55	15.81	12.68	13.12	13.66	14.11	15.36
8H	4H	12.59	13.07	13.55	14.05	15.30	12.21	12.70	13.17	13.67	14.92
	6H	13.22	13.62	14.21	14.63	15.88	12.83	13.24	13.82	14.25	15.50
	8H	13.44	13.79	14.43	14.79	16.06	13.04	13.40	14.04	14.40	15.67
	12H	13.57	13.88	14.57	14.87	16.19	13.16	13.47	14.16	14.46	15.78
12H	4H	12.58	13.02	13.56	14.00	15.26	12.21	12.65	13.19	13.63	14.89
	6H	13.25	13.60	14.24	14.60	15.87	12.87	13.23	13.87	14.23	15.50
	8H	13.49	13.80	14.49	14.79	16.11	13.11	13.42	14.11	14.41	15.73