

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918607

Luminaire Tested: DFN2DIP-4P3F0-050D030US935-FLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P918607  
REPORT IS A COMBINATION OF REPORTS P900565 AND P897473  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-050D030US935-FLLONL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6819.1 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 71.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P918607  
CATALOG NUMBER: DFN2DIP-4P3F0-050D030US935-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P918607

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US935-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	60	58	57	53
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48	53	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	47	44	41	37
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	34	30	27	25
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	29	25	22	19
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1909	1909	1909
5°	1911	1881	1894
10°	1894	1855	1868
15°	1865	1823	1827
20°	1826	1779	1786
25°	1788	1727	1738
30°	1739	1679	1677
35°	1694	1622	1613
40°	1638	1564	1551
45°	1581	1506	1488
50°	1520	1446	1416
55°	1456	1375	1349
60°	1383	1292	1272
65°	1303	1206	1181
70°	1202	1100	1084
75°	1062	974	993
80°	893	813	821
85°	629	539	538

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1581 cd/sqm



TEST NUMBER: P918607

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US935-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.7	2.3
10°-20°	443.6	6.5
20°-30°	651.9	9.6
30°-40°	757.2	11.1
40°-50°	756.2	11.1
50°-60°	659.4	9.7
60°-70°	487.4	7.1
70°-80°	275.8	4.0
80°-90°	74.3	1.1
90°-100°	28.7	0.4
100°-110°	107.2	1.6
110°-120°	284.2	4.2
120°-130°	471.3	6.9
130°-140°	500.7	7.3
140°-150°	465.3	6.8
150°-160°	374.1	5.5
160°-170°	241.1	3.5
170°-180°	83.0	1.2
0°-30°	1253.2	18.4
0°-40°	2010.3	29.5
0°-60°	3425.9	50.2
0°-90°	4263.5	62.5
90°-120°	420.1	6.2
90°-150°	1857.5	27.2
90°-180°	2556.0	37.5
0°-180°	6819.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1651	1664	1661	159
15°	1595	1585	1564	1570	1562	449
25°	1443	1430	1403	1406	1403	664
35°	1245	1229	1203	1194	1186	778
45°	1013	1002	978	960	954	782
55°	767	757	738	718	710	686
65°	517	507	491	477	469	511
75°	270	267	259	250	253	289
85°	66	64	63	58	56	74
90°	1	8	13	16	17	6
95°	41	20	24	28	27	49
105°	192	211	38	45	48	205
115°	363	373	389	97	52	357
125°	513	521	533	537	539	457
135°	635	645	650	657	655	490
145°	736	736	746	751	747	460
155°	810	805	812	816	811	373
165°	854	850	852	857	852	241
175°	874	869	870	875	869	83
180°	872	872	872	872	872	



TEST NUMBER: P918607

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US935-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1675.1	1675.1	1675.1	1675.1	1675.1
2.5°	1684.8	1676.8	1659.1	1675.1	1672.1
5°	1675.1	1668.8	1651.0	1663.8	1660.8
7.5°	1663.8	1654.2	1636.5	1649.5	1646.2
10°	1646.2	1634.9	1615.7	1628.4	1623.7
12.5°	1621.9	1612.4	1593.1	1601.1	1597.8
15°	1594.6	1585.0	1564.0	1570.5	1562.5
17.5°	1560.7	1551.2	1530.2	1538.2	1530.2
20°	1523.7	1514.2	1491.6	1496.3	1490.0
22.5°	1486.8	1472.2	1451.2	1451.2	1447.9
25°	1443.2	1430.4	1403.0	1406.1	1403.0
27.5°	1394.8	1383.5	1362.7	1357.9	1349.9
30°	1346.6	1333.7	1309.6	1304.8	1298.3
32.5°	1295.0	1285.5	1259.6	1249.9	1243.5
35°	1245.1	1229.1	1203.2	1193.5	1185.5
37.5°	1188.7	1174.2	1148.4	1137.1	1129.1
40°	1130.8	1117.8	1092.0	1077.6	1071.2
42.5°	1074.4	1061.4	1035.8	1019.5	1010.0
45°	1013.2	1001.9	977.7	960.1	953.6
47.5°	953.6	942.3	916.5	898.7	889.2
50°	890.7	882.7	860.1	837.6	829.5
52.5°	829.5	818.2	797.4	779.6	768.4
55°	766.8	757.1	737.7	718.4	710.4
57.5°	703.9	695.9	674.9	655.6	649.0
60°	641.0	634.7	612.2	594.3	589.6
62.5°	579.9	568.6	552.5	536.4	529.9
65°	517.1	507.4	491.3	476.8	468.7
67.5°	452.7	444.5	430.2	418.9	412.3
70°	393.0	386.6	372.0	360.8	354.5
72.5°	331.9	325.4	317.4	306.1	301.3
75°	270.5	267.4	259.2	249.7	253.0
77.5°	215.9	209.3	206.1	201.3	196.6
80°	161.2	159.5	156.2	151.4	148.2
82.5°	109.5	109.5	108.0	101.5	101.5
85°	66.0	64.4	62.9	57.9	56.4
87.5°	29.0	25.8	22.6	17.7	16.1
90°	0.6	7.6	12.6	15.8	17.0
92.5°	15.8	13.3	15.2	16.4	17.0
95°	41.0	20.1	24.5	27.8	27.1
97.5°	73.8	22.1	32.1	34.1	34.7
100°	111.7	25.2	36.0	41.0	42.3
102.5°	153.3	152.1	37.2	44.1	46.1
105°	191.7	210.7	38.5	45.4	48.0
107.5°	236.5	252.3	39.8	46.7	49.2
110°	279.5	292.7	110.4	47.4	49.9



TEST NUMBER: P918607

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US935-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	319.9	331.1	320.5	48.6	50.5
115°	362.7	373.4	389.2	97.1	51.7
117.5°	399.9	412.5	423.3	333.0	167.8
120°	441.5	451.0	462.4	469.9	384.8
122.5°	476.8	487.0	499.6	503.3	504.0
125°	512.8	521.0	533.0	537.4	539.3
127.5°	545.6	554.4	564.0	570.2	570.8
130°	576.5	586.7	593.6	600.5	599.9
132.5°	608.0	616.3	623.2	628.9	628.3
135°	634.6	644.7	650.3	656.7	655.4
137.5°	662.3	669.9	676.2	682.5	680.6
140°	689.4	694.5	701.4	707.1	704.0
142.5°	712.2	716.6	724.8	729.8	726.7
145°	736.2	735.5	746.2	750.6	747.4
147.5°	756.9	755.0	765.8	768.9	766.4
150°	777.1	772.7	782.8	786.5	783.4
152.5°	794.1	789.1	798.6	802.4	798.0
155°	810.5	804.9	812.4	816.2	811.2
157.5°	823.8	818.8	824.5	828.9	823.8
160°	835.2	831.4	835.2	839.0	834.5
162.5°	845.2	841.5	844.6	849.0	843.3
165°	854.0	850.3	852.2	856.6	852.2
167.5°	861.0	857.2	859.1	863.6	857.9
170°	866.7	862.9	864.2	868.6	862.9
172.5°	870.5	866.7	868.0	872.4	866.7
175°	873.6	869.2	870.5	874.9	868.6
177.5°	874.9	870.5	871.2	875.5	869.9
180°	871.8	871.8	871.8	871.8	871.8



TEST NUMBER: P918607  
 CATALOG NUMBER: DFN2DIP-4P3F0-050D030US935-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.57	11.55	11.41	12.42	13.50	10.12	11.11	10.96	11.97	13.05
	3H	12.23	13.12	13.09	13.99	15.10	11.74	12.63	12.60	13.50	14.61
	4H	12.82	13.66	13.69	14.54	15.66	12.33	13.16	13.20	14.04	15.16
	6H	13.22	14.00	14.11	14.88	16.01	12.73	13.50	13.61	14.38	15.51
	8H	13.33	14.07	14.22	14.97	16.10	12.83	13.57	13.72	14.47	15.60
	12H	13.38	14.08	14.28	14.98	16.14	12.87	13.57	13.77	14.47	15.63
4H	2H	11.04	11.88	11.91	12.76	13.87	10.68	11.52	11.56	12.40	13.52
	3H	12.91	13.61	13.80	14.52	15.65	12.50	13.20	13.39	14.11	15.25
	4H	13.63	14.26	14.52	15.17	16.33	13.20	13.84	14.10	14.75	15.91
	6H	14.14	14.69	15.06	15.63	16.79	13.71	14.26	14.63	15.19	16.36
	8H	14.29	14.81	15.21	15.73	16.91	13.86	14.37	14.77	15.30	16.47
	12H	14.37	14.83	15.31	15.78	16.96	13.92	14.39	14.86	15.33	16.51
8H	4H	13.83	14.34	14.74	15.27	16.44	13.45	13.97	14.37	14.89	16.07
	6H	14.46	14.89	15.40	15.85	17.03	14.08	14.50	15.02	15.47	16.64
	8H	14.68	15.05	15.63	16.01	17.20	14.29	14.66	15.24	15.62	16.81
	12H	14.81	15.14	15.77	16.10	17.34	14.40	14.73	15.36	15.69	16.93
12H	4H	13.82	14.28	14.75	15.23	16.41	13.45	13.91	14.39	14.86	16.04
	6H	14.49	14.87	15.44	15.82	17.02	14.12	14.49	15.07	15.45	16.64
	8H	14.73	15.06	15.69	16.02	17.26	14.35	14.68	15.31	15.64	16.88