

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921276

Luminaire Tested: DFN2DIP-4P3F0-020D030US940-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921276
REPORT IS A COMBINATION OF REPORTS P899040 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US940-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3883.4 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921276

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921276

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	840	840	840
5°	841	826	832
10°	832	809	804
15°	820	782	762
20°	804	745	711
25°	788	703	661
30°	767	660	598
35°	746	614	543
40°	724	567	479
45°	700	514	422
50°	674	461	366
55°	647	404	312
60°	616	345	256
65°	580	285	230
70°	536	229	208
75°	482	200	189
80°	403	167	162
85°	273	109	121

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 851 cd/sqm

TEST NUMBER: P921276

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	1.8
10°-20°	189.6	4.9
20°-30°	266.3	6.9
30°-40°	290.2	7.5
40°-50°	266.8	6.9
50°-60°	209.5	5.4
60°-70°	136.4	3.5
70°-80°	70.2	1.8
80°-90°	20.3	0.5
90°-100°	52.3	1.3
100°-110°	166.3	4.3
110°-120°	284.7	7.3
120°-130°	374.4	9.6
130°-140°	420.2	10.8
140°-150°	412.1	10.6
150°-160°	345.7	8.9
160°-170°	229.2	5.9
170°-180°	80.1	2.1
0°-30°	525.0	13.5
0°-40°	815.2	21.0
0°-60°	1291.4	33.3
0°-90°	1518.3	39.1
90°-120°	503.4	13.0
90°-150°	1710.0	44.0
90°-180°	2365.0	60.9
0°-180°	3883.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	1	9	25	24	24	4
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	

TEST NUMBER: P921276

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9

TEST NUMBER: P921276

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1

TEST NUMBER: P921276

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.39	6.14	6.44	7.19	8.62	1.36	2.11	2.41	3.16	4.58
	3H	7.06	7.73	8.12	8.79	10.23	2.53	3.20	3.59	4.26	5.70
	4H	7.66	8.30	8.73	9.36	10.81	2.98	3.61	4.05	4.67	6.12
	6H	8.08	8.66	9.16	9.73	11.18	3.29	3.87	4.37	4.94	6.39
	8H	8.20	8.75	9.28	9.83	11.29	3.37	3.93	4.46	5.01	6.46
	12H	8.26	8.78	9.35	9.86	11.33	3.41	3.94	4.50	5.01	6.49
4H	2H	5.40	6.03	6.48	7.10	8.54	1.94	2.58	3.02	3.64	5.08
	3H	7.22	7.74	8.30	8.83	10.29	3.28	3.80	4.36	4.89	6.35
	4H	7.90	8.39	8.99	9.47	10.95	3.82	4.30	4.91	5.38	6.86
	6H	8.41	8.82	9.51	9.93	11.40	4.22	4.64	5.32	5.74	7.21
	8H	8.58	8.97	9.68	10.06	11.55	4.35	4.73	5.44	5.83	7.32
	12H	8.67	9.02	9.78	10.13	11.62	4.40	4.75	5.52	5.86	7.36
8H	4H	7.86	8.25	8.96	9.34	10.83	4.09	4.47	5.18	5.57	7.06
	6H	8.42	8.74	9.54	9.88	11.36	4.59	4.91	5.71	6.05	7.53
	8H	8.63	8.91	9.76	10.03	11.54	4.78	5.06	5.90	6.18	7.68
	12H	8.76	9.01	9.89	10.12	11.67	4.89	5.13	6.02	6.25	7.79
12H	4H	7.81	8.16	8.93	9.27	10.76	4.09	4.44	5.20	5.54	7.04
	6H	8.39	8.67	9.52	9.79	11.30	4.64	4.92	5.77	6.04	7.54
	8H	8.61	8.85	9.74	9.97	11.51	4.84	5.09	5.97	6.20	7.75

END OF REPORT