

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905207

Luminaire Tested: DFN2DIP-HX2F0-050D020US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905207
REPORT IS A COMBINATION OF REPORTS P900677 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D020US835-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905207

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905207

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	98	94	90	97	93	90	86	84	81	78	75	73	71	67	66	64
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	44	52	45	40	47	42	38	42	38	35
6	66	54	45	39	63	51	44	38	47	40	35	42	37	33	38	34	31
7	61	49	40	35	58	47	39	34	42	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	35	30	26	32	28	24
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4584	4584	4584
5°	4584	4509	4542
10°	4540	4438	4472
15°	4465	4354	4368
20°	4368	4241	4261
25°	4271	4109	4139
30°	4151	3985	3987
35°	4036	3841	3826
40°	3897	3695	3672
45°	3758	3548	3514
50°	3605	3394	3332
55°	3444	3215	3162
60°	3262	3005	2968
65°	3062	2785	2740
70°	2809	2518	2492
75°	2460	2197	2252
80°	2037	1788	1817
85°	1383	1122	1125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3758 cd/sqm

TEST NUMBER: P905207

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	2.6
10°-20°	515.2	7.4
20°-30°	757.2	10.9
30°-40°	879.4	12.7
40°-50°	878.3	12.7
50°-60°	765.8	11.1
60°-70°	566.1	8.2
70°-80°	320.3	4.6
80°-90°	85.7	1.2
90°-100°	22.3	0.3
100°-110°	83.0	1.2
110°-120°	220.1	3.2
120°-130°	365.0	5.3
130°-140°	387.7	5.6
140°-150°	360.3	5.2
150°-160°	289.7	4.2
160°-170°	186.7	2.7
170°-180°	64.2	0.9
0°-30°	1455.5	21.0
0°-40°	2334.9	33.7
0°-60°	3979.0	57.4
0°-90°	4951.2	71.4
90°-120°	325.3	4.7
90°-150°	1438.2	20.8
90°-180°	1979.0	28.6
0°-180°	6930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	85
90°	0	6	10	12	13	6
95°	32	16	19	22	21	38
105°	148	163	30	35	37	159
115°	281	289	301	75	40	276
125°	397	403	413	416	418	354
135°	491	499	504	508	508	380
145°	570	570	578	581	579	356
155°	628	623	629	632	628	289
165°	661	658	660	663	660	187
175°	676	673	674	677	672	64
180°	675	675	675	675	675	

TEST NUMBER: P905207

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.5	5.9	9.7	12.2	13.2
92.5°	12.2	10.3	11.7	12.7	13.2
95°	31.7	15.6	19.0	21.5	21.0
97.5°	57.1	17.1	24.9	26.4	26.9
100°	86.5	19.5	27.8	31.7	32.7
102.5°	118.7	117.7	28.8	34.2	35.7
105°	148.5	163.1	29.8	35.1	37.1
107.5°	183.2	195.3	30.8	36.1	38.1
110°	216.4	226.6	85.5	36.7	38.6



TEST NUMBER: P905207

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	247.6	256.4	248.1	37.6	39.1
115°	280.8	289.1	301.4	75.2	40.1
117.5°	309.6	319.4	327.7	257.9	129.9
120°	341.9	349.2	358.0	363.9	297.9
122.5°	369.2	377.0	386.8	389.7	390.3
125°	397.1	403.4	412.7	416.1	417.6
127.5°	422.5	429.3	436.7	441.5	442.0
130°	446.4	454.2	459.6	465.0	464.5
132.5°	470.8	477.2	482.5	486.9	486.5
135°	491.4	499.2	503.5	508.5	507.5
137.5°	512.8	518.7	523.6	528.5	527.0
140°	533.8	537.8	543.1	547.5	545.1
142.5°	551.4	554.9	561.2	565.1	562.6
145°	570.0	569.5	577.8	581.2	578.8
147.5°	586.1	584.6	592.9	595.3	593.4
150°	601.7	598.3	606.1	609.0	606.6
152.5°	614.9	611.0	618.3	621.3	617.8
155°	627.6	623.2	629.1	632.0	628.1
157.5°	637.9	634.0	638.4	641.8	637.9
160°	646.7	643.7	646.7	649.6	646.2
162.5°	654.4	651.5	654.0	657.4	653.0
165°	661.3	658.4	659.8	663.3	659.8
167.5°	666.7	663.7	665.2	668.7	664.2
170°	671.1	668.1	669.1	672.5	668.1
172.5°	674.0	671.1	672.1	675.5	671.1
175°	676.4	673.0	674.0	677.4	672.5
177.5°	677.4	674.0	674.5	677.9	673.5
180°	675.0	675.0	675.0	675.0	675.0

TEST NUMBER: P905207

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.20	15.30	14.95	16.07	17.00	13.78	14.88	14.53	15.65	16.57
	3H	15.86	16.84	16.62	17.62	18.58	15.40	16.38	16.16	17.16	18.12
	4H	16.44	17.37	17.22	18.15	19.13	15.98	16.91	16.76	17.70	18.67
	6H	16.83	17.69	17.62	18.48	19.47	16.37	17.23	17.16	18.03	19.01
	8H	16.93	17.75	17.73	18.56	19.55	16.47	17.29	17.28	18.11	19.09
	12H	16.98	17.76	17.79	18.57	19.58	16.52	17.30	17.33	18.11	19.12
4H	2H	14.68	15.61	15.47	16.40	17.37	14.34	15.27	15.13	16.06	17.03
	3H	16.54	17.32	17.34	18.14	19.13	16.16	16.93	16.95	17.76	18.74
	4H	17.24	17.95	18.05	18.77	19.79	16.85	17.56	17.66	18.38	19.39
	6H	17.75	18.36	18.58	19.21	20.23	17.35	17.97	18.18	18.81	19.83
	8H	17.89	18.46	18.72	19.31	20.34	17.50	18.07	18.33	18.91	19.94
	12H	17.97	18.48	18.82	19.34	20.38	17.56	18.07	18.41	18.94	19.98
8H	4H	17.45	18.02	18.28	18.86	19.90	17.10	17.67	17.93	18.51	19.54
	6H	18.06	18.53	18.92	19.42	20.45	17.71	18.18	18.57	19.07	20.10
	8H	18.27	18.69	19.14	19.57	20.62	17.91	18.33	18.78	19.21	20.26
	12H	18.39	18.76	19.27	19.63	20.74	18.02	18.40	18.90	19.27	20.37
12H	4H	17.44	17.96	18.29	18.82	19.86	17.10	17.61	17.95	18.48	19.52
	6H	18.09	18.51	18.96	19.39	20.44	17.75	18.17	18.62	19.05	20.10
	8H	18.32	18.69	19.19	19.56	20.67	17.98	18.35	18.85	19.22	20.32