

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905229

Luminaire Tested: DFN2DIP-HX2F0-060D020US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905229
REPORT IS A COMBINATION OF REPORTS P900680 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D020US835-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7080.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905229

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905229

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	68	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	54	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	50	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	34	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5843	5843	5843
5°	5843	5736	5776
10°	5776	5610	5577
15°	5687	5411	5277
20°	5572	5143	4912
25°	5455	4844	4560
30°	5301	4539	4118
35°	5149	4213	3728
40°	4994	3877	3285
45°	4815	3507	2883
50°	4630	3133	2492
55°	4435	2737	2116
60°	4209	2324	1732
65°	3948	1906	1547
70°	3631	1516	1385
75°	3233	1310	1239
80°	2661	1061	1043
85°	1740	655	731

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4815 cd/sqm

TEST NUMBER: P905229

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	3.3
10°-20°	638.0	9.0
20°-30°	895.7	12.7
30°-40°	976.4	13.8
40°-50°	897.4	12.7
50°-60°	704.8	10.0
60°-70°	458.8	6.5
70°-80°	236.1	3.3
80°-90°	61.5	0.9
90°-100°	22.3	0.3
100°-110°	83.0	1.2
110°-120°	220.1	3.1
120°-130°	365.0	5.2
130°-140°	387.7	5.5
140°-150°	360.3	5.1
150°-160°	289.7	4.1
160°-170°	186.7	2.6
170°-180°	64.2	0.9
0°-30°	1766.2	24.9
0°-40°	2742.6	38.7
0°-60°	4344.8	61.4
0°-90°	5101.2	72.1
90°-120°	325.3	4.6
90°-150°	1438.2	20.3
90°-180°	1979.0	28.0
0°-180°	7080.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2480	2480	2480	2480	2480	
5°	2480	2469	2439	2460	2453	235
15°	2359	2334	2258	2215	2193	665
25°	2141	2069	1921	1829	1795	985
35°	1845	1730	1533	1391	1342	1155
45°	1508	1358	1122	963	909	1165
55°	1147	972	729	595	552	1025
65°	774	592	390	314	307	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	111
90°	0	6	10	12	13	7
95°	32	16	19	22	21	38
105°	148	163	30	35	37	159
115°	281	289	301	75	40	276
125°	397	403	413	416	418	354
135°	491	499	504	508	508	380
145°	570	570	578	581	579	356
155°	628	623	629	632	628	289
165°	661	658	660	663	660	187
175°	676	673	674	677	672	64
180°	675	675	675	675	675	

TEST NUMBER: P905229

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2479.8	2479.8	2479.8	2479.8	2479.8
2.5°	2491.0	2479.8	2455.0	2477.6	2473.1
5°	2479.8	2468.6	2439.3	2459.6	2452.9
7.5°	2459.6	2446.2	2414.8	2423.6	2412.4
10°	2432.6	2416.9	2372.2	2365.3	2351.9
12.5°	2399.1	2378.8	2318.1	2304.8	2280.0
15°	2358.6	2333.8	2257.6	2215.0	2192.6
17.5°	2311.5	2275.5	2181.2	2131.9	2096.0
20°	2257.6	2212.6	2100.5	2044.5	1995.0
22.5°	2199.3	2147.6	2017.4	1941.2	1907.6
25°	2141.0	2069.1	1921.0	1829.1	1795.3
27.5°	2071.5	1995.0	1831.2	1725.7	1674.1
30°	1997.4	1911.9	1732.4	1618.1	1557.4
32.5°	1925.5	1822.2	1638.4	1503.6	1447.4
35°	1844.8	1730.3	1532.9	1391.4	1341.9
37.5°	1766.2	1642.6	1434.1	1279.1	1223.1
40°	1683.1	1548.6	1330.7	1171.4	1113.1
42.5°	1597.9	1454.3	1227.6	1061.4	1005.5
45°	1508.1	1357.6	1122.2	962.6	908.8
47.5°	1422.9	1263.6	1021.2	861.7	812.4
50°	1328.6	1169.3	922.4	767.4	720.5
52.5°	1236.4	1068.1	828.1	680.0	637.4
55°	1146.7	971.7	729.3	594.8	552.1
57.5°	1054.8	875.2	641.9	516.2	480.2
60°	960.5	781.0	549.8	435.5	399.5
62.5°	868.6	689.1	471.2	363.6	345.7
65°	774.3	592.4	390.5	314.3	307.4
67.5°	684.5	502.6	314.3	276.0	269.3
70°	590.2	415.2	260.2	237.9	228.8
72.5°	500.5	334.3	217.6	199.8	195.2
75°	412.9	255.7	179.5	163.8	161.7
77.5°	325.5	181.7	141.4	132.4	127.9
80°	244.5	130.2	107.6	98.8	98.8
82.5°	170.5	87.6	74.0	69.5	69.5
85°	96.4	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.5	5.9	9.7	12.2	13.2
92.5°	12.2	10.3	11.7	12.7	13.2
95°	31.7	15.6	19.0	21.5	21.0
97.5°	57.1	17.1	24.9	26.4	26.9
100°	86.5	19.5	27.8	31.7	32.7
102.5°	118.7	117.7	28.8	34.2	35.7
105°	148.5	163.1	29.8	35.1	37.1
107.5°	183.2	195.3	30.8	36.1	38.1
110°	216.4	226.6	85.5	36.7	38.6

TEST NUMBER: P905229

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	247.6	256.4	248.1	37.6	39.1
115°	280.8	289.1	301.4	75.2	40.1
117.5°	309.6	319.4	327.7	257.9	129.9
120°	341.9	349.2	358.0	363.9	297.9
122.5°	369.2	377.0	386.8	389.7	390.3
125°	397.1	403.4	412.7	416.1	417.6
127.5°	422.5	429.3	436.7	441.5	442.0
130°	446.4	454.2	459.6	465.0	464.5
132.5°	470.8	477.2	482.5	486.9	486.5
135°	491.4	499.2	503.5	508.5	507.5
137.5°	512.8	518.7	523.6	528.5	527.0
140°	533.8	537.8	543.1	547.5	545.1
142.5°	551.4	554.9	561.2	565.1	562.6
145°	570.0	569.5	577.8	581.2	578.8
147.5°	586.1	584.6	592.9	595.3	593.4
150°	601.7	598.3	606.1	609.0	606.6
152.5°	614.9	611.0	618.3	621.3	617.8
155°	627.6	623.2	629.1	632.0	628.1
157.5°	637.9	634.0	638.4	641.8	637.9
160°	646.7	643.7	646.7	649.6	646.2
162.5°	654.4	651.5	654.0	657.4	653.0
165°	661.3	658.4	659.8	663.3	659.8
167.5°	666.7	663.7	665.2	668.7	664.2
170°	671.1	668.1	669.1	672.5	668.1
172.5°	674.0	671.1	672.1	675.5	671.1
175°	676.4	673.0	674.0	677.4	672.5
177.5°	677.4	674.0	674.5	677.9	673.5
180°	675.0	675.0	675.0	675.0	675.0

TEST NUMBER: P905229

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.99	16.04	15.74	16.81	17.73	10.98	12.03	11.73	12.79	13.71
	3H	16.66	17.60	17.43	18.38	19.33	12.17	13.11	12.93	13.88	14.83
	4H	17.26	18.15	18.05	18.93	19.90	12.61	13.50	13.39	14.28	15.25
	6H	17.68	18.49	18.47	19.29	20.26	12.93	13.75	13.72	14.54	15.52
	8H	17.80	18.57	18.60	19.39	20.36	13.02	13.80	13.82	14.61	15.59
	12H	17.86	18.60	18.67	19.40	20.40	13.06	13.80	13.87	14.61	15.61
4H	2H	15.04	15.92	15.82	16.70	17.67	11.59	12.47	12.37	13.25	14.22
	3H	16.86	17.59	17.65	18.41	19.39	12.94	13.67	13.73	14.49	15.47
	4H	17.54	18.20	18.35	19.02	20.03	13.48	14.14	14.29	14.96	15.97
	6H	18.04	18.61	18.87	19.46	20.47	13.89	14.47	14.72	15.31	16.32
	8H	18.20	18.74	19.04	19.58	20.61	14.01	14.55	14.84	15.39	16.41
	12H	18.30	18.78	19.15	19.64	20.67	14.08	14.56	14.93	15.42	16.45
8H	4H	17.52	18.05	18.35	18.89	19.92	13.76	14.30	14.59	15.13	16.16
	6H	18.06	18.51	18.92	19.39	20.41	14.26	14.71	15.12	15.59	16.61
	8H	18.26	18.66	19.13	19.53	20.58	14.44	14.83	15.31	15.71	16.75
	12H	18.39	18.74	19.27	19.61	20.71	14.55	14.90	15.43	15.77	16.87
12H	4H	17.48	17.96	18.33	18.82	19.85	13.77	14.25	14.62	15.11	16.14
	6H	18.04	18.43	18.91	19.31	20.35	14.30	14.70	15.17	15.58	16.62
	8H	18.25	18.60	19.12	19.46	20.56	14.51	14.86	15.38	15.72	16.82