

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921318

Luminaire Tested: DFN2DIP-4P3F0-040D040US940-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P921318  
REPORT IS A COMBINATION OF REPORTS P899053 AND P895917  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-040D040US940-FLLFLL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6687.9 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 67.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P921318  
CATALOG NUMBER: DFN2DIP-4P3F0-040D040US940-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P921318

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US940-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1582	1582	1582
5°	1583	1559	1570
10°	1569	1537	1548
15°	1545	1510	1514
20°	1513	1474	1480
25°	1481	1431	1440
30°	1441	1391	1389
35°	1403	1344	1336
40°	1357	1296	1285
45°	1310	1248	1233
50°	1260	1198	1173
55°	1206	1140	1118
60°	1146	1071	1054
65°	1080	999	979
70°	996	912	898
75°	880	807	823
80°	740	673	680
85°	521	446	445

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1310 cd/sqm



TEST NUMBER: P921318

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US940-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.6	2.0
10°-20°	367.5	5.5
20°-30°	540.1	8.1
30°-40°	627.3	9.4
40°-50°	626.6	9.4
50°-60°	546.3	8.2
60°-70°	403.9	6.0
70°-80°	228.5	3.4
80°-90°	63.5	0.9
90°-100°	69.8	1.0
100°-110°	221.8	3.3
110°-120°	379.5	5.7
120°-130°	499.2	7.5
130°-140°	560.3	8.4
140°-150°	549.4	8.2
150°-160°	460.9	6.9
160°-170°	305.7	4.6
170°-180°	106.8	1.6
0°-30°	1038.3	15.5
0°-40°	1665.6	24.9
0°-60°	2838.5	42.4
0°-90°	3534.4	52.8
90°-120°	671.2	10.0
90°-150°	2280.1	34.1
90°-180°	3153.0	47.1
0°-180°	6687.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1378	1376	132
15°	1321	1313	1296	1301	1295	372
25°	1196	1185	1162	1165	1162	550
35°	1032	1018	997	989	982	644
45°	840	830	810	796	790	648
55°	635	627	611	595	589	568
65°	428	420	407	395	388	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	61
90°	1	12	33	31	32	6
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P921318

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US940-FLLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1387.9	1387.9	1387.9	1387.9	1387.9
2.5°	1396.0	1389.3	1374.6	1387.9	1385.4
5°	1387.9	1382.6	1367.9	1378.5	1376.0
7.5°	1378.5	1370.6	1355.8	1366.6	1364.0
10°	1364.0	1354.6	1338.6	1349.2	1345.2
12.5°	1343.8	1335.9	1319.9	1326.6	1323.8
15°	1321.2	1313.2	1295.8	1301.2	1294.6
17.5°	1293.2	1285.2	1267.8	1274.4	1267.8
20°	1262.4	1254.5	1235.8	1239.7	1234.6
22.5°	1231.8	1219.8	1202.4	1202.4	1199.7
25°	1195.7	1185.1	1162.4	1165.0	1162.4
27.5°	1155.7	1146.3	1129.1	1125.1	1118.5
30°	1115.7	1105.0	1085.0	1081.0	1075.7
32.5°	1073.0	1065.1	1043.7	1035.6	1030.2
35°	1031.6	1018.3	996.9	988.9	982.2
37.5°	984.9	972.9	951.5	942.2	935.5
40°	936.9	926.1	904.7	892.9	887.5
42.5°	890.2	879.4	858.2	844.7	836.8
45°	839.5	830.2	810.0	795.5	790.1
47.5°	790.1	780.7	759.4	744.7	736.7
50°	738.0	731.3	712.7	693.9	687.2
52.5°	687.2	678.0	660.7	646.0	636.6
55°	635.3	627.2	611.3	595.2	588.6
57.5°	583.2	576.6	559.1	543.1	537.8
60°	531.1	525.8	507.2	492.5	488.5
62.5°	480.5	471.1	457.8	444.4	439.1
65°	428.5	420.4	407.1	395.0	388.4
67.5°	375.1	368.3	356.4	347.1	341.7
70°	325.7	320.3	308.3	298.9	293.6
72.5°	275.0	269.6	263.0	253.6	249.6
75°	224.2	221.6	214.8	206.9	209.6
77.5°	178.8	173.4	170.8	166.7	162.8
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.5	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2



TEST NUMBER: P921318

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US940-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0



TEST NUMBER: P921318  
 CATALOG NUMBER: DFN2DIP-4P3F0-040D040US940-FLLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.09	9.98	10.02	10.93	12.16	8.64	9.53	9.58	10.48	11.71
	3H	10.75	11.54	11.69	12.50	13.76	10.26	11.05	11.20	12.01	13.27
	4H	11.33	12.09	12.29	13.05	14.31	10.84	11.59	11.80	12.56	13.82
	6H	11.73	12.43	12.70	13.39	14.67	11.23	11.93	12.20	12.89	14.17
	8H	11.84	12.50	12.81	13.48	14.75	11.33	11.99	12.31	12.98	14.25
	12H	11.88	12.51	12.86	13.49	14.79	11.37	12.00	12.35	12.98	14.28
4H	2H	9.55	10.30	10.51	11.27	12.53	9.19	9.95	10.16	10.91	12.17
	3H	11.41	12.04	12.39	13.04	14.31	11.01	11.63	11.98	12.63	13.90
	4H	12.13	12.70	13.11	13.69	14.99	11.70	12.28	12.68	13.26	14.56
	6H	12.64	13.13	13.63	14.14	15.44	12.20	12.70	13.20	13.71	15.01
	8H	12.79	13.25	13.78	14.25	15.56	12.35	12.81	13.34	13.81	15.13
	12H	12.86	13.28	13.87	14.30	15.61	12.41	12.83	13.42	13.85	15.16
8H	4H	12.32	12.78	13.32	13.79	15.10	11.94	12.41	12.94	13.41	14.72
	6H	12.95	13.33	13.97	14.37	15.68	12.56	12.94	13.58	13.99	15.30
	8H	13.16	13.50	14.19	14.53	15.86	12.77	13.11	13.80	14.14	15.47
	12H	13.29	13.59	14.33	14.62	15.99	12.88	13.18	13.92	14.21	15.58
12H	4H	12.31	12.72	13.32	13.74	15.06	11.94	12.35	12.95	13.37	14.69
	6H	12.97	13.31	14.00	14.34	15.67	12.60	12.94	13.63	13.97	15.30
	8H	13.21	13.51	14.25	14.54	15.91	12.83	13.13	13.87	14.16	15.53