

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905231

Luminaire Tested: DFN2DIP-HX2F0-060D030US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905231
REPORT IS A COMBINATION OF REPORTS P900689 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D030US835-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8910.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905231

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905231

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71	71	71	67
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63	62	60	56
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49	46	43	40
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44	40	37	34
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5501	5501	5501
5°	5501	5411	5450
10°	5447	5325	5366
15°	5358	5224	5241
20°	5242	5089	5113
25°	5125	4931	4967
30°	4981	4783	4784
35°	4844	4609	4591
40°	4676	4434	4406
45°	4509	4258	4216
50°	4326	4072	3998
55°	4133	3858	3795
60°	3915	3606	3562
65°	3675	3342	3288
70°	3371	3021	2990
75°	2952	2636	2702
80°	2444	2146	2180
85°	1659	1347	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4509 cd/sqm

TEST NUMBER: P905231

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	2.5
10°-20°	618.3	6.9
20°-30°	908.6	10.2
30°-40°	1055.3	11.8
40°-50°	1054.0	11.8
50°-60°	919.0	10.3
60°-70°	679.4	7.6
70°-80°	384.4	4.3
80°-90°	103.2	1.2
90°-100°	33.4	0.4
100°-110°	124.4	1.4
110°-120°	330.1	3.7
120°-130°	547.5	6.1
130°-140°	581.5	6.5
140°-150°	540.5	6.1
150°-160°	434.5	4.9
160°-170°	280.0	3.1
170°-180°	96.4	1.1
0°-30°	1746.6	19.6
0°-40°	2801.8	31.4
0°-60°	4774.8	53.6
0°-90°	5941.8	66.7
90°-120°	487.9	5.5
90°-150°	2157.3	24.2
90°-180°	2968.0	33.3
0°-180°	8910.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	103
90°	1	9	15	18	20	8
95°	48	23	28	32	32	56
105°	223	245	45	53	56	238
115°	421	434	452	113	60	415
125°	596	605	619	624	626	531
135°	737	749	755	763	761	569
145°	855	854	867	872	868	535
155°	941	935	944	948	942	434
165°	992	988	990	995	990	280
175°	1015	1010	1011	1016	1009	97
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P905231

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.7	8.8	14.6	18.4	19.7
92.5°	18.4	15.4	17.6	19.1	19.7
95°	47.6	23.4	28.5	32.3	31.5
97.5°	85.7	25.7	37.3	39.6	40.3
100°	129.7	29.3	41.8	47.6	49.1
102.5°	178.0	176.6	43.2	51.2	53.5
105°	222.7	244.7	44.7	52.7	55.7
107.5°	274.7	293.0	46.2	54.2	57.2
110°	324.6	339.9	128.2	55.0	57.9

TEST NUMBER: P905231

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.5	384.6	372.2	56.4	58.6
115°	421.2	433.7	452.0	112.8	60.1
117.5°	464.5	479.1	491.6	386.8	194.9
120°	512.8	523.8	537.0	545.8	446.9
122.5°	553.8	565.6	580.3	584.6	585.4
125°	595.6	605.1	619.1	624.2	626.4
127.5°	633.7	643.9	655.0	662.3	663.0
130°	669.6	681.4	689.4	697.4	696.8
132.5°	706.2	715.8	723.8	730.4	729.7
135°	737.0	748.8	755.3	762.7	761.2
137.5°	769.2	778.0	785.4	792.7	790.5
140°	800.7	806.6	814.6	821.2	817.6
142.5°	827.2	832.3	841.8	847.6	844.0
145°	855.0	854.2	866.7	871.8	868.1
147.5°	879.1	876.9	889.4	893.0	890.1
150°	902.6	897.5	909.2	913.5	909.9
152.5°	922.3	916.5	927.5	931.9	926.8
155°	941.4	934.9	943.6	948.0	942.2
157.5°	956.8	951.0	957.6	962.7	956.8
160°	970.0	965.6	970.0	974.4	969.2
162.5°	981.7	977.3	981.0	986.1	979.5
165°	991.9	987.6	989.8	994.9	989.8
167.5°	1000.0	995.6	997.8	1003.0	996.4
170°	1006.6	1002.2	1003.7	1008.8	1002.2
172.5°	1011.0	1006.6	1008.1	1013.2	1006.6
175°	1014.6	1009.5	1011.0	1016.1	1008.8
177.5°	1016.1	1011.0	1011.8	1016.9	1010.3
180°	1012.5	1012.5	1012.5	1012.5	1012.5

TEST NUMBER: P905231

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.47	15.51	15.27	16.33	17.34	14.05	15.08	14.85	15.91	16.92
	3H	16.12	17.05	16.93	17.88	18.92	15.66	16.59	16.47	17.42	18.46
	4H	16.70	17.58	17.53	18.41	19.47	16.24	17.12	17.07	17.96	19.01
	6H	17.09	17.90	17.93	18.74	19.81	16.63	17.44	17.47	18.28	19.35
	8H	17.19	17.96	18.04	18.82	19.89	16.73	17.50	17.58	18.37	19.43
	12H	17.23	17.97	18.09	18.83	19.92	16.77	17.51	17.63	18.36	19.46
4H	2H	14.94	15.82	15.78	16.66	17.71	14.61	15.48	15.44	16.32	17.37
	3H	16.80	17.53	17.64	18.40	19.47	16.41	17.15	17.26	18.02	19.08
	4H	17.50	18.16	18.36	19.03	20.13	17.10	17.77	17.96	18.64	19.73
	6H	18.00	18.58	18.87	19.47	20.57	17.60	18.18	18.48	19.07	20.17
	8H	18.14	18.68	19.02	19.57	20.68	17.74	18.28	18.62	19.17	20.28
	12H	18.21	18.70	19.11	19.60	20.72	17.81	18.29	18.70	19.20	20.32
8H	4H	17.70	18.24	18.57	19.13	20.24	17.35	17.89	18.22	18.77	19.88
	6H	18.31	18.75	19.21	19.68	20.79	17.95	18.40	18.86	19.33	20.44
	8H	18.51	18.91	19.43	19.83	20.96	18.16	18.55	19.07	19.48	20.60
	12H	18.64	18.98	19.55	19.90	21.08	18.27	18.62	19.18	19.53	20.71
12H	4H	17.69	18.17	18.59	19.08	20.20	17.34	17.83	18.24	18.74	19.86
	6H	18.33	18.73	19.25	19.65	20.78	17.99	18.39	18.91	19.31	20.44
	8H	18.56	18.91	19.48	19.83	21.01	18.22	18.57	19.14	19.48	20.66