

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907879

Luminaire Tested: DFN2DIP-HX2F0-020D030US840-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907879  
REPORT IS A COMBINATION OF REPORTS P900681 AND P897595  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-020D030US840-FLONL  
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4998.9 lumens  
Efficiency: N/A  
Efficacy: 135.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 37  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907879  
CATALOG NUMBER: DFN2DIP-HX2F0-020D030US840-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P907879

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US840-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1852	1852	1852
5°	1852	1821	1835
10°	1834	1793	1806
15°	1804	1759	1764
20°	1765	1713	1721
25°	1725	1660	1672
30°	1677	1610	1610
35°	1631	1552	1545
40°	1574	1493	1483
45°	1518	1433	1419
50°	1456	1371	1346
55°	1391	1299	1277
60°	1318	1214	1199
65°	1237	1126	1107
70°	1135	1017	1007
75°	994	887	910
80°	823	723	734
85°	558	454	455

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1518 cd/sqm



TEST NUMBER: P907879

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US840-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.0	1.5
10°-20°	208.1	4.2
20°-30°	305.8	6.1
30°-40°	355.2	7.1
40°-50°	354.8	7.1
50°-60°	309.4	6.2
60°-70°	228.7	4.6
70°-80°	129.4	2.6
80°-90°	36.0	0.7
90°-100°	33.7	0.7
100°-110°	125.7	2.5
110°-120°	333.3	6.7
120°-130°	552.9	11.1
130°-140°	587.3	11.7
140°-150°	545.8	10.9
150°-160°	438.8	8.8
160°-170°	282.8	5.7
170°-180°	97.3	1.9
0°-30°	587.9	11.8
0°-40°	943.2	18.9
0°-60°	1607.3	32.2
0°-90°	2001.3	40.0
90°-120°	492.7	9.9
90°-150°	2178.7	43.6
90°-180°	2998.0	60.0
0°-180°	4998.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	786	783	775	781	779	75
15°	748	744	734	737	733	211
25°	677	671	658	660	658	312
35°	584	577	564	560	556	365
45°	475	470	459	450	447	367
55°	360	355	346	337	333	322
65°	243	238	231	224	220	240
75°	127	126	122	117	119	135
85°	31	30	30	27	26	35
90°	1	9	15	19	20	5
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P907879

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US840-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	785.9	785.9	785.9	785.9	785.9
2.5°	790.4	786.7	778.3	785.9	784.5
5°	785.9	782.9	774.6	780.6	779.1
7.5°	780.6	776.1	767.8	773.9	772.3
10°	772.3	767.1	758.0	764.0	761.7
12.5°	760.9	756.5	747.4	751.1	749.6
15°	748.1	743.7	733.8	736.8	733.1
17.5°	732.3	727.8	717.9	721.6	717.9
20°	714.9	710.3	699.7	702.1	699.0
22.5°	697.5	690.7	680.9	680.9	679.3
25°	677.1	671.1	658.2	659.6	658.2
27.5°	654.4	649.1	639.3	637.1	633.3
30°	631.8	625.7	614.4	612.2	609.0
32.5°	607.5	603.1	591.0	586.4	583.4
35°	584.2	576.6	564.5	560.0	556.1
37.5°	557.7	550.9	538.8	533.5	529.7
40°	530.5	524.4	512.3	505.6	502.5
42.5°	504.0	498.0	485.9	478.4	473.8
45°	475.3	470.1	458.7	450.4	447.4
47.5°	447.4	442.1	430.0	421.6	417.2
50°	417.9	414.1	403.5	392.9	389.2
52.5°	389.2	383.8	374.1	365.8	360.5
55°	359.7	355.2	346.1	337.1	333.3
57.5°	330.2	326.5	316.6	307.6	304.5
60°	300.7	297.8	287.2	278.8	276.6
62.5°	272.1	266.7	259.2	251.7	248.6
65°	242.6	238.0	230.6	223.7	219.9
67.5°	212.4	208.5	201.8	196.5	193.5
70°	184.4	181.4	174.5	169.3	166.3
72.5°	155.7	152.7	148.9	143.6	141.4
75°	126.9	125.5	121.6	117.1	118.7
77.5°	101.3	98.3	96.6	94.4	92.2
80°	75.6	74.8	73.3	71.0	69.5
82.5°	51.4	51.4	50.7	47.7	47.7
85°	30.9	30.2	29.5	27.2	26.5
87.5°	13.6	12.1	10.6	8.4	7.6
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P907879

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US840-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P907879  
 CATALOG NUMBER: DFN2DIP-HX2F0-020D030US840-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.28	9.06	9.32	10.10	11.51	7.86	8.63	8.89	9.68	11.09
	3H	9.91	10.61	10.96	11.66	13.08	9.45	10.14	10.50	11.20	12.62
	4H	10.47	11.14	11.53	12.19	13.62	10.02	10.68	11.08	11.73	13.17
	6H	10.85	11.46	11.92	12.52	13.96	10.39	11.00	11.46	12.06	13.50
	8H	10.94	11.52	12.02	12.60	14.04	10.49	11.07	11.56	12.14	13.58
	12H	10.98	11.53	12.06	12.60	14.06	10.52	11.07	11.60	12.14	13.60
4H	2H	8.72	9.38	9.79	10.44	11.87	8.38	9.04	9.45	10.10	11.53
	3H	10.55	11.10	11.62	12.18	13.63	10.17	10.72	11.24	11.80	13.25
	4H	11.24	11.75	12.32	12.82	14.29	10.85	11.35	11.93	12.43	13.89
	6H	11.73	12.16	12.82	13.26	14.72	11.33	11.77	12.42	12.86	14.32
	8H	11.86	12.27	12.95	13.36	14.84	11.47	11.87	12.55	12.96	14.44
	12H	11.92	12.29	13.03	13.39	14.87	11.52	11.88	12.62	12.99	14.47
8H	4H	11.42	11.83	12.51	12.91	14.39	11.07	11.47	12.16	12.56	14.04
	6H	12.02	12.35	13.13	13.48	14.96	11.67	12.00	12.78	13.13	14.61
	8H	12.22	12.52	13.34	13.63	15.12	11.87	12.16	12.98	13.27	14.77
	12H	12.33	12.59	13.45	13.70	15.23	11.96	12.22	13.09	13.33	14.86
12H	4H	11.40	11.77	12.50	12.87	14.35	11.05	11.42	12.16	12.52	14.01
	6H	12.04	12.34	13.16	13.45	14.94	11.70	11.99	12.82	13.11	14.60
	8H	12.26	12.52	13.38	13.63	15.16	11.92	12.17	13.04	13.28	14.82