

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907892

Luminaire Tested: DFN2DIP-HX2F0-020D060US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907892
REPORT IS A COMBINATION OF REPORTS P899192 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D060US840-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7079.2 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907892

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907892

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1967	1967	1967
5°	1967	1931	1944
10°	1944	1888	1877
15°	1914	1821	1776
20°	1876	1731	1654
25°	1836	1631	1535
30°	1784	1528	1386
35°	1733	1418	1255
40°	1681	1305	1106
45°	1621	1181	970
50°	1559	1055	839
55°	1493	921	712
60°	1417	782	583
65°	1329	642	521
70°	1222	510	467
75°	1088	441	417
80°	896	358	351
85°	585	220	246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2568 cd/sqm

TEST NUMBER: P907892

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	1.1
10°-20°	214.8	3.0
20°-30°	301.5	4.3
30°-40°	328.7	4.6
40°-50°	302.1	4.3
50°-60°	237.3	3.4
60°-70°	154.4	2.2
70°-80°	79.5	1.1
80°-90°	25.7	0.4
90°-100°	118.6	1.7
100°-110°	376.8	5.3
110°-120°	644.8	9.1
120°-130°	848.0	12.0
130°-140°	951.8	13.4
140°-150°	933.4	13.2
150°-160°	783.0	11.1
160°-170°	519.2	7.3
170°-180°	181.5	2.6
0°-30°	594.5	8.4
0°-40°	923.2	13.0
0°-60°	1462.6	20.7
0°-90°	1722.2	24.3
90°-120°	1140.1	16.1
90°-150°	3873.3	54.7
90°-180°	5357.0	75.7
0°-180°	7079.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	835	835	835	835	835	
5°	835	831	821	828	826	79
15°	794	786	760	746	738	224
25°	721	696	647	616	604	331
35°	621	582	516	468	452	389
45°	508	457	378	324	306	392
55°	386	327	246	200	186	345
65°	261	199	132	106	104	258
75°	139	86	60	55	54	147
85°	32	17	14	14	14	37
90°	2	21	57	53	55	7
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	

TEST NUMBER: P907892

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	834.8	834.8	834.8	834.8	834.8
2.5°	838.5	834.8	826.4	834.0	832.5
5°	834.8	831.0	821.1	828.0	825.7
7.5°	828.0	823.4	812.8	815.9	812.0
10°	818.9	813.5	798.5	796.2	791.7
12.5°	807.6	800.7	780.3	775.9	767.5
15°	794.0	785.6	759.9	745.6	738.1
17.5°	778.1	766.0	734.3	717.6	705.6
20°	759.9	744.8	707.1	688.2	671.6
22.5°	740.3	723.0	679.1	653.5	642.2
25°	720.7	696.5	646.6	615.7	604.3
27.5°	697.3	671.6	616.4	580.9	563.5
30°	672.4	643.6	583.2	544.7	524.2
32.5°	648.1	613.4	551.5	506.1	487.3
35°	621.0	582.5	516.0	468.4	451.7
37.5°	594.5	552.9	482.7	430.6	411.7
40°	566.5	521.3	448.0	394.4	374.7
42.5°	537.9	489.6	413.2	357.3	338.5
45°	507.7	457.0	377.8	324.1	305.9
47.5°	479.0	425.4	343.8	290.0	273.5
50°	447.3	393.6	310.5	258.3	242.6
52.5°	416.2	359.5	278.7	228.9	214.6
55°	386.0	327.1	245.5	200.3	185.8
57.5°	355.1	294.6	216.1	173.8	161.7
60°	323.4	262.9	185.1	146.6	134.5
62.5°	292.4	232.0	158.6	122.4	116.3
65°	260.6	199.4	131.5	105.8	103.5
67.5°	230.5	169.2	105.8	92.9	90.7
70°	198.6	139.8	87.6	80.1	77.1
72.5°	168.4	112.5	73.2	67.3	65.7
75°	139.0	86.0	60.4	55.1	54.4
77.5°	109.6	61.2	47.6	44.5	43.0
80°	82.3	43.8	36.3	33.2	33.2
82.5°	57.4	29.5	24.9	23.4	23.4
85°	32.4	16.6	14.3	14.3	14.3
87.5°	12.1	6.1	6.1	5.3	5.3
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0

TEST NUMBER: P907892

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3

TEST NUMBER: P907892

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.28	6.93	7.43	8.07	9.67	2.26	2.92	3.41	4.05	5.65
	3H	7.91	8.50	9.08	9.65	11.26	3.42	4.01	4.58	5.15	6.77
	4H	8.50	9.06	9.67	10.20	11.82	3.85	4.41	5.02	5.55	7.17
	6H	8.89	9.40	10.07	10.55	12.18	4.14	4.66	5.32	5.81	7.43
	8H	9.00	9.49	10.18	10.65	12.27	4.22	4.71	5.40	5.87	7.49
	12H	9.05	9.51	10.23	10.67	12.31	4.25	4.71	5.44	5.87	7.51
4H	2H	6.27	6.83	7.45	7.97	9.59	2.82	3.38	4.00	4.52	6.14
	3H	8.05	8.52	9.23	9.69	11.32	4.13	4.60	5.32	5.77	7.40
	4H	8.72	9.15	9.90	10.31	11.95	4.66	5.09	5.84	6.25	7.90
	6H	9.20	9.57	10.39	10.75	12.39	5.05	5.42	6.24	6.60	8.24
	8H	9.36	9.70	10.54	10.87	12.53	5.17	5.51	6.35	6.68	8.34
	12H	9.43	9.74	10.63	10.93	12.58	5.21	5.52	6.41	6.71	8.37
8H	4H	8.67	9.01	9.85	10.18	11.84	4.91	5.25	6.10	6.43	8.08
	6H	9.20	9.48	10.41	10.70	12.35	5.40	5.68	6.60	6.90	8.55
	8H	9.40	9.65	10.61	10.84	12.51	5.58	5.82	6.79	7.01	8.69
	12H	9.51	9.73	10.73	10.92	12.62	5.67	5.89	6.89	7.08	8.78
12H	4H	8.61	8.92	9.81	10.11	11.76	4.90	5.21	6.11	6.40	8.06
	6H	9.17	9.42	10.38	10.61	12.28	5.44	5.69	6.65	6.88	8.55
	8H	9.37	9.58	10.58	10.78	12.48	5.63	5.84	6.84	7.03	8.74

END OF REPORT