

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907905

Luminaire Tested: DFN2DIP-HX2F0-030D040US840-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907905  
REPORT IS A COMBINATION OF REPORTS P900694 AND P897595  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-030D040US840-RLONL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6574.1 lumens  
Efficiency: N/A  
Efficacy: 120.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 54.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907905  
CATALOG NUMBER: DFN2DIP-HX2F0-030D040US840-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P907905  
 CATALOG NUMBER: DFN2DIP-HX2F0-030D040US840-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19			
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15			
8	53	42	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2950	2950	2950
5°	2950	2896	2916
10°	2916	2833	2816
15°	2871	2732	2665
20°	2814	2597	2480
25°	2755	2446	2303
30°	2677	2292	2079
35°	2600	2127	1883
40°	2522	1958	1659
45°	2432	1771	1456
50°	2338	1582	1258
55°	2239	1382	1069
60°	2125	1173	875
65°	1993	962	781
70°	1834	766	699
75°	1632	662	625
80°	1344	535	527
85°	879	331	369

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2432 cd/sqm



TEST NUMBER: P907905

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US840-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.4	1.8
10°-20°	322.1	4.9
20°-30°	452.3	6.9
30°-40°	493.0	7.5
40°-50°	453.1	6.9
50°-60°	355.9	5.4
60°-70°	231.6	3.5
70°-80°	119.2	1.8
80°-90°	32.8	0.5
90°-100°	44.9	0.7
100°-110°	167.6	2.5
110°-120°	444.4	6.8
120°-130°	737.1	11.2
130°-140°	783.0	11.9
140°-150°	727.7	11.1
150°-160°	585.1	8.9
160°-170°	377.0	5.7
170°-180°	129.8	2.0
0°-30°	891.8	13.6
0°-40°	1384.8	21.1
0°-60°	2193.8	33.4
0°-90°	2577.5	39.2
90°-120°	656.9	10.0
90°-150°	2904.8	44.2
90°-180°	3997.0	60.8
0°-180°	6574.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	12	20	25	27	6
95°	64	32	38	43	42	76
105°	300	330	60	71	75	320
115°	567	584	609	152	81	558
125°	802	815	834	840	843	715
135°	992	1008	1017	1027	1025	767
145°	1151	1150	1167	1174	1169	720
155°	1268	1259	1271	1276	1269	584
165°	1336	1330	1333	1340	1333	377
175°	1366	1359	1361	1368	1358	130
180°	1363	1363	1363	1363	1363	



TEST NUMBER: P907905

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US840-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.9	11.8	19.7	24.7	26.6
92.5°	24.7	20.7	23.6	25.7	26.6
95°	64.0	31.5	38.4	43.4	42.4
97.5°	115.4	34.5	50.3	53.3	54.2
100°	174.6	39.5	56.2	64.0	66.0
102.5°	239.6	237.8	58.2	69.0	72.0
105°	299.8	329.5	60.2	71.0	74.9
107.5°	369.9	394.6	62.2	73.0	77.0
110°	437.1	457.7	172.7	74.0	77.9



TEST NUMBER: P907905

CATALOG NUMBER: DFN2DIP-HX2F0-030D040US840-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	500.2	517.9	501.1	75.9	79.0
115°	567.1	583.9	608.6	151.9	81.0
117.5°	625.4	645.1	662.0	520.8	262.4
120°	690.5	705.3	723.1	735.0	601.8
122.5°	745.7	761.5	781.3	787.2	788.2
125°	801.9	814.9	833.5	840.5	843.4
127.5°	853.2	867.1	881.9	891.8	892.7
130°	901.6	917.5	928.2	939.1	938.2
132.5°	950.9	963.8	974.6	983.5	982.6
135°	992.4	1008.2	1017.0	1026.9	1025.0
137.5°	1035.7	1047.5	1057.5	1067.3	1064.4
140°	1078.1	1086.1	1096.9	1105.8	1100.9
142.5°	1113.8	1120.6	1133.5	1141.2	1136.4
145°	1151.2	1150.2	1166.9	1173.9	1168.9
147.5°	1183.7	1180.7	1197.5	1202.4	1198.6
150°	1215.3	1208.4	1224.3	1230.1	1225.2
152.5°	1241.9	1234.1	1248.8	1254.8	1247.9
155°	1267.6	1258.8	1270.6	1276.5	1268.6
157.5°	1288.3	1280.4	1289.4	1296.3	1288.3
160°	1306.1	1300.1	1306.1	1311.9	1305.0
162.5°	1321.8	1316.0	1320.9	1327.8	1318.9
165°	1335.6	1329.8	1332.7	1339.6	1332.7
167.5°	1346.6	1340.5	1343.6	1350.5	1341.6
170°	1355.4	1349.5	1351.4	1358.4	1349.5
172.5°	1361.3	1355.4	1357.5	1364.3	1355.4
175°	1366.1	1359.3	1361.3	1368.2	1358.4
177.5°	1368.2	1361.3	1362.3	1369.3	1360.4
180°	1363.3	1363.3	1363.3	1363.3	1363.3



TEST NUMBER: P907905  
 CATALOG NUMBER: DFN2DIP-HX2F0-030D040US840-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.67	10.42	10.72	11.47	12.89	5.65	6.40	6.70	7.45	8.87
	3H	11.32	11.99	12.38	13.05	14.48	6.82	7.49	7.88	8.55	9.99
	4H	11.90	12.54	12.98	13.60	15.05	7.25	7.89	8.32	8.95	10.39
	6H	12.30	12.88	13.38	13.95	15.41	7.55	8.14	8.64	9.20	10.66
	8H	12.41	12.97	13.50	14.05	15.50	7.64	8.19	8.72	9.27	10.72
	12H	12.46	12.99	13.55	14.06	15.54	7.67	8.20	8.76	9.27	10.75
4H	2H	9.67	10.31	10.75	11.37	12.82	6.22	6.86	7.30	7.92	9.37
	3H	11.47	12.00	12.55	13.08	14.54	7.55	8.07	8.63	9.16	10.62
	4H	12.14	12.62	13.23	13.70	15.18	8.08	8.56	9.17	9.64	11.12
	6H	12.62	13.04	13.72	14.14	15.61	8.47	8.89	9.57	9.99	11.46
	8H	12.78	13.17	13.88	14.26	15.75	8.59	8.98	9.69	10.07	11.56
	12H	12.86	13.21	13.98	14.32	15.81	8.64	8.99	9.76	10.10	11.59
8H	4H	12.09	12.48	13.19	13.58	15.07	8.34	8.72	9.43	9.82	11.31
	6H	12.63	12.95	13.75	14.09	15.57	8.83	9.15	9.95	10.28	11.77
	8H	12.83	13.11	13.96	14.23	15.73	9.01	9.29	10.13	10.40	11.91
	12H	12.95	13.19	14.08	14.31	15.85	9.11	9.35	10.24	10.47	12.01
12H	4H	12.04	12.39	13.16	13.50	14.99	8.33	8.68	9.45	9.79	11.28
	6H	12.60	12.88	13.73	14.00	15.51	8.87	9.15	10.00	10.27	11.77
	8H	12.80	13.05	13.93	14.16	15.71	9.06	9.31	10.19	10.42	11.97