

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907919

Luminaire Tested: DFN2DIP-HX2F0-040D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907919
REPORT IS A COMBINATION OF REPORTS P900685 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D030US840-FLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6998.4 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907919
CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907919

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57	57	57	57
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53	48	48	48	48
2	91	83	77	72	84	77	72	67	67	63	59	58	55	52	49	47	45	40	40	40	40
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	40	38	34	34	34	34
4	76	65	57	50	70	61	53	48	53	47	43	45	41	38	39	35	33	29	29	29	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26	26	26	26
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25	22	22	22	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20	20	20	20
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18	18	18	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16	16	16	16
10	48	36	28	24	45	34	27	22	30	24	20	26	22	18	23	19	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3703	3703	3703
5°	3703	3643	3669
10°	3668	3585	3613
15°	3608	3517	3529
20°	3529	3427	3443
25°	3450	3320	3344
30°	3353	3220	3221
35°	3261	3103	3091
40°	3149	2985	2966
45°	3036	2867	2839
50°	2912	2742	2692
55°	2783	2598	2555
60°	2636	2428	2398
65°	2474	2250	2214
70°	2269	2034	2013
75°	1988	1775	1819
80°	1645	1444	1469
85°	1117	907	908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3036 cd/sqm



TEST NUMBER: P907919

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	2.1
10°-20°	416.2	5.9
20°-30°	611.7	8.7
30°-40°	710.5	10.2
40°-50°	709.6	10.1
50°-60°	618.7	8.8
60°-70°	457.4	6.5
70°-80°	258.8	3.7
80°-90°	70.1	1.0
90°-100°	33.7	0.5
100°-110°	125.7	1.8
110°-120°	333.3	4.8
120°-130°	552.9	7.9
130°-140°	587.3	8.4
140°-150°	545.8	7.8
150°-160°	438.8	6.3
160°-170°	282.8	4.0
170°-180°	97.3	1.4
0°-30°	1175.9	16.8
0°-40°	1886.3	27.0
0°-60°	3214.6	45.9
0°-90°	4000.8	57.2
90°-120°	492.7	7.0
90°-150°	2178.7	31.1
90°-180°	2998.0	42.8
0°-180°	6998.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1468	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	1	9	15	19	20	6
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P907919

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.8	1571.8	1571.8	1571.8	1571.8
2.5°	1580.9	1573.4	1556.7	1571.8	1568.9
5°	1571.8	1565.8	1549.1	1561.2	1558.3
7.5°	1561.2	1552.2	1535.5	1547.7	1544.7
10°	1544.7	1534.1	1516.0	1528.0	1523.5
12.5°	1521.9	1512.9	1494.8	1502.4	1499.2
15°	1496.2	1487.2	1467.5	1473.6	1466.1
17.5°	1464.5	1455.5	1435.8	1443.3	1435.8
20°	1429.7	1420.7	1399.6	1404.0	1398.2
22.5°	1395.0	1381.4	1361.7	1361.7	1358.7
25°	1354.1	1342.1	1316.5	1319.4	1316.5
27.5°	1308.8	1298.2	1278.7	1274.1	1266.7
30°	1263.5	1251.4	1228.8	1224.3	1218.2
32.5°	1215.2	1206.2	1181.9	1172.9	1166.7
35°	1168.3	1153.3	1129.0	1119.9	1112.4
37.5°	1115.4	1101.8	1077.5	1067.0	1059.4
40°	1061.1	1048.8	1024.6	1011.2	1005.1
42.5°	1008.1	995.9	971.9	956.6	947.7
45°	950.7	940.2	917.4	900.9	894.7
47.5°	894.7	884.1	860.0	843.3	834.4
50°	835.8	828.2	807.1	785.9	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.3	674.1	666.6
57.5°	660.5	653.0	633.2	615.1	609.0
60°	601.5	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.5	503.3	497.3
65°	485.2	476.1	461.0	447.4	439.9
67.5°	424.7	417.1	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.7
75°	253.9	251.0	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.1
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P907919

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P907919
 CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.32	13.25	13.21	14.16	15.33	11.90	12.83	12.79	13.74	14.91
	3H	13.96	14.80	14.87	15.72	16.91	13.50	14.33	14.41	15.26	16.45
	4H	14.54	15.32	15.46	16.25	17.45	14.08	14.86	15.00	15.79	16.99
	6H	14.92	15.65	15.85	16.58	17.79	14.46	15.19	15.39	16.12	17.33
	8H	15.02	15.71	15.96	16.66	17.87	14.56	15.25	15.50	16.20	17.41
	12H	15.06	15.72	16.00	16.66	17.90	14.60	15.25	15.54	16.20	17.44
4H	2H	12.78	13.57	13.71	14.50	15.70	12.44	13.23	13.37	14.16	15.36
	3H	14.62	15.28	15.56	16.24	17.45	14.24	14.90	15.18	15.86	17.07
	4H	15.32	15.92	16.27	16.88	18.11	14.93	15.53	15.87	16.48	17.72
	6H	15.82	16.34	16.78	17.31	18.55	15.42	15.94	16.38	16.92	18.16
	8H	15.96	16.44	16.92	17.41	18.66	15.56	16.04	16.52	17.01	18.27
	12H	16.02	16.46	17.00	17.45	18.70	15.62	16.05	16.60	17.04	18.30
8H	4H	15.51	16.00	16.47	16.97	18.22	15.16	15.65	16.12	16.62	17.87
	6H	16.12	16.52	17.10	17.53	18.78	15.77	16.17	16.75	17.18	18.43
	8H	16.32	16.68	17.32	17.68	18.95	15.97	16.32	16.96	17.32	18.59
	12H	16.44	16.75	17.44	17.75	19.06	16.07	16.38	17.07	17.38	18.69
12H	4H	15.50	15.94	16.48	16.92	18.18	15.15	15.59	16.14	16.58	17.84
	6H	16.14	16.50	17.14	17.50	18.77	15.80	16.16	16.80	17.16	18.43
	8H	16.37	16.68	17.37	17.68	18.99	16.02	16.34	17.02	17.33	18.65