

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924004

Luminaire Tested: DFN2DIP-4P3F0-020D030US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924004
REPORT IS A COMBINATION OF REPORTS P899040 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US950-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4154.6 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924004
CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P924004

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	899	899	899
5°	900	884	890
10°	890	866	861
15°	877	837	816
20°	860	797	760
25°	843	752	707
30°	820	706	640
35°	798	657	580
40°	775	606	512
45°	749	550	451
50°	721	493	391
55°	692	432	333
60°	659	369	274
65°	621	305	247
70°	574	245	223
75°	516	214	202
80°	431	178	174
85°	292	116	129

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 907 cd/sqm



TEST NUMBER: P924004

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	1.8
10°-20°	202.9	4.9
20°-30°	284.8	6.9
30°-40°	310.5	7.5
40°-50°	285.4	6.9
50°-60°	224.1	5.4
60°-70°	145.9	3.5
70°-80°	75.1	1.8
80°-90°	21.7	0.5
90°-100°	56.0	1.3
100°-110°	178.0	4.3
110°-120°	304.6	7.3
120°-130°	400.5	9.6
130°-140°	449.6	10.8
140°-150°	440.9	10.6
150°-160°	369.8	8.9
160°-170°	245.3	5.9
170°-180°	85.7	2.1
0°-30°	561.6	13.5
0°-40°	872.1	21.0
0°-60°	1381.7	33.3
0°-90°	1624.4	39.1
90°-120°	538.5	13.0
90°-150°	1829.5	44.0
90°-180°	2530.0	60.9
0°-180°	4154.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	789	789	789	789	789	
5°	789	785	776	782	780	75
15°	750	742	718	704	697	211
25°	681	658	611	582	571	313
35°	587	550	488	442	427	367
45°	480	432	357	306	289	370
55°	365	309	232	189	176	326
65°	246	188	124	100	98	244
75°	131	81	57	52	51	139
85°	31	16	14	14	14	35
90°	1	10	27	25	26	4
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	



TEST NUMBER: P924004

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	788.6	788.6	788.6	788.6	788.6
2.5°	792.1	788.6	780.7	787.9	786.5
5°	788.6	785.0	775.7	782.2	780.0
7.5°	782.2	777.9	767.9	770.7	767.1
10°	773.6	768.5	754.3	752.1	747.9
12.5°	762.9	756.4	737.2	733.0	725.0
15°	750.0	742.1	717.9	704.3	697.3
17.5°	735.1	723.6	693.7	677.9	666.6
20°	717.9	703.6	668.0	650.2	634.4
22.5°	699.4	683.0	641.6	617.3	606.6
25°	680.9	658.0	610.8	581.7	570.9
27.5°	658.7	634.4	582.3	548.7	532.3
30°	635.2	608.0	550.9	514.6	495.2
32.5°	612.3	579.5	521.0	478.1	460.3
35°	586.6	550.3	487.5	442.5	426.7
37.5°	561.6	522.3	456.0	406.8	388.9
40°	535.2	492.5	423.2	372.5	353.9
42.5°	508.1	462.5	390.4	337.5	319.8
45°	479.6	431.7	356.9	306.1	289.0
47.5°	452.5	401.8	324.7	274.0	258.3
50°	422.5	371.9	293.4	244.0	229.2
52.5°	393.1	339.6	263.3	216.3	202.7
55°	364.6	309.0	231.9	189.2	175.5
57.5°	335.4	278.3	204.2	164.2	152.7
60°	305.5	248.3	174.9	138.5	127.1
62.5°	276.2	219.1	149.9	115.6	109.9
65°	246.2	188.4	124.2	100.0	97.8
67.5°	217.7	159.8	100.0	87.8	85.7
70°	187.7	132.0	82.7	75.7	72.8
72.5°	159.1	106.3	69.2	63.5	62.1
75°	131.3	81.3	57.0	52.1	51.4
77.5°	103.5	57.8	44.9	42.1	40.6
80°	77.8	41.4	34.2	31.4	31.4
82.5°	54.2	27.9	23.6	22.1	22.1
85°	30.6	15.6	13.5	13.5	13.5
87.5°	11.4	5.7	5.7	5.0	5.0
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3



TEST NUMBER: P924004

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2



TEST NUMBER: P924004
 CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.63	6.38	6.68	7.43	8.85	1.59	2.34	2.64	3.39	4.81
	3H	7.30	7.96	8.36	9.03	10.47	2.77	3.44	3.83	4.50	5.94
	4H	7.90	8.53	8.97	9.59	11.04	3.21	3.84	4.28	4.91	6.35
	6H	8.31	8.89	9.39	9.96	11.42	3.52	4.10	4.60	5.17	6.63
	8H	8.43	8.99	9.52	10.07	11.52	3.61	4.16	4.69	5.24	6.69
	12H	8.49	9.02	9.58	10.09	11.57	3.64	4.17	4.73	5.24	6.72
4H	2H	5.64	6.27	6.71	7.33	8.78	2.17	2.81	3.25	3.87	5.32
	3H	7.45	7.98	8.54	9.07	10.53	3.51	4.04	4.60	5.13	6.59
	4H	8.14	8.62	9.23	9.70	11.18	4.05	4.53	5.14	5.61	7.09
	6H	8.64	9.06	9.74	10.16	11.64	4.46	4.87	5.56	5.97	7.45
	8H	8.81	9.20	9.91	10.30	11.79	4.58	4.97	5.68	6.06	7.55
	12H	8.90	9.25	10.02	10.36	11.86	4.64	4.99	5.75	6.10	7.59
8H	4H	8.10	8.48	9.20	9.58	11.07	4.32	4.71	5.42	5.80	7.29
	6H	8.66	8.97	9.78	10.11	11.60	4.83	5.15	5.95	6.28	7.77
	8H	8.87	9.15	10.00	10.27	11.77	5.01	5.29	6.14	6.41	7.92
	12H	9.00	9.24	10.13	10.36	11.90	5.12	5.37	6.25	6.48	8.03
12H	4H	8.04	8.39	9.16	9.50	11.00	4.32	4.67	5.44	5.78	7.27
	6H	8.63	8.91	9.76	10.03	11.53	4.87	5.15	6.00	6.27	7.78
	8H	8.84	9.09	9.97	10.20	11.75	5.08	5.32	6.21	6.44	7.98