

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907920

Luminaire Tested: DFN2DIP-HX2F0-040D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907920
REPORT IS A COMBINATION OF REPORTS P899166 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D030US840-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6114.7 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907920

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907920

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	100	96	92	88		93	89	86	83		77	75	72		66	64	63		55	54	53
2	91	84	78	73		85	79	73	69		68	64	61		58	56	53		49	47	46
3	84	74	67	62		78	70	63	58		61	56	52		52	49	46		44	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	51	46		66	56	49	43		49	43	39		42	38	35		36	33	30
6	65	53	46	40		61	50	43	38		44	38	34		38	34	31		33	30	27
7	61	48	41	35		56	46	39	34		40	35	30		35	31	27		30	27	24
8	56	44	37	31		52	42	35	30		37	31	27		32	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	28	25		30	25	22		26	23	20
10	49	37	30	25		46	35	29	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3934	3934	3934
5°	3934	3862	3889
10°	3889	3777	3755
15°	3829	3643	3553
20°	3751	3462	3307
25°	3673	3261	3070
30°	3569	3056	2772
35°	3467	2837	2510
40°	3363	2611	2212
45°	3242	2361	1941
50°	3117	2110	1677
55°	2986	1842	1425
60°	2833	1564	1166
65°	2658	1283	1041
70°	2445	1021	932
75°	2176	882	835
80°	1791	714	703
85°	1171	441	493

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3242 cd/sqm

TEST NUMBER: P907920

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	2.6
10°-20°	429.5	7.0
20°-30°	603.0	9.9
30°-40°	657.4	10.8
40°-50°	604.2	9.9
50°-60°	474.5	7.8
60°-70°	308.9	5.1
70°-80°	159.0	2.6
80°-90°	43.3	0.7
90°-100°	59.3	1.0
100°-110°	188.4	3.1
110°-120°	322.4	5.3
120°-130°	424.0	6.9
130°-140°	475.9	7.8
140°-150°	466.7	7.6
150°-160°	391.5	6.4
160°-170°	259.6	4.2
170°-180°	90.7	1.5
0°-30°	1189.0	19.4
0°-40°	1846.4	30.2
0°-60°	2925.1	47.8
0°-90°	3436.3	56.2
90°-120°	570.1	9.3
90°-150°	1936.6	31.7
90°-180°	2678.0	43.8
0°-180°	6114.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1670	1670	1670	1670	1670	
5°	1670	1662	1642	1656	1651	158
15°	1588	1571	1520	1491	1476	447
25°	1441	1393	1293	1231	1209	663
35°	1242	1165	1032	937	903	777
45°	1015	914	756	648	612	784
55°	772	654	491	400	372	690
65°	521	399	263	212	207	517
75°	278	172	121	110	109	294
85°	65	33	29	29	29	75
90°	1	10	28	27	28	6
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P907920

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1669.5	1669.5	1669.5	1669.5	1669.5
2.5°	1677.1	1669.5	1652.8	1668.1	1665.0
5°	1669.5	1661.9	1642.2	1655.9	1651.4
7.5°	1655.9	1646.9	1625.8	1631.6	1624.2
10°	1637.8	1627.2	1597.0	1592.4	1583.5
12.5°	1615.2	1601.5	1560.6	1551.7	1535.0
15°	1587.9	1571.2	1519.9	1491.3	1476.2
17.5°	1556.2	1532.0	1468.4	1435.3	1411.1
20°	1519.9	1489.7	1414.1	1376.4	1343.1
22.5°	1480.7	1445.9	1358.2	1306.9	1284.3
25°	1441.4	1393.0	1293.2	1231.4	1208.6
27.5°	1394.6	1343.1	1232.8	1161.9	1127.0
30°	1344.7	1287.2	1166.3	1089.3	1048.5
32.5°	1296.4	1226.8	1103.0	1012.3	974.4
35°	1242.0	1164.9	1032.0	936.8	903.4
37.5°	1189.1	1105.9	965.4	861.1	823.4
40°	1133.2	1042.6	896.0	788.7	749.4
42.5°	1075.7	979.1	826.5	714.6	676.9
45°	1015.3	914.0	755.5	648.1	611.9
47.5°	958.0	850.7	687.5	580.2	546.9
50°	894.4	787.2	621.0	516.6	485.0
52.5°	832.4	719.1	557.5	457.8	429.1
55°	772.0	654.2	491.0	400.4	371.7
57.5°	710.1	589.3	432.1	347.5	323.4
60°	646.6	525.7	370.1	293.2	269.0
62.5°	584.8	463.9	317.2	244.8	232.8
65°	521.3	398.8	262.9	211.6	206.9
67.5°	460.9	338.4	211.6	185.8	181.3
70°	397.4	279.5	175.2	160.2	154.0
72.5°	337.0	225.1	146.5	134.5	131.5
75°	277.9	172.2	120.9	110.3	108.9
77.5°	219.1	122.3	95.2	89.2	86.0
80°	164.6	87.7	72.4	66.6	66.6
82.5°	114.8	59.0	49.9	46.8	46.8
85°	64.9	33.2	28.7	28.7	28.7
87.5°	24.2	12.0	12.0	10.6	10.6
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0

TEST NUMBER: P907920

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P907920

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.33	13.21	13.24	14.13	15.32	8.31	9.19	9.22	10.12	11.30
	3H	13.98	14.77	14.91	15.71	16.91	9.49	10.28	10.41	11.21	12.42
	4H	14.58	15.32	15.51	16.26	17.48	9.93	10.67	10.86	11.61	12.83
	6H	14.98	15.67	15.93	16.61	17.84	10.24	10.92	11.18	11.87	13.10
	8H	15.10	15.75	16.05	16.71	17.94	10.32	10.97	11.27	11.93	13.16
	12H	15.15	15.77	16.11	16.73	17.98	10.36	10.98	11.32	11.93	13.19
4H	2H	12.35	13.09	13.29	14.03	15.25	8.90	9.64	9.84	10.58	11.80
	3H	14.15	14.77	15.11	15.74	16.97	10.23	10.85	11.18	11.82	13.05
	4H	14.83	15.39	15.79	16.36	17.61	10.77	11.33	11.73	12.30	13.55
	6H	15.32	15.81	16.30	16.79	18.05	11.17	11.66	12.15	12.65	13.90
	8H	15.48	15.94	16.46	16.92	18.19	11.29	11.75	12.27	12.73	14.00
	12H	15.57	15.98	16.56	16.97	18.25	11.35	11.76	12.34	12.76	14.03
8H	4H	14.80	15.25	15.77	16.23	17.50	11.04	11.49	12.01	12.47	13.74
	6H	15.34	15.71	16.34	16.73	18.00	11.54	11.91	12.54	12.93	14.20
	8H	15.54	15.87	16.55	16.88	18.16	11.71	12.04	12.72	13.05	14.34
	12H	15.66	15.95	16.67	16.95	18.29	11.82	12.11	12.83	13.11	14.45
12H	4H	14.75	15.16	15.74	16.15	17.43	11.04	11.45	12.04	12.45	13.72
	6H	15.31	15.64	16.32	16.65	17.94	11.58	11.91	12.59	12.92	14.20
	8H	15.52	15.81	16.53	16.81	18.14	11.78	12.07	12.79	13.07	14.40