

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924021

Luminaire Tested: DFN2DIP-4P3F0-030D020US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924021
REPORT IS A COMBINATION OF REPORTS P900552 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US950-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4321.6 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924021

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924021

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1348	1348	1348
5°	1349	1326	1335
10°	1335	1299	1291
15°	1316	1255	1223
20°	1291	1195	1141
25°	1265	1128	1061
30°	1231	1059	960
35°	1197	985	871
40°	1163	909	769
45°	1123	825	677
50°	1082	740	586
55°	1038	648	500
60°	988	554	411
65°	931	457	370
70°	861	367	334
75°	773	322	303
80°	647	267	261
85°	438	174	193

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1123 cd/sqm

TEST NUMBER: P924021

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	2.6
10°-20°	304.3	7.0
20°-30°	427.3	9.9
30°-40°	465.7	10.8
40°-50°	428.1	9.9
50°-60°	336.2	7.8
60°-70°	218.8	5.1
70°-80°	112.6	2.6
80°-90°	29.9	0.7
90°-100°	21.2	0.5
100°-110°	79.1	1.8
110°-120°	209.9	4.9
120°-130°	348.2	8.1
130°-140°	369.8	8.6
140°-150°	343.7	8.0
150°-160°	276.4	6.4
160°-170°	178.1	4.1
170°-180°	61.3	1.4
0°-30°	842.5	19.5
0°-40°	1308.2	30.3
0°-60°	2072.5	48.0
0°-90°	2433.8	56.3
90°-120°	310.3	7.2
90°-150°	1372.0	31.7
90°-180°	1888.0	43.7
0°-180°	4321.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	0	6	9	12	13	4
95°	30	15	18	20	20	36
105°	142	156	28	34	35	151
115°	268	276	288	72	38	264
125°	379	385	394	397	398	338
135°	469	476	480	485	484	362
145°	544	543	551	554	552	340
155°	599	594	600	603	599	276
165°	631	628	629	633	629	178
175°	645	642	643	646	642	61
180°	644	644	644	644	644	

TEST NUMBER: P924021

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	0.5	5.6	9.3	11.6	12.6
92.5°	11.6	9.8	11.2	12.1	12.6
95°	30.2	14.9	18.1	20.5	20.0
97.5°	54.5	16.3	23.8	25.2	25.7
100°	82.5	18.6	26.5	30.2	31.2
102.5°	113.2	112.3	27.5	32.6	34.1
105°	141.7	155.6	28.4	33.5	35.4
107.5°	174.8	186.3	29.4	34.4	36.3
110°	206.4	216.2	81.6	35.0	36.8



TEST NUMBER: P924021

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	236.2	244.6	236.7	35.9	37.3
115°	267.9	275.8	287.5	71.7	38.3
117.5°	295.4	304.7	312.6	246.0	123.9
120°	326.2	333.1	341.5	347.2	284.2
122.5°	352.2	359.7	369.0	371.8	372.3
125°	378.8	384.8	393.7	397.0	398.4
127.5°	403.1	409.6	416.6	421.2	421.7
130°	425.9	433.3	438.5	443.6	443.1
132.5°	449.1	455.2	460.3	464.5	464.1
135°	468.8	476.2	480.3	485.1	484.2
137.5°	489.2	494.8	499.5	504.2	502.8
140°	509.2	513.1	518.1	522.3	520.0
142.5°	526.0	529.4	535.4	539.1	536.7
145°	543.8	543.3	551.2	554.5	552.2
147.5°	559.1	557.7	565.6	567.9	566.1
150°	574.0	570.8	578.2	581.0	578.7
152.5°	586.6	582.9	589.9	592.7	589.4
155°	598.7	594.5	600.2	602.9	599.2
157.5°	608.6	604.8	609.0	612.3	608.6
160°	617.0	614.1	617.0	619.7	616.5
162.5°	624.3	621.5	623.9	627.2	623.0
165°	630.9	628.1	629.4	632.8	629.4
167.5°	636.0	633.2	634.6	637.9	633.6
170°	640.2	637.4	638.3	641.6	637.4
172.5°	643.0	640.2	641.2	644.4	640.2
175°	645.3	642.0	643.0	646.2	641.6
177.5°	646.2	643.0	643.5	646.7	642.5
180°	643.9	643.9	643.9	643.9	643.9

TEST NUMBER: P924021

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-RLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.72	9.61	9.63	10.53	11.71	4.68	5.57	5.59	6.49	7.67
	3H	10.40	11.19	11.32	12.12	13.33	5.87	6.66	6.79	7.59	8.80
	4H	11.01	11.75	11.94	12.69	13.91	6.32	7.06	7.25	8.00	9.22
	6H	11.43	12.12	12.37	13.06	14.29	6.63	7.32	7.58	8.27	9.49
	8H	11.55	12.21	12.51	13.17	14.39	6.72	7.38	7.68	8.34	9.56
	12H	11.62	12.24	12.57	13.19	14.44	6.77	7.39	7.72	8.34	9.59
4H	2H	8.74	9.49	9.69	10.43	11.64	5.28	6.03	6.22	6.97	8.18
	3H	10.57	11.19	11.52	12.16	13.39	6.63	7.25	7.58	8.22	9.45
	4H	11.26	11.83	12.22	12.79	14.05	7.17	7.74	8.13	8.70	9.96
	6H	11.78	12.26	12.75	13.25	14.50	7.59	8.08	8.56	9.06	10.32
	8H	11.95	12.41	12.93	13.38	14.65	7.72	8.17	8.69	9.15	10.42
	12H	12.05	12.46	13.04	13.45	14.72	7.78	8.19	8.77	9.18	10.46
8H	4H	11.23	11.69	12.21	12.67	13.93	7.46	7.91	8.43	8.89	10.16
	6H	11.80	12.17	12.80	13.19	14.46	7.97	8.34	8.97	9.36	10.63
	8H	12.01	12.34	13.02	13.35	14.63	8.15	8.48	9.16	9.49	10.78
	12H	12.15	12.44	13.16	13.44	14.77	8.27	8.56	9.28	9.56	10.89
12H	4H	11.19	11.60	12.18	12.59	13.87	7.46	7.87	8.45	8.87	10.14
	6H	11.77	12.10	12.78	13.11	14.40	8.02	8.35	9.02	9.36	10.64
	8H	11.99	12.28	13.00	13.29	14.62	8.22	8.51	9.23	9.52	10.85

END OF REPORT