

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924039

Luminaire Tested: DFN2DIP-4P3F0-040D020US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924039
REPORT IS A COMBINATION OF REPORTS P900553 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D020US950-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5666.7 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 53
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924039
CATALOG NUMBER: DFN2DIP-4P3F0-040D020US950-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P924039

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67				67
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56				56
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47				47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40				40
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34				34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30				30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26				26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23				23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21				21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19				19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17				17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1692	1692	1692
5°	1694	1667	1679
10°	1679	1644	1656
15°	1653	1616	1620
20°	1619	1577	1583
25°	1584	1531	1540
30°	1542	1488	1486
35°	1501	1438	1429
40°	1452	1386	1375
45°	1402	1335	1319
50°	1347	1281	1255
55°	1290	1219	1196
60°	1226	1145	1128
65°	1155	1069	1048
70°	1066	976	961
75°	942	864	880
80°	791	720	728
85°	558	477	477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1402 cd/sqm



TEST NUMBER: P924039

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.8	2.5
10°-20°	393.2	6.9
20°-30°	577.9	10.2
30°-40°	671.2	11.8
40°-50°	670.3	11.8
50°-60°	584.5	10.3
60°-70°	432.1	7.6
70°-80°	244.5	4.3
80°-90°	65.7	1.2
90°-100°	21.2	0.4
100°-110°	79.1	1.4
110°-120°	209.9	3.7
120°-130°	348.2	6.1
130°-140°	369.8	6.5
140°-150°	343.7	6.1
150°-160°	276.4	4.9
160°-170°	178.1	3.1
170°-180°	61.3	1.1
0°-30°	1110.8	19.6
0°-40°	1782.0	31.4
0°-60°	3036.8	53.6
0°-90°	3779.0	66.7
90°-120°	310.3	5.5
90°-150°	1372.0	24.2
90°-180°	1888.0	33.3
0°-180°	5666.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	0	6	9	12	13	5
95°	30	15	18	20	20	36
105°	142	156	28	34	35	151
115°	268	276	288	72	38	264
125°	379	385	394	397	398	338
135°	469	476	480	485	484	362
145°	544	543	551	554	552	340
155°	599	594	600	603	599	276
165°	631	628	629	633	629	178
175°	645	642	643	646	642	61
180°	644	644	644	644	644	



TEST NUMBER: P924039

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	0.5	5.6	9.3	11.6	12.6
92.5°	11.6	9.8	11.2	12.1	12.6
95°	30.2	14.9	18.1	20.5	20.0
97.5°	54.5	16.3	23.8	25.2	25.7
100°	82.5	18.6	26.5	30.2	31.2
102.5°	113.2	112.3	27.5	32.6	34.1
105°	141.7	155.6	28.4	33.5	35.4
107.5°	174.8	186.3	29.4	34.4	36.3
110°	206.4	216.2	81.6	35.0	36.8



TEST NUMBER: P924039

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	236.2	244.6	236.7	35.9	37.3
115°	267.9	275.8	287.5	71.7	38.3
117.5°	295.4	304.7	312.6	246.0	123.9
120°	326.2	333.1	341.5	347.2	284.2
122.5°	352.2	359.7	369.0	371.8	372.3
125°	378.8	384.8	393.7	397.0	398.4
127.5°	403.1	409.6	416.6	421.2	421.7
130°	425.9	433.3	438.5	443.6	443.1
132.5°	449.1	455.2	460.3	464.5	464.1
135°	468.8	476.2	480.3	485.1	484.2
137.5°	489.2	494.8	499.5	504.2	502.8
140°	509.2	513.1	518.1	522.3	520.0
142.5°	526.0	529.4	535.4	539.1	536.7
145°	543.8	543.3	551.2	554.5	552.2
147.5°	559.1	557.7	565.6	567.9	566.1
150°	574.0	570.8	578.2	581.0	578.7
152.5°	586.6	582.9	589.9	592.7	589.4
155°	598.7	594.5	600.2	602.9	599.2
157.5°	608.6	604.8	609.0	612.3	608.6
160°	617.0	614.1	617.0	619.7	616.5
162.5°	624.3	621.5	623.9	627.2	623.0
165°	630.9	628.1	629.4	632.8	629.4
167.5°	636.0	633.2	634.6	637.9	633.6
170°	640.2	637.4	638.3	641.6	637.4
172.5°	643.0	640.2	641.2	644.4	640.2
175°	645.3	642.0	643.0	646.2	641.6
177.5°	646.2	643.0	643.5	646.7	642.5
180°	643.9	643.9	643.9	643.9	643.9



TEST NUMBER: P924039
 CATALOG NUMBER: DFN2DIP-4P3F0-040D020US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.48	11.51	11.28	12.34	13.35	10.03	11.07	10.83	11.89	12.90
	3H	12.15	13.08	12.96	13.91	14.95	11.66	12.59	12.47	13.42	14.46
	4H	12.74	13.62	13.57	14.46	15.51	12.25	13.12	13.08	13.96	15.01
	6H	13.15	13.96	13.99	14.80	15.87	12.65	13.46	13.49	14.30	15.37
	8H	13.25	14.02	14.10	14.89	15.96	12.75	13.52	13.60	14.39	15.45
	12H	13.31	14.04	14.16	14.90	15.99	12.80	13.53	13.65	14.39	15.48
4H	2H	10.96	11.83	11.79	12.67	13.72	10.60	11.48	11.44	12.32	13.37
	3H	12.83	13.57	13.68	14.44	15.50	12.43	13.16	13.27	14.03	15.10
	4H	13.55	14.22	14.41	15.09	16.18	13.13	13.79	13.99	14.66	15.76
	6H	14.07	14.65	14.95	15.54	16.64	13.64	14.22	14.51	15.11	16.21
	8H	14.22	14.76	15.10	15.65	16.76	13.79	14.32	14.66	15.21	16.32
	12H	14.30	14.79	15.20	15.70	16.81	13.85	14.34	14.75	15.25	16.36
8H	4H	13.76	14.30	14.63	15.19	16.30	13.38	13.92	14.26	14.81	15.92
	6H	14.39	14.84	15.29	15.77	16.88	14.01	14.45	14.91	15.38	16.49
	8H	14.61	15.00	15.52	15.93	17.06	14.22	14.61	15.13	15.54	16.66
	12H	14.74	15.09	15.66	16.01	17.19	14.33	14.68	15.25	15.60	16.78
12H	4H	13.75	14.24	14.65	15.14	16.26	13.38	13.87	14.28	14.78	15.89
	6H	14.42	14.82	15.33	15.74	16.87	14.05	14.44	14.96	15.37	16.49
	8H	14.67	15.01	15.58	15.93	17.11	14.28	14.63	15.20	15.55	16.73