

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910611

Luminaire Tested: DFN2DIP-HX2F0-020D040US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910611
REPORT IS A COMBINATION OF REPORTS P900691 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D040US850-FLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6587.5 lumens
Efficiency: N/A
Efficacy: 147.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910611
CATALOG NUMBER: DFN2DIP-HX2F0-020D040US850-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P910611
 CATALOG NUMBER: DFN2DIP-HX2F0-020D040US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33			
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28			
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29	24			
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20			
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21	17			
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15			
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13			
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12			
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10			
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9			
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2033	2033	2033
5°	2033	2000	2015
10°	2014	1968	1984
15°	1981	1931	1938
20°	1938	1881	1890
25°	1895	1823	1836
30°	1841	1768	1768
35°	1791	1704	1697
40°	1729	1639	1628
45°	1667	1574	1559
50°	1599	1506	1478
55°	1528	1426	1403
60°	1447	1333	1317
65°	1358	1236	1215
70°	1246	1116	1106
75°	1092	974	999
80°	904	794	806
85°	612	498	500

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1667 cd/sqm



TEST NUMBER: P910611

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.2
10°-20°	228.6	3.5
20°-30°	335.9	5.1
30°-40°	390.1	5.9
40°-50°	389.6	5.9
50°-60°	339.7	5.2
60°-70°	251.1	3.8
70°-80°	142.1	2.2
80°-90°	40.1	0.6
90°-100°	49.4	0.7
100°-110°	184.0	2.8
110°-120°	488.1	7.4
120°-130°	809.5	12.3
130°-140°	859.9	13.1
140°-150°	799.2	12.1
150°-160°	642.5	9.8
160°-170°	414.0	6.3
170°-180°	142.5	2.2
0°-30°	645.7	9.8
0°-40°	1035.8	15.7
0°-60°	1765.1	26.8
0°-90°	2198.5	33.4
90°-120°	721.5	11.0
90°-150°	3190.0	48.4
90°-180°	4389.0	66.6
0°-180°	6587.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	1	13	22	27	29	6
95°	70	35	42	48	47	83
105°	329	362	66	78	82	352
115°	623	641	668	167	89	613
125°	881	895	915	923	926	785
135°	1090	1107	1117	1128	1126	842
145°	1264	1263	1281	1289	1284	791
155°	1392	1382	1395	1402	1393	641
165°	1467	1460	1464	1471	1464	414
175°	1500	1493	1495	1502	1492	143
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P910611

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	1.0	13.0	21.6	27.2	29.2
92.5°	27.2	22.7	26.0	28.2	29.2
95°	70.3	34.6	42.1	47.7	46.6
97.5°	126.8	37.9	55.2	58.6	59.6
100°	191.7	43.4	61.8	70.3	72.5
102.5°	263.2	261.2	63.9	75.7	79.1
105°	329.3	361.9	66.1	78.0	82.3
107.5°	406.2	433.3	68.3	80.2	84.5
110°	480.0	502.6	189.6	81.3	85.5



TEST NUMBER: P910611

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	549.3	568.7	550.3	83.4	86.7
115°	622.8	641.2	668.4	166.8	88.9
117.5°	686.8	708.4	726.9	571.9	288.1
120°	758.3	774.5	794.0	807.1	660.9
122.5°	818.9	836.3	858.0	864.5	865.6
125°	880.7	894.9	915.4	923.0	926.2
127.5°	937.0	952.2	968.5	979.4	980.4
130°	990.1	1007.5	1019.3	1031.3	1030.3
132.5°	1044.2	1058.4	1070.3	1080.1	1079.1
135°	1089.8	1107.2	1116.9	1127.7	1125.6
137.5°	1137.4	1150.4	1161.3	1172.1	1168.9
140°	1184.0	1192.7	1204.6	1214.4	1208.9
142.5°	1223.1	1230.7	1244.7	1253.3	1248.0
145°	1264.3	1263.2	1281.4	1289.1	1283.7
147.5°	1299.9	1296.6	1315.1	1320.5	1316.3
150°	1334.6	1327.0	1344.4	1350.9	1345.4
152.5°	1363.8	1355.2	1371.4	1377.9	1370.4
155°	1392.0	1382.4	1395.3	1401.8	1393.1
157.5°	1414.8	1406.1	1416.0	1423.5	1414.8
160°	1434.3	1427.7	1434.3	1440.7	1433.2
162.5°	1451.6	1445.1	1450.6	1458.1	1448.4
165°	1466.8	1460.3	1463.5	1471.1	1463.5
167.5°	1478.7	1472.1	1475.5	1483.1	1473.3
170°	1488.5	1482.0	1484.1	1491.7	1482.0
172.5°	1494.9	1488.5	1490.7	1498.3	1488.5
175°	1500.3	1492.7	1494.9	1502.5	1491.7
177.5°	1502.5	1494.9	1496.0	1503.7	1493.9
180°	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P910611
 CATALOG NUMBER: DFN2DIP-HX2F0-020D040US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.83	8.56	8.92	9.64	11.13	7.41	8.14	8.49	9.22	10.71
	3H	9.45	10.11	10.55	11.20	12.71	8.99	9.65	10.09	10.74	12.25
	4H	10.02	10.64	11.13	11.73	13.25	9.56	10.18	10.67	11.28	12.79
	6H	10.39	10.96	11.51	12.06	13.59	9.93	10.50	11.05	11.60	13.13
	8H	10.48	11.03	11.60	12.14	13.66	10.03	10.57	11.15	11.68	13.20
	12H	10.52	11.03	11.64	12.14	13.68	10.06	10.57	11.18	11.68	13.22
4H	2H	8.26	8.88	9.38	9.98	11.49	7.93	8.55	9.04	9.64	11.16
	3H	10.09	10.61	11.21	11.73	13.25	9.71	10.22	10.83	11.35	12.87
	4H	10.78	11.25	11.90	12.37	13.91	10.38	10.86	11.51	11.97	13.52
	6H	11.26	11.67	12.39	12.80	14.34	10.87	11.27	12.00	12.41	13.95
	8H	11.40	11.78	12.53	12.90	14.46	11.00	11.38	12.13	12.51	14.06
	12H	11.45	11.80	12.60	12.94	14.49	11.05	11.39	12.19	12.53	14.09
8H	4H	10.95	11.33	12.08	12.46	14.01	10.60	10.98	11.73	12.11	13.66
	6H	11.55	11.86	12.70	13.03	14.58	11.20	11.51	12.35	12.68	14.23
	8H	11.75	12.03	12.91	13.18	14.75	11.40	11.67	12.55	12.82	14.39
	12H	11.86	12.10	13.02	13.25	14.85	11.49	11.73	12.65	12.88	14.49
12H	4H	10.93	11.27	12.08	12.41	13.97	10.59	10.93	11.73	12.07	13.63
	6H	11.57	11.85	12.73	13.00	14.57	11.23	11.51	12.39	12.66	14.23
	8H	11.79	12.03	12.95	13.18	14.78	11.44	11.69	12.61	12.83	14.44